










PCB LAYOUT KEYED / CONNECTED ONLY WITH ADDITIONAL FRAME (THICK KEYING)
Leiterplattenanschluss kodiert / nur in Verbindung mit zusätzlichem Rahmen



PCB LAYOUT KEYED / CONNECTED ONLY WITH ADDITIONAL FRAME (SLIM KEYING)
Leiterplattenanschluss kodiert / nur in Verbindung mit zusätzlichem Rahmen




- 19 COLOR MARKING IN THIS AREA. COLOR SEE TABLE
- 18 SLOT, THICK, BETWEEN CAVITIES
- 17 KEYING, THICK, BETWEEN POSITION
- 16 SLOT, SLIM, FOR SIDE KEYING, LAST CAVITY
Schlitz,duenn, an letzte Kammer
- 15 SLOT, SLIM, FOR SIDE KEYING,SIDE CAVITY 1
Schlitz,duenn, fuer Seitenkodierung
- 14 SIDE KEYING, SLIM, ON LAST CAVITY
Seitenkodierung, duenn, an letzte Kammer
- 13 SIDE KEYING, SLIM, ON CAVITY 1
Seitenkodierung, duenn, an Kammer 1
- 12 KEYING SLIM BETWEEN POSITIONS
- 11 PRELIMINARY PART NOT RELEASED FOR PRODUCTION
- 10 TE LOGO
- 9 INCLUSIVE COPPER LOADING
Inklusive Kupferkaschierung
- 8 PCB PREFERABLY CHAMFERED
Leiterplatte vorzugsweise angefast
- 7 SLOT, THICK, FOR SIDE KEYING
Schlitz,dick, fuer Seitenkodierung
- 6 SIDE KEYING, THICK, ON LAST CAVITY
Seitenkodierung, dick, an letzte Kammer
- 5 WIRE RANG: 0.22-0.35mm² SEE APPLICATION SPEC. 114-18467
Drahtgrößenbereich: 0.22-0.35mm² siehe Verarbeitungsspec. 114-18467
- 4 IEC60695-2-11 / IEC60335-1 GLOW WIRE TEST 750 °C WITHOUT FLAME
IEC60695-2-11 / IEC60335-1 Gluehdrahttest 750 °C ohne Flamme
- 3 X..CAVITY LOADED WITH CONTACT
O..CAVITY WITHOUT CONTACT
X..Kammer mit Kontakt bestueckt
O..Kammer ohne Kontakt
- 2 MATING PART: PCB (WITH FRAMES ACC. RAST 2.5 E.G. PN 964 575/576
TABHEADER PN 829 866/867
Passender Gegenstecker: Leiterplatten (mit Rahmen nach RAST 2.5 z.B.
964 575/576) Tabwannen Nr. 829 866/867
- 1 KEYING RIBS: CUTTING WITH TERMINATION MACHINE POSSIBLE
Kodierrippe; Schneiden auf der Verarbeitungsmaschine moeglich



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN H. Karabiyik 24MAY2002	 TE Connectivity		NAME AMP DUOPLUG 2.5 MARK II FEMALE CONNECTOR 3-20 POSITION SELECTIVE LOADED	RESTRICTED TO -
DIMENSIONS: mm		CHK B. Schnaubel 24MAY2002				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. Klenger 24MAY2002	PRODUCT SPEC 108-18785		SIZE A 1	CAGE CODE 00779
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±°	APPLICATION SPEC 114-18467	WEIGHT -			
MATERIAL -	FINISH -	Customer Drawing		SHEET 1 OF 2		REP 021

Kodierschema

a b c d



OBSOLETE

OBSOLETE

OBSOLETE