




6 12 12
OBSOLETE

9

FINISH	B	A	NO OF POSN	PART NUMBER
--------	---	---	---------------	----------------

SUPERSEDED BY 6-147100-6		△	△	43.18[1.700]	45.72[1.800]	36	△	4-147100-1
OBSOLETE		△		2.54[.100]	5.08[.200]	4	△	4-147100-0
		△		-	2.54[.100]	2	△	3-147100-9
				99.06[3.900]	101.60[4.000]	80	△	3-147100-8
				96.52[3.800]	99.06[3.900]	78	△	3-147100-7
				93.98[3.700]	96.52[3.800]	76	△	3-147100-6
				91.44[3.600]	93.98[3.700]	74	△	3-147100-5
				88.90[3.500]	91.44[3.600]	72	△	3-147100-4
				86.36[3.400]	88.90[3.500]	70	△	3-147100-3
				83.82[3.300]	86.36[3.400]	68	△	3-147100-2
				81.28[3.200]	83.82[3.300]	66	△	3-147100-1
				78.74[3.100]	81.28[3.200]	64	△	3-147100-0
				76.20[3.000]	78.74[3.100]	62	△	2-147100-9
				73.66[2.900]	76.20[3.000]	60	△	2-147100-8
				71.12[2.800]	73.66[2.900]	58	△	2-147100-7
				68.58[2.700]	71.12[2.800]	56	△	2-147100-6
				66.04[2.600]	68.58[2.700]	54	△	2-147100-5
				63.50[2.500]	66.04[2.600]	52	△	2-147100-4
				60.96[2.400]	63.50[2.500]	50	△	2-147100-3
				58.42[2.300]	60.96[2.400]	48	△	2-147100-2
				55.88[2.200]	58.42[2.300]	46	△	2-147100-1
			53.34[2.100]	55.88[2.200]	44	△	2-147100-0	
		△		50.80[2.000]	53.34[2.100]	42	△	1-147100-9
				48.26[1.900]	50.80[2.000]	40	△	1-147100-8
				45.72[1.800]	48.26[1.900]	38	△	1-147100-7
SUPERSEDED 6-147100-6				43.18[1.700]	45.72[1.800]	36	△	1-147100-6
				40.64[1.600]	43.18[1.700]	34	△	1-147100-5
				38.10[1.500]	40.64[1.600]	32	△	1-147100-4
				35.56[1.400]	38.10[1.500]	30	△	1-147100-3
				33.02[1.300]	35.56[1.400]	28	△	1-147100-2
				30.48[1.200]	33.02[1.300]	26	△	1-147100-1
				27.94[1.100]	30.48[1.200]	24	△	1-147100-0
				25.40[1.000]	27.94[1.100]	22	△	147100-9
				22.86[.900]	25.40[1.000]	20	△	147100-8
				20.32[.800]	22.86[.900]	18	△	147100-7
SUPERSEDED 5-147100-6				17.78[.700]	20.32[.800]	16	△	147100-6
				15.24[.600]	17.78[.700]	14	△	147100-5
				12.70[.500]	15.24[.600]	12	△	147100-4
		△		10.16[.400]	12.70[.500]	10	△	147100-3
		△		7.62[.300]	10.16[.400]	8	△	147100-2
		△		5.08[.200]	7.62[.300]	6	△	147100-1
		△						

SUPERSEDED 6-147100-6

SUPERSEDED 5-147100-6

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN M.BINNER	06NOV2002			TE Connectivity Ltd.	
DIMENSIONS: mm [INCHES]						TOLERANCES UNLESS OTHERWISE SPECIFIED:		CW .JOLSON	06NOV02	NAME	
								APR .JOLSON	06NOV02		
						PRODUCT SPEC		AMPMODU_REC ASSY, MOD IV			
						108-25022		DBL ROW, DUAL ENTRY, .100X.100CL,			
						APPLICATION SPEC		VERTICAL MOUNT			
						114-25018					
MATERIAL						WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE								A1	00779	147100	-
CUSTOMER DRAWING								SCALE	SHEET	OF	REV
								4:1	1	1	K5