

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19164-0317](#)
Status: **Active**
Overview: [Perma-Seal™ Terminals](#)
Description: Perma-Seal™ Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-015 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19164](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Perma-Seal™ Terminals](#)
Product Name Perma-Seal™
Type Ring
UPC 800753115729

Physical

Barrel Type Closed
Insulation NiAc™
Material - Plating Mating Tin
Net Weight 2.446/g
Packaging Type Adhesive Tape on Reel
Stud Size 1/4" (M6)
Wire Insulation Diameter 7.87mm
Wire Size AWG 10, 12
Wire Size mm² 1.23 - 1.94

Material Info

Old Part Number SC-230-14T

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-015
Sales Drawing SD-19164-041



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19164Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Power Crimp Tool	0640057400
Head for Terminals	
10-22 AWG Wire	
PremiumGrade™	0640017400
Hand Crimp Tool	
ATP Perishable	0198082025
Tool Kit used in ATP	
Presses that Process	
Product on Tape	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19164-0317](#)