

---

**REVISION HISTORY**

| Revision | Description   | Issue Date |
|----------|---|------------|
| 1.0      | Initial issue   | Feb 2007   |
| 2.0      | Add-in industrial temperature option for 28-pin 600 mil PDIP.<br>Standby current(I <sub>sb1</sub> ) reduced to be 20uA for I-grade and 10uA for C grade | July 2017  |



## 8K X 8 BIT LOW POWER CMOS SRAM

### FEATURES

- Access time :55ns
- Low power consumption:  
Operation current :  
15mA (TYP.),  $V_{CC} = 3.0V$   
Standby current :  
1 $\mu A$  (TYP.),  $V_{CC} = 3.0V$
- Wide range power supply : 2.7 ~ 5.5V
- Fully Compatible with all Competitors 5V product
- Fully Compatible with all Competitors 3.3V product
- All inputs and outputs TTL compatible
- Fully static operation
- Tri-state output
- Data retention voltage :1.5V (MIN.)
- **All products ROHS Compliant**
- Package : 28-pin 600 mil PDIP  
28-pin 330 mil SOP  
28-pin 8mm x 13.4mm sTSOP


### GENERAL DESCRIPTION

The AS6C6264 is a 65,536-bit low power CMOS static random access memory organized as 8,192 words by 8 bits. It is fabricated using very high performance, high reliability CMOS technology. Its standby current is stable within the range of operating temperature.

The AS6C6264 is well designed for low power application, and particularly well suited for battery back-up nonvolatile memory application.

The AS6C6264 operates with wide range power supply.

### FUNCTIONAL BLOCK DIAGRAM




### PIN DESCRIPTION

| SYMBOL    | DESCRIPTION         |
|-----------|---------------------|
| A0 - A12  | Address Inputs      |
| DQ0 - DQ7 | Data Inputs/Outputs |
| CE#, CE2  | Chip Enable Inputs  |
| WE#       | Write Enable Input  |
| OE#       | Output Enable Input |
| Vcc       | Power Supply        |
| Vss       | Ground              |
| NC        | No Connection       |



## 8K X 8 BIT LOW POWER CMOS SRAM

### PIN CONFIGURATION



### ABSOLUTE MAXIMUM RATINGS\*

| PARAMETER                            | SYMBOL              | RATING             | UNIT |
|--------------------------------------|---------------------|--------------------|------|
| Terminal Voltage with Respect to Vss | V <sub>TERM</sub>   | -0.5 to 7.0        | V    |
| Operating Temperature                | T <sub>A</sub>      | 0 to 70(C grade)   | °C   |
|                                      |                     | -40 to 85(I grade) |      |
| Storage Temperature                  | T <sub>STG</sub>    | -65 to 150         | °C   |
| Power Dissipation                    | P <sub>D</sub>      | 1                  | W    |
| DC Output Current                    | I <sub>OUT</sub>    | 50                 | mA   |
| Soldering Temperature (under 10 sec) | T <sub>SOLDER</sub> | 260                | °C   |

\*Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to the absolute maximum rating conditions for extended period may affect device reliability.

### TRUTH TABLE

| MODE           | CE# | CE2 | OE# | WE# | I/O OPERATION    | SUPPLY CURRENT                     |
|----------------|-----|-----|-----|-----|------------------|------------------------------------|
| Standby        | H   | X   | X   | X   | High-Z           | I <sub>SB</sub> , I <sub>SB1</sub> |
|                | X   | L   | X   | X   | High-Z           | I <sub>SB</sub> , I <sub>SB1</sub> |
| Output Disable | L   | H   | H   | H   | High-Z           | I <sub>CC</sub> , I <sub>CC1</sub> |
| Read           | L   | H   | L   | H   | D <sub>OUT</sub> | I <sub>CC</sub> , I <sub>CC1</sub> |
| Write          | L   | H   | X   | L   | D <sub>IN</sub>  | I <sub>CC</sub> , I <sub>CC1</sub> |

Note: H = V<sub>IH</sub>, L = V<sub>IL</sub>, X = Don't care.



## 8K X 8 BIT LOW POWER CMOS SRAM

### DC ELECTRICAL CHARACTERISTICS

| PARAMETER                              | SYMBOL                       | TEST CONDITION   | MIN.  | TYP. <sup>5</sup> | MAX.                 | UNIT |
|--|------------------------------|--|-------|-------------------|----------------------|------|
| Supply Voltage                         | V <sub>CC</sub>              |  | 2.7   | 3.0               | 5.5                  | V    |
| Input High Voltage                     | V <sub>IH</sub> <sup>1</sup> |  | 2.4V  | -                 | V <sub>CC</sub> +0.3 | V    |
| Input Low Voltage                      | V <sub>IL</sub> <sup>2</sup> |  | - 0.5 | -                 | 0.6                  | V    |
| Input Leakage Current                  | I <sub>LI</sub>              | V <sub>CC</sub> ≥ V <sub>IN</sub> ≥ V <sub>SS</sub>  | - 1   | -                 | 1                    | μA   |
| Output Leakage Current                 | I <sub>LO</sub>              | V <sub>CC</sub> ≥ V <sub>OUT</sub> ≥ V <sub>SS</sub> ,<br>Output Disabled  | - 1   | -                 | 1                    | μA   |
| Output High Voltage                    | V <sub>OH</sub>              | I <sub>OH</sub> = -1mA   | 2.4   | 3.0               | -                    | V    |
| Output Low Voltage                     | V <sub>OL</sub>              | I <sub>OL</sub> = 2mA  | -     | -                 | 0.4                  | V    |
| Average Operating Power supply Current | I <sub>CC</sub>              | Cycle time = Min.<br>CE# = V <sub>IL</sub> and CE2 = V <sub>IH</sub> ,<br>I <sub>I/O</sub> = 0mA   | - 55  | 15                | 45                   | mA   |
|  | I <sub>CC1</sub>             | Cycle time = 1μs<br>CE# ≤ 0.2V and CE2 ≥ V <sub>CC</sub> -0.2V,<br>I <sub>I/O</sub> = 0mA<br>other pins at 0.2V or V <sub>CC</sub> -0.2V | -     | 3                 | 10                   | mA   |
| Standby Power Supply Current           | I <sub>SB1</sub>             | CE# ≥ V <sub>CC</sub> -0.2V<br>or CE2 ≤ 0.2V   | -C    | 1                 | 10 <sup>*4</sup>     | μA   |
|  |                              |  | -I    | 1                 | 20 <sup>*4</sup>     | μA   |

Notes: C = Commercial Temperature I = Industrial temperature

1. V<sub>IH</sub>(max) = V<sub>CC</sub> + 3.0V for pulse width less than 10ns.

2. V<sub>IL</sub>(min) = V<sub>SS</sub> - 3.0V for pulse width less than 10ns.

3. Over/Undershoot specifications are characterized, not 100% tested.

4. 10 μA for special request

5. Typical values are included for reference only and are not guaranteed or tested.

Typical values are measured at V<sub>CC</sub> = V<sub>CC</sub>(TYP.) and T<sub>A</sub> = 25°C

### CAPACITANCE (T<sub>A</sub> = 25°C, f = 1.0MHz)

| PARAMETER                | SYMBOL           | MIN. | MAX | UNIT |
|--------------------------|------------------|------|-----|------|
| Input Capacitance        | C <sub>IN</sub>  | -    | 6   | pF   |
| Input/Output Capacitance | C <sub>I/O</sub> | -    | 8   | pF   |

Note : These parameters are guaranteed by device characterization, but not production tested.

### AC TEST CONDITIONS

|  |   |
|--|---|
| Input Pulse Levels                       | 0.2V to V <sub>CC</sub> - 0.2V  |
| Input Rise and Fall Times                | 3ns   |
| Input and Output Timing Reference Levels | 1.5V  |
| Output Load                              | C <sub>L</sub> = 50pF + 1TTL, I <sub>OH</sub> /I <sub>OL</sub> = -1mA/2mA |



## AC ELECTRICAL CHARACTERISTICS

### (1) READ CYCLE

| PARAMETER                          | SYM.               |  |  | AS6C6264-55 |      |  |  | UNIT |
|------------------------------------|--------------------|--|--|-------------|------|--|--|------|
|                                    |                    |  |  | MIN.        | MAX. |  |  |      |
| Read Cycle Time                    | t <sub>RC</sub>    |  |  | 55          | -    |  |  | ns   |
| Address Access Time                | t <sub>AA</sub>    |  |  | -           | 55   |  |  | ns   |
| Chip Enable Access Time            | t <sub>ACE</sub>   |  |  | -           | 55   |  |  | ns   |
| Output Enable Access Time          | t <sub>OE</sub>    |  |  |             | 30   |  |  | ns   |
| Chip Enable to Output in Low-Z     | t <sub>CLZ</sub> * |  |  | 10          | -    |  |  | ns   |
| Output Enable to Output in Low-Z   | t <sub>OLZ</sub> * |  |  | 5           | -    |  |  | ns   |
| Chip Disable to Output in High-Z   | t <sub>CHZ</sub> * |  |  | -           | 20   |  |  | ns   |
| Output Disable to Output in High-Z | t <sub>OHZ</sub> * |  |  |             | 20   |  |  | ns   |
| Output Hold from Address Change    | t <sub>OH</sub>    |  |  | 10          | -    |  |  | ns   |

### (2) WRITE CYCLE


| PARAMETER                        | SYM.               |  |  | AS6C6264-55 |      |  |  | UNIT |
|----------------------------------|--------------------|--|--|-------------|------|--|--|------|
|                                  |                    |  |  | MIN.        | MAX. |  |  |      |
| Write Cycle Time                 | t <sub>WC</sub>    |  |  | 55          | -    |  |  | ns   |
| Address Valid to End of Write    | t <sub>AW</sub>    |  |  | 50          | -    |  |  | ns   |
| Chip Enable to End of Write      | t <sub>CW</sub>    |  |  | 50          | -    |  |  | ns   |
| Address Set-up Time              | t <sub>AS</sub>    |  |  | 0           | -    |  |  | ns   |
| Write Pulse Width                | t <sub>WP</sub>    |  |  | 45          | -    |  |  | ns   |
| Write Recovery Time              | t <sub>WR</sub>    |  |  | 0           | -    |  |  | ns   |
| Data to Write Time Overlap       | t <sub>DW</sub>    |  |  | 25          | -    |  |  | ns   |
| Data Hold from End of Write Time | t <sub>DH</sub>    |  |  | 0           | -    |  |  | ns   |
| Output Active from End of Write  | t <sub>OW</sub> *  |  |  | 5           | -    |  |  | ns   |
| Write to Output in High-Z        | t <sub>WHZ</sub> * |  |  | -           | 20   |  |  | ns   |

\*These parameters are guaranteed by device characterization, but not production tested.




## TIMING WAVEFORMS

### READ CYCLE 1 (Address Controlled) (1,2)



### READ CYCLE 2 (CE# and CE2 and OE# Controlled) (1,3,4,5)




#### Notes :

- 1.WE# is high for read cycle.
- 2.Device is continuously selected OE# = low, CE# = low, CE2 = high.
- 3.Address must be valid prior to or coincident with CE# = low, CE2 = high; otherwise  $t_{AA}$  is the limiting parameter.
4. $t_{CLZ}$ ,  $t_{OLZ}$ ,  $t_{CHZ}$  and  $t_{OHZ}$  are specified with  $C_L = 5pF$ . Transition is measured  $\pm 500mV$  from steady state.
- 5.At any given temperature and voltage condition,  $t_{CHZ}$  is less than  $t_{CLZ}$ ,  $t_{OHZ}$  is less than  $t_{OLZ}$ .




# 8K X 8 BIT LOW POWER CMOS SRAM

## WRITE CYCLE 1 (WE# Controlled) (1,2,3,5,6)



## WRITE CYCLE 2 (CE# and CE2 Controlled) (1,2,5,6)



### Notes :

1. WE#, CE# must be high or CE2 must be low during all address transitions.
2. A write occurs during the overlap of a low CE#, high CE2, low WE#.
3. During a WE#-controlled write cycle with OE# low, tWP must be greater than tWHZ + tDW to allow the drivers to turn off and data to be placed on the bus.
4. During this period, I/O pins are in the output state, and input signals must not be applied.
5. If the CE# low transition and CE2 high transition occurs simultaneously with or after WE# low transition, the outputs remain in a high impedance state.
6. tOW and tWHZ are specified with CL = 5pF. Transition is measured  $\pm 500\text{mV}$  from steady state.




## DATA RETENTION CHARACTERISTICS

| PARAMETER                           | SYMBOL           | TEST CONDITION  | MIN.              | TYP. | MAX. | UNIT    |
|-------------------------------------|------------------|---|-------------------|------|------|---------|
| V <sub>CC</sub> for Data Retention  | V <sub>DR</sub>  | CE# $\geq$ V <sub>CC</sub> - 0.2V<br>or CE2 $\leq$ 0.2V                           | 1.5               | -    | 5.5  | V       |
| Data Retention Current              | I <sub>DR</sub>  | V <sub>CC</sub> = 1.5V<br>CE# $\geq$ V <sub>CC</sub> - 0.2V<br>or CE2 $\leq$ 0.2V | -                 | 0.5  | 10   | $\mu$ A |
| Chip Disable to Data Retention Time | t <sub>CDR</sub> | See Data Retention Waveforms (below)  | 0                 | -    | -    | ns      |
| Recovery Time                       | t <sub>R</sub>   |   | t <sub>RC</sub> * | -    | -    | ns      |


t<sub>RC</sub>\* = Read Cycle Time

## DATA RETENTION WAVEFORM

### Low V<sub>CC</sub> Data Retention Waveform (1) (CE# controlled)



### Low V<sub>CC</sub> Data Retention Waveform (2) (CE2 controlled)








## PACKAGE OUTLINE DIMENSION


28 pin 600 mil PDIP Package Outline Dimension



| SYM. | UNIT | INCH.(BASE) | MM(REF)      |
|------|------|-------------|--------------|
| A1   |      | 0.010 (MIN) | 0.254 (MIN)  |
| A2   |      | 0.150±0.005 | 3.810±0.127  |
| B    |      | 0.020 (MAX) | 0.508(MAX)   |
| B1   |      | 0.055 (MAX) | 1.397(MAX)   |
| c    |      | 0.012 (MAX) | 0.304 (MAX)  |
| D    |      | 1.430 (MAX) | 36.322 (MAX) |
| E    |      | 0.6 (TYP)   | 15.24 (TYP)  |
| E1   |      | 0.52 (MAX)  | 13.208 (MAX) |
| e    |      | 0.100 (TYP) | 2.540(TYP)   |
| eB   |      | 0.625 (MAX) | 15.87 (MAX)  |
| L    |      | 0.180(MAX)  | 4.572(MAX)   |
| S    |      | 0.06 (MAX)  | 1.524 (MAX)  |
| Q1   |      | 0.08(MAX)   | 2.032(MAX)   |
| Θ    |      | 15°(MAX)    | 15°(MAX)     |




28 pin 330 mil SOP Package Outline Dimension



| SYM. | UNIT | INCH(BASE)  | MM(REF)      |
|------|------|-------------|--------------|
| A    |      | 0.120 (MAX) | 3.048 (MAX)  |
| A1   |      | 0.002(MIN)  | 0.05(MIN)    |
| A2   |      | 0.098±0.005 | 2.489±0.127  |
| b    |      | 0.016 (TYP) | 0.406(TYP)   |
| c    |      | 0.010 (TYP) | 0.254(TYP)   |
| D    |      | 0.728 (MAX) | 18.491 (MAX) |
| E    |      | 0.340 (MAX) | 8.636 (MAX)  |
| E1   |      | 0.465±0.012 | 11.811±0.305 |
| e    |      | 0.050 (TYP) | 1.270(TYP)   |
| L    |      | 0.05 (MAX)  | 1.270 (MAX)  |
| L1   |      | 0.067±0.008 | 1.702 ±0.203 |
| S    |      | 0.047 (MAX) | 1.194 (MAX)  |
| y    |      | 0.003(MAX)  | 0.076(MAX)   |
| Θ    |      | 0°~10°      | 0°~10°       |



28 pin 8mm x 13.4mm sTSP Package Outline Dimension



| UNIT<br>SYM. | INCH(BASE)   | MM(REF)    |
|--------------|--------------|------------|
| A            | 0.047 (MAX)  | 1.20 (MAX) |
| A1           | 0.004±0.002  | 0.10±0.05  |
| A2           | 0.039±0.002  | 1.00±0.05  |
| b            | 0.006 (TYP)  | 0.15(TYP)  |
| c            | 0.010 (TYP)  | 0.254(TYP) |
| Db           | 0.465±0.004  | 11.80±0.10 |
| E            | 0.315±0.004  | 8.00±0.10  |
| e            | 0.022 (TYP)  | 0.55(TYP)  |
| D            | 0.528±0.008  | 13.40±0.20 |
| L            | 0.020±0.004  | 0.50±0.10  |
| L1           | 0.0315±0.004 | 0.80±0.10  |
| y            | 0.08(MAX)    | 0.003(MAX) |
| Θ            | 0°~5°        | 0°~5°      |

Note : E dimension is not including end flash. The total of both sides' end flash is not above 0.3mm.



## 8K X 8 BIT LOW POWER CMOS SRAM


### ORDERING INFORMATION

#### Ordering Codes

| Alliance                        | Organization | VCC range | Package                   | Operating Temp                 | Speed ns |
|---------------------------------|--------------|-----------|---------------------------|--------------------------------|----------|
| <a href="#">AS6C6264-55PCN</a>  | 8k x 8       | 2.7-5.5V  | 28pin 600mil PDIP         | Commercial ~<br>0° C to 70° C  | 55       |
| <a href="#">AS6C6264-55PIN</a>  | 8k x 8       | 2.7-5.5V  | 28pin 600mil PDIP         | Industrial ~<br>-40°C to 85° C | 55       |
| <a href="#">AS6C6264-55SCN</a>  | 8k x 8       | 2.7-5.5V  | 28pin 330mil SOP          | Commercial ~<br>0° C to 70° C  | 55       |
| <a href="#">AS6C6264-55SIN</a>  | 8k x 8       | 2.7-5.5V  | 28pin 330mil SOP          | Industrial ~<br>-40°C to 85° C | 55       |
| <a href="#">AS6C6264-55STCN</a> | 8k x 8       | 2.7-5.5V  | 28pin sTSOP (8 x 13.4 mm) | Commercial ~<br>0° C to 70° C  | 55       |
| <a href="#">AS6C6264-55STIN</a> | 8k x 8       | 2.7-5.5V  | 28pin sTSOP (8 x 13.4 mm) | Industrial ~<br>-40°C to 85° C | 55       |

#### Part numbering system

| AS6C                  | 6264                                  | - 55        | X   | X   | N                                 |
|-----------------------|---------------------------------------|-------------|---|---|-----------------------------------|
| low power SRAM prefix | Device Number<br><a href="#">6264</a> | Access Time | Package Options:<br>P = 28 pin 600 mil P-DIP<br>S = 28 pin 330 mil SOP<br>ST = 28 pin sTSOP (8mm x 13.4 mm) | Temperature Range:<br>C = Commercial (0°C to +70° C)<br>I = Industrial (-40° to +85° C) | N = Lead Free ROHS Compliant Part |



Alliance Memory, Inc.  
511 Taylor Way,  
San Carlos, CA 94070, USA  
Tel: +1 650 610 6800  
Fax: +1 650 620 9211  
[www.alliancememory.com](http://www.alliancememory.com)

Copyright © Alliance Memory  
All Rights Reserved  
Part Number: AS6C6264  
Document Version: v. 2.0

© Copyright 2003 Alliance Memory, Inc. All rights reserved. Our three-point logo, our name and Intelliwatt are trademarks or registered trademarks of Alliance. All other brand and product names may be the trademarks of their respective companies. Alliance reserves the right to make changes to this document and its products at any time without notice. Alliance assumes no responsibility for any errors that may appear in this document. The data contained herein represents Alliance's best data and/or estimates at the time of issuance. Alliance reserves the right to change or correct this data at any time, without notice. If the product described herein is under development, significant changes to these specifications are possible. The information in this product data sheet is intended to be general descriptive information for potential customers and users, and is not intended to operate as, or provide, any guarantee or warrantee to any user or customer. Alliance does not assume any responsibility or liability arising out of the application or use of any product described herein, and disclaims any express or implied warranties related to the sale and/or use of Alliance products including liability or warranties related to fitness for a particular purpose, merchantability, or infringement of any intellectual property rights, except as express agreed to in Alliance's Terms and Conditions of Sale (which are available from Alliance). All sales of Alliance products are made exclusively according to Alliance's Terms and Conditions of Sale. The purchase of products from Alliance does not convey a license under any patent rights, copyrights, mask works rights, trademarks, or any other intellectual property rights of Alliance or third parties. Alliance does not authorize its products for use as critical components in life-supporting systems where a malfunction or failure may reasonably be expected to result in significant injury to the user, and the inclusion of Alliance products in such life-supporting systems implies that the manufacturer assumes all risk of such use and agrees to indemnify Alliance against all claims arising from such use.