




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A6	REVISED PER ECO-13-005565	30MAR13	KH	JO

- | | | |
|---|--|----|
| 1 | HOUSING: GLASS FILLED POLYESTER, PCT, COLOR: BLACK | |
| 2 | CONTACT: PHOSPHOR BRONZE | |
| 3 | CONTACT FINISH: 3.81-7.62 (.000150-.000300) MATTE TIN ALL OVER
0.00127(.000050) MIN NICKEL ENTIRE CONTACT | |
| 4 | MOLDED IN ARROW DESIGNATES MATING FACE OF CONNECTOR | |
| 5 | DIMENSIONS PERTAINS TO CAVITY CENTERLINES | |
| 6 | DATUMS AND BASIC DIMENSIONS ARE ESTABLISHED BY
THE CUSTOMER | 11 |
| 7 | PRE-PRODUCTION-PRELIMINARY PARTS | 12 |
| 8 | NO PART NUMBER MARKING REQUIRED FOR THIS PART | |
| 9 | ROHS 2002/95/EC COMPLIANT | |

- TE LOGO AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION.
- MARK PART NUMBER AND DATE CODE IN APPROXIMATE LOCATION SHOWN, EITHER END



SECTION X-X



RECOMMENDED PC BOARD LAYOUT

$\frac{7}{7}$	165.10[6.500]	65	6-5147733-4
$\frac{7}{7}$	162.56[6.400]	64	6-5147733-3
$\frac{7}{7}$	160.02[6.300]	63	6-5147733-2
$\frac{7}{7}$	157.48[6.200]	62	6-5147733-1
$\frac{7}{7}$	152.94[6.100]	61	6-5147733-0
$\frac{7}{7}$	152.40[6.000]	60	5-5147733-9
$\frac{7}{7}$	149.86[5.900]	59	5-5147733-8
$\frac{7}{7}$	147.32[5.800]	58	5-5147733-7
$\frac{7}{7}$	144.78[5.700]	57	5-5147733-6
$\frac{7}{7}$	147.32[5.600]	56	5-5147733-5
$\frac{7}{7}$	139.70[5.500]	55	5-5147733-4
$\frac{7}{7}$	137.16[5.400]	54	5-5147733-3
$\frac{7}{7}$	134.62[5.300]	53	5-5147733-2
$\frac{7}{7}$	132.08[5.200]	52	5-5147733-1
$\frac{7}{7}$	129.54[5.100]	51	5-5147733-0
$\frac{7}{7}$	127.00[5.000]	50	4-5147733-9
$\frac{7}{7}$	124.46[4.900]	49	4-5147733-8
$\frac{7}{7}$	121.92[4.800]	48	4-5147733-7
$\frac{7}{7}$	119.38[4.700]	47	4-5147733-6
$\frac{7}{7}$	116.84[4.600]	46	4-5147733-5
$\frac{7}{7}$	114.30[4.500]	45	4-5147733-4
$\frac{7}{7}$	111.76[4.400]	44	4-5147733-3
$\frac{7}{7}$	109.22[4.300]	43	4-5147733-2
$\frac{7}{7}$	106.68[4.200]	42	4-5147733-1
$\frac{7}{7}$	104.14[4.100]	41	4-5147733-0

	101.60[4.000]	40	3-5147733-9
	99.06[3.900]	39	3-5147733-8
	96.52[3.800]	38	3-5147733-7
	93.98[3.700]	37	3-5147733-6
	91.44[3.600]	36	3-5147733-5
	88.90[3.500]	35	3-5147733-4
	86.36[3.400]	34	3-5147733-3
	83.82[3.300]	33	3-5147733-2
	81.28[3.200]	32	3-5147733-1
	78.74[3.100]	31	3-5147733-0
	76.20[3.000]	30	2-5147733-9
	73.66[2.900]	29	2-5147733-8
	71.12[2.800]	28	2-5147733-7
	68.58[2.700]	27	2-5147733-6
	66.04[2.600]	26	2-5147733-5
	63.50[2.500]	25	2-5147733-4
	60.96[2.400]	24	2-5147733-3
	58.42[2.300]	23	2-5147733-2
	55.88[2.200]	22	2-5147733-1
	53.34[2.100]	21	2-5147733-0
	50.80[2.000]	20	1-5147733-9
	48.26[1.900]	19	1-5147733-8
	45.72[1.800]	18	1-5147733-7
	43.18[1.700]	17	1-5147733-6
	40.64[1.600]	16	1-5147733-5
	38.10[1.500]	15	1-5147733-4
	35.56[1.400]	14	1-5147733-3
	33.02[1.300]	13	1-5147733-2
	30.48[1.200]	12	1-5147733-1
	27.94[1.100]	11	1-5147733-0
	25.40[1.000]	10	5147733-9
	22.86[.900]	9	5147733-8
	20.32[.800]	8	5147733-7
	17.78[.700]	7	5147733-6
	15.24[.600]	6	5147733-5
8	10.16[.500]	5	5147733-4
8	10.16[.400]	4	5147733-3
8	7.62[.300]	3	5147733-2
8	5.08[.200]	2	5147733-1

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN BSV		10NOV04		 TE Connectivity												
			CHK —		—														
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME		AMPMODU MODII RECPT. ASSY., HORZ., SURFACE MOUNT, .100CL, 1 ROW CLOSED ENTRY, END STACK											
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		PRODUCT SPEC —															
MATERIAL		FINISH		APPLICATION SPEC —		SIZE					CAGE CODE		DRAWING NO		RESTRICTED TO				
 				WEIGHT —		A2		00779		C-5147733		—							
CUSTOMER DRAWING								SCALE		5:1		SHEET		1 of 1		REV		A6	