






No. of pos.	A	B
1	3.90	-
2	6.44	2.54
3	8.98	5.08
4	11.52	7.62
5	14.06	10.16
6	16.60	12.70
7	19.14	15.24
8	21.68	17.78
9	24.22	20.32
10	26.76	22.86
12	31.84	27.94

DATE CODE

First digit:
last digit of the year

Second digit:

- 1 January
- 2 February
- 3 March
- 4 April
- 5 May
- 6 June
- 7 July
- 8 August
- 9 September
- X October
- Y November
- Z December

SCHEMATIC




(2, 3, 4, 5, 6, 7, 8, 9, 10, 12, POS AVAIL)

Specifications:

Contact rating:	100mA, 50V DC
Contact resistance:	50mOhm max.
Insulation resistance:	100MOhm min. at 500V DC
Dielectric strength:	500V AC for 1 minute
Operating temperature:	-40°C to +85°C
Storage temperature:	-40°C to +85°C
Mechanical life:	10 000 cycles per switch
Electrical life:	5 000 cycles per switch 25mA, 24V DC
Operating force:	1 000gf max.
Soldering conditions:	wave-soldering: 260°C, max. 5sec.
Stroke:	2.0mm
Material:	Actuator: UL94V-0 high-thermoplastic; white Contacts / terminals: phosphor bronze, 0.2µm gold plated over 1µm nickel Case: PBT, UL94V-0, black Potting material: epoxy

P.C.B. LAYOUT




Tolerances: ±0.20mm			Date	Name	DSS 200 N	
			04/09	dr		
Operat. temperature	11/09	dr			30 17 74	
Mechan., elect. life	11/09	dr				
Print	08/09	dr				
Plating	05/09	dr				
Modifications	Date	Name				Page
						1/2



knitter-switch

Packaging:

DSS 201 N - DSS 203 N:



DSS 204 N - DSS 212 N:



Pole	Quantity per tube
1	126
2	72
3	51
4	40
5	32
6	27
7	24
8	21
9	19
10	17
12	14



Tolerances: ±0.20mm			Date	Name	DSS 200 N	
			04/09	dr		
					30 17 74	
Modifications			Date	Name	Page	
					2/2	