



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H5	REVISED PER ECO-16-011163	08SEP2016	DD	AH
	H6	REVISED PER ECO-17-014752	11OCT2017	JMS	AH




- 1 0.00076 MINIMUM THICK GOLD PLATE OVER 0.0013 MINIMUM NICKEL PLATE.
- 2 0.0008 MINIMUM THICK PRE-TIN.
- 3 0.75 x 0.75 DIE IDENTIFICATION MARK.


SECTION A-A



SECTION B-B



SECTION C-C



	1.2 - 2.7	AVS 0.5 - 2.0mm (#20 -#14 AWG) ²	184030-3
	1.2 - 2.7	AVS 0.5 - 2.0mm (#20 -#14 AWG) ²	184030-1
FINISH	INSULATION DIA	WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KD LYTLE	7/07/94			TE Connectivity						
		CHK JP KUNKLE	7/26/94									
DIMENSIONS: mm		APVD JP KUNKLE	7/26/94	NAME CONTACT, RECEPTACLE, .070 TYPE -								
		PRODUCT SPEC										
		-										
		APPLICATION SPEC										
		-		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO				
MATERIAL PHOS BRZ (0.3 THK)		FINISH - -		WEIGHT -		A2 00779		C=184030		-		
CUSTOMER DRAWING				SCALE		10:1		SHEET	1 OF 1		REV	H6