


## S505H

5 mm x 20 mm 400 Vdc/500-600 Vac time-delay fuses



### Product features

- 400 Vdc/500-600 Vac rating
- Time-delay, high breaking capacity
- 5 mm x 20 mm physical size
- Ceramic tube with plated end cap construction
- Designed to IEC 60127-2, Standard, Sheet 5
- RoHS Compliant, lead free and halogen free
- Optional axial leads available

Electrical Characteristics								
Amps	1.5I <sub>n</sub>	2.1I <sub>n</sub>	2.75I <sub>n</sub>		4I <sub>n</sub>		10I <sub>n</sub>	
	Min min.	Max min.	Min ms	Max s	Min ms	Max s	Min ms	Max ms
<1A	>60	<30	>250	<80	>50	<5	>5	<150
1A-3.15A	>60	<30	>750	<80	>95	<5	>10	<150
4A-6.3A	>60	<30	>750	<80	>150	<5	>10	<150
8A-10A	>30	<30	>750	<80	>150	<5	>10	<150

### Specifications

Catalog Number	Voltage Rating Vac	Max. Voltage Rating		Interrupting Rating (A) Under			Typical DC Cold Resistance Ω <sup>3</sup>	Typical Voltage Drop (mV) <sup>4</sup>	Typical Value I <sup>2</sup> t (A <sup>2</sup> s) <sup>5</sup>	Agency Approvals				
										250Vac			PSE/JET	cURus <sup>7</sup>
		AC	DC	250 Vac	Max Volts	400 Vdc				TUV	CQC	CCC		
S505H-500-R	250	600	400	1500	100	1500	0.507	295	0.188					x
S505H-800-R	250	600	400	1500	100	1500	0.237	189	0.632					x
S505H-1-R	250	600	400	1500	100	1500	0.14	153	1.28				X	x
S505H-1.25-R	250	600	400	1500	100	1500	0.108	150	2.22				X	x
S505H-1.6-R	250	600	400	1500	100	1500	0.07	125	6.78				X	x
S505H-2-R	250	600	400	1500	100	1500	0.055	128	11.44	X		X	X	x
S505H-2.5-R	250	600	400	1500	100	1500	0.04	126	24.23	X		X	X	x
S505H-3.15-R	250	600	400	1500	100	1500	0.031	121	43.55	X		X	X	x
S505H-4-R	250	600	400	1500	100	1500	0.019	90	38.45	X		X	X	x
S505H-5-R	250	600	400	1500	100	1500	0.015	89	71.3	X		X	X	x
S505H-6.3-R	250	500	400	1500	100	1500	0.011	80	111.4	X		X	X	x
S505H-8-R	250	500	400	1500	100	1500	0.007	76	228.2	X	X		X	x
S505H-10-R	250	500	400	1500	100	1500	0.006	72	349.5	X	X		X	x

1. Max. Voltage rating: Base on the breaking capacity test according to UL.
2. - Breaking Capacity of 250 VAC/1500 A is tested by all agency approvals, test condition is 250 Vac, PF: 0.7-0.8.  
- Breaking Capacity of Max. voltage is tested by UL, PF:1.  
- Breaking Capacity Test of DC is tested by UL under Capacitor Bank 4800 mF (for 400 V, 1500 A), 2400 mF (for 400 V, 500 A).

3. Cold Resistance: Measure at <10% rated current.
4. Typical Voltage Drop: Voltage drop is measured under ambient 20 °C with rated current
5. Typical Pre-Arc I<sup>2</sup>t: Measured at 10In DC
6. Does not apply to axial leaded versions.
7. 600/500 Vac, 400 Vdc.

### Applications

- Power supplies - adapters
- Desktops/notebooks
- TVs / Displays
- Set top boxes
- Lighting ballasts
- Battery chargers
- Printers
- Game systems
- Air conditioners

### Agency information

#### S505H-XXX-R (Ferrule)

- cURus approval: Guide JFHR2, File E56412 and Guide JFHR8, File E56412
- CCC: 2A-4A, Cert. No.: 2010010207395946; 5A-6.3A Cert. No.: 2010010207390567
- CQC Approval: 8A-10A, Cert. No.: CQC10012043350
- TUV Approval: 2A-10A, Cert. No.: R50172128
- PSE Approval: 1A-5A, Cert. No.: JET1641-31003-1009; 6.3A-10A, Cert. No: JET1641-31003-1011


#### S505H-V-XXX-R (Axial Leads)

- PSE Approval: 1A-5A, Cert. No.: JET1641-31003-1010; 6.3A-10A, Cert. No: JET1641-31003-1012
- cURus approval: Guide JFHR2, File E56412 and Guide JFHR8, File E56412




Powering Business Worldwide

Dimensions - mm




A (ref): 0.65 mm (0.5 A - 6.3 A), 0.80 mm (8 A-10 A)


Time-Current Curves




Construction



500-800mA




1-1.6 Amps



2 Amps & Above

- 1. Ceramic Tube
- 2. Wire Fuse Element
- 3. Plated Fuse Cap
- 4. Filler
- 5. Solder
- 6. Eyelet




Axial Leaded Versions

- 1. S505H-XXX-R
- 2. Axial Leaded Cap

Wave Soldering Parameters

Note: These devices are NOT recommended for IR or convection reflow processes.



- Reservoir Temperature: 260°C ± 3°C
- Soldering Time: 10 seconds max.


Recommended Hand Solder Parameters

- Soldering Iron Tip Temperature: 350°C ± 5°C
- Heating Time: 5 seconds max.

Operating Temperature Range

- -40°C to +85°C (see temperature derating curve below for percentage of fuse rating per ambient temperature)

Temperature Derating Curve



Packaging Code	
Packaging Code Prefix	Description
BK-	100 fuses packed into a cardboard carton with flaps folded
BK1-	1000 fuses packed into a poly bag
TR2-	1500 axial leaded fuses on tape and reel
Option Code	
Option Code	Description
-V	Axial leads – copper tinned wire with nickel plated brass end caps
-R	RoHS compliant version

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton  
Electronics Division  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
[www.eaton.com/electronics](http://www.eaton.com/electronics)

© 2017 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 4406 BU-SB11276  
June 2017