



DRAWING MADE IN THIRD ANGLE PROJECTION

© COPYRIGHT 1983 AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U.S. PATENTS AND/OR PATENTS PENDING.

LOC DIST
R 39


REVISIONS					DATE	APPROVED
P	F	ZONE	LTR	DESCRIPTION		
✓	✓	Q		RELEASED WAS 5098-25	10-4-83	DE [Signature]
✓	✓	A		REV. PER ECN R-1387	8-6-85	MPH [Signature]
✓	✓	B		REV. PER ECN R-2586	1-14-87	RL [Signature]
✓	✓	C		OBSOLETE -4, -5, & -6 / ECN R-2520	1-21-87	MPH [Signature]




- 66750 -2 1. AS SHOWN
- 3 1. SAME AS -2 EXCEPT:
2. LOOSE PIECE
- OBSOLETE** 1. SAME AS -2 EXCEPT:
2. REVERSE REEL
- OBSOLETE** 1. SAME AS -2 EXCEPT
- OBSOLETE** 1. SAME AS -5 EXCEPT:
2. LOOSE PIECE

PLATING THICKNESS MEASUREMENT POINT

- SELECTIVELY PLATE GOLD PER MIL-G-45204 OVER NICKEL PER QQ-N-290.
- SELECTIVELY PLATE .000050 GOLD PER MIL-G-45204 OVER NICKEL PER QQ-N-290.
3. STOCK THICKNESS: .0126+.0005
4. MAX INSULATION DIA.: .049 WHEN CONTACT IS LOADED IN STANDARD CR SERIES CAVITY.



SECTION B-B



SECTION A-A

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.		CONTRACT NO.		PART NO.	
TOLERANCES ON: DECIMALS ± .005 ANGLES ±		DR EQ Engraved 6-30-80		AMP INCORPORATED Harrisburg, Pa.	
MATERIAL COPPER-ALLOY PER QQ-B-750		CHK 10-18-83 APPROD 10/18/83		NAME CR ACTIVE CONTACT	
FINISH SEE DASH NO'S.		APPR 10/21/83		24-20 AWG WIRE RANGE	
		DSGN APPR		SIZE CODE IDENT NO DRAWING NO	
		OTHER APPR		C 00779 66750	
				SCALE NTS SHEET 1 OF 1	