



Panel Mount, Shocksafe 5x20mm / 6.3x32mm Fuses

IEC 60127-6
UL 512
CSA C22.2, No.39

VDE Report
SEMKO
UL Recognized
CSA Certified
SEV



Panel alternatives



12.7mm diameter D-hole or double D-hole
Admissible torque on plastic hex nut is 1.2Nm

Solderable or 4.8mm quick connect-fits 0.5mm tab

IP 40 (IEC 60529)
PC2 (IEC 60127-6)

Holder/Cap: Black Thermoplastic, UL 94V0
Metal Parts: Copper alloy, corrosion protected
Terminals: Solderable, tinned

Electrical Data (25 °C)
Rated Voltage: 250V
Rated Current: 10A (VDE/SEMKO)
 16A (CSA)
 20A (UL)
Rated Power : 4.0W (VDE/SEMKO)

-40°C to +85°C (consider de-rating)

-40°C/+85°C/21 days (IEC 60068-2-1...3)

+10°C to +60°C
relative humidity ≤ 75% yearly average,
without dew, maximum value for 30 days - 95%

24 cycles at 15 min. each (IEC 60068-2-6)
10 - 60Hz at 0.75mm amplitude
60 - 500Hz at 10g acceleration

 $\leq 5\text{m}\Omega$

4 kV, 50 Hz, 1 min., dry

 $> 10^3 \text{ M}\Omega$ (500 VDC, 1 min.)

235°C, 2 sec. (Wave)
350°C, 1 sec. (Soldering Iron)

350°C, 5 sec. (IEC 60068-2-20)

Conductor - 2.5mm²


860, 250V, Approvals

5.3q (860) / 3.3q (865) / 2.5q (866)

Cap / No. 865




For 5x20mm Fuses



Cap / No. 866



For 6.3x32mm Fuses



Order Information

Bulk (100 pcs.)

Holder	No. 860 0000 100
Cap, 5x20mm	No. 865 0000 100
Cap, 6.3x32mm	No. 866 0000 100

Note: 1.00 means the number one with two decimal places. 1,000 means the number one thousand.



Specifications are subject to change without notice

In our continuing strategy to deliver unparalleled circuit protection solutions, technical expertise and application leadership, we proudly introduce the **WICKMANN Group** and its products to the Littelfuse portfolio.