



LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN APVD
			A	ECO-06-009997	02MAY2006	RB NE
			A1	REVISED PER ECO-09-024927	09NOV09	KK AEG



- THIS POST IS NOT COMPATIBLE WITH TERMI-POINT APPLICATIONS.
- POINT OF MEASUREMENT FOR PLATING THICKNESS.
- .000100-.000200 MATTE TIN OVER .000030 NICKEL.
- ROHS 2002/95/EC COMPLIANT.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	OBSOLETE	.573	.125	.400		2-5086182-5
		.715	.187	.480		2-5086182-2
		.998	.150	.800		1-5086182-0
		.748	.320	.380		5086182-9
		.595	.187	.360		5086182-2
		.800	.187	.565		5086182-1

C	B	A	FINISH	PART NUMBER
---	---	---	--------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R BROWN 02MAY2006		 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
			CHK N EPPLEY 02MAY2006					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		APVD N EPPLEY 02MAY2006		NAME CONTACT, MALE, MOD I LOOSE PIECE .031X.062 -		
	PRODUCT SPEC -							
	APPLICATION SPEC -							
	WEIGHT -							
	MATERIAL BRASS			FINISH NOTE 3		SIZE A2	CAGE CODE 00779	DRAWING NO C=5086182
CUSTOMER DRAWING					SCALE 4:1	SHEET 1 of 1	REV A1	