




| Part Number | Forced Convection Thermal Resistance °C/W at 150.0mm length | Natural Convection Thermal Resistance °C/W at 150.0mm length | Width mm | Height mm | Surface Area mm/m | Weight kg/m |
|-------------|---|--|----------|-----------|-------------------|-------------|
| OS533 | 1.68 | 4.13 | 22.00 | 28.50 | 200.0 | 0.48 |



Notes

Thermal resistance – Natural Convection, part length = 150mm

Thermal resistance – Forced convection. Airspeed in inlet tunnel = 2m/s

Figures are for Black anodised or Unfinished parts

Ambient T = 25C

Heat sink T =100C

Non Standard Extrusions

Aavid Thermalloy has over 10,000 extrusion profile designs on file, most with the extrusion die already available. These parts have minimum order requirements and longer lead times, but may be cost effective compared to a new design.

Customizing & Advanced Capabilities

We offer several options for those applications which require a more unique solution. Challenge us with your thermal requirements - we can design custom solutions.