




<div>MICRO SWITCH</div> <div>a Honeywell Division</div> <div>FED. MFG. CODE 91929</div>	ASSEMBLY - TOGGLE SWITCH	CATALOG LISTING 66AT315 SERIES CHART 1	CATALOG LISTING	KEYWAY POSITION		CENTER POSITION		OPPOSITE KEYWAY POSITION	
				C-NC	C-NO	C-NO	C-NC	C-NC	C-NO
			66AT315-1	1, 2, 3	4, 5, 6	NONE	ALL	4, 5, 6	1, 2, 3
			66AT315-3	1, 2, 3	4, 5, 6	NONE	NONE	4, 5, 6	1, 2, 3
			66AT315-5	1, 2, 3*	4, 5, 6*	NONE	ALL	4, 5, 6	1, 2, 3
			66AT315-7	1, 2, 3*	4, 5, 6*	NONE	ALL	4, 5, 6*	1, 2, 3*
			* ASTERISK DENOTES MOMENTARY POSITION						



CORROSION RESISTANT LEVER  
BUSHING AND BRACKET 4



- NOTES
- 1 - UNIT INCLUDES 6X "SX" TYPE BASIC SWITCH (MEETS REQUIREMENTS OF MIL-S-8805/4)
  - 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
  - 3 - TERMINALS ARE PLATED FOR SOLDERING
  - 4 DULL FINISH ON LEVER AND BUSHING
  - 5 SWITCH NUMBERS STAMPED ON END OF BASIC SWITCHES
  - 6 TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNT
  - 7 - WHEN LEVER IS MOVED OUT OF A MAINTAINED POSITION, IT WILL RETURN OF ITS OWN ACCORD TO THE ORIGINAL POSITION OF THE ADJACENT POSITION. THE TOGGLE LEVER MAY HANG UP BETWEEN THE TWO ADJACENT POSITIONS ONLY BY EXERTING CONSIDERABLE EFFORT
  - 8 FOR PANEL SEAL TO BE EFFECTIVE MOUNTING HOLE IN PANEL SHOULD NOT EXCEED Ø.500

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION	
CHARACTERISTICS	ELECTRICAL DATA		SCALE FULL
	CONTACT ARRANGEMENT		DO NOT SCALE PRINT
	6X S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
	L22 1A 125 VAC		ONE PLACE (.0) ±.030
			TWO PLACE (.00) ±.015
			THREE PLACE (.000) ±.005
			ANGLES ±
			WEIGHT .08 LB EST



ANSI Y14.5M-1982 APPLIES

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[66AT315-1](#)