



N-Channel Enhancement-Mode Vertical DMOS FETs

Ordering Information

$BV_{DSS} /$ BV_{DGS}	$R_{DS(ON)}$ (max)	$I_{D(ON)}$ (min)	Order Number / Package
			TO-92
60V	7.5Ω	500mA	2N7008

Features

- ☐ Free from secondary breakdown
- ☐ Low power drive requirement
- ☐ Ease of paralleling
- ☐ Low C_{ISS} and fast switching speeds
- ☐ Excellent thermal stability
- ☐ Integral Source-Drain diode
- ☐ High input impedance and high gain
- ☐ Complementary N- and P-channel devices

Applications

- ☐ Motor controls
- ☐ Converters
- ☐ Amplifiers
- ☐ Switches
- ☐ Power supply circuits
- ☐ Drivers (relays, hammers, solenoids, lamps, memories, displays, bipolar transistors, etc.)

Absolute Maximum Ratings

Drain-to-Source Voltage	BV_{DSS}
Drain-to-Gate Voltage	BV_{DGS}
Gate-to-Source Voltage	± 30V
Operating and Storage Temperature	-55°C to +150°C
Soldering Temperature*	300°C


* Distance of 1.6 mm from case for 10 seconds.

Advanced DMOS Technology

These enhancement-mode (normally-off) transistors utilize a vertical DMOS structure and Supertex's well-proven silicon-gate manufacturing process. This combination produces devices with the power handling capabilities of bipolar transistors and with the high input impedance and positive temperature coefficient inherent in MOS devices. Characteristic of all MOS structures, these devices are free from thermal runaway and thermally-induced secondary breakdown.

Supertex's vertical DMOS FETs are ideally suited to a wide range of switching and amplifying applications where high breakdown voltage, high input impedance, low input capacitance, and fast switching speeds are desired.

Package Option



Note: See Package Outline section for dimensions.

Thermal Characteristics

Package	I_D (continuous)*	I_D (pulsed)	Power Dissipation @ $T_C = 25^\circ\text{C}$	θ_{JC} $^\circ\text{C/W}$	θ_{JA} $^\circ\text{C/W}$	I_{DR}^*	I_{DRM}
TO-92	230mA	1.3A	1W	125	170	230mA	1.3A

* I_D (continuous) is limited by max rated T_J .


Electrical Characteristics (@ 25°C unless otherwise specified)

Symbol	Parameter	Min	Typ	Max	Unit	Conditions
BV_{DSS}	Drain-to-Source Breakdown Voltage	60			V	$I_D = -10\mu\text{A}$, $V_{GS} = 0\text{V}$
$V_{GS(th)}$	Gate Threshold Voltage	1		2.5	V	$V_{GS} = V_{DS}$, $I_D = 250\mu\text{A}$
I_{GSS}	Gate Body Leakage			100	nA	$V_{GS} = \pm 30\text{V}$, $V_{DS} = 0\text{V}$
I_{DSS}	Zero Gate Voltage Drain Current			1	μA	$V_{GS} = 0\text{V}$, $V_{DS} = 50\text{V}$
				500	μA	$V_{GS} = 0\text{V}$, $V_{DS} = 50\text{V}$ $T_A = 125^\circ\text{C}$
$I_{D(ON)}$	ON-State Drain Current	500			mA	$V_{GS} = 10\text{V}$, $V_{DS} \geq 2V_{DS(ON)}$
$R_{DS(ON)}$	Static Drain-to-Source ON-State Resistance			7.5	Ω	$V_{GS} = 5\text{V}$, $I_D = 50\text{mA}$
				7.5		$V_{GS} = 10\text{V}$, $I_D = 500\text{mA}$
G_{FS}	Forward Transconductance	80			mS	$V_{DS} = 10\text{V}$, $I_D = 0.2\text{A}$
C_{ISS}	Input Capacitance			50	pF	$V_{GS} = 0\text{V}$, $V_{DS} = 25\text{V}$ $f = 1\text{MHz}$
C_{OSS}	Common Source Output Capacitance			25		
C_{RSS}	Reverse Transfer Capacitance			5		
$t_{(ON)}$	Turn-ON Time			20	ns	$V_{DD} = 30\text{V}$, $I_D = 200\text{mA}$, $R_{GEN} = 25\Omega$
$t_{(OFF)}$	Turn-OFF Time			20		
V_{SD}	Diode Forward Voltage Drop			1.5	V	$I_{SD} = 150\text{mA}$, $V_{GS} = 0\text{V}$

Notes:

1. All D.C. parameters 100% tested at 25°C unless otherwise stated. (Pulse test: $300\mu\text{s}$ pulse, 2% duty cycle.)
2. All A.C. parameters sample tested.

Switching Waveforms and Test Circuit



01/06/03

Supertex inc.

©2003 Supertex Inc. All rights reserved. Unauthorized use or reproduction prohibited.

1235 Bordeaux Drive, Sunnyvale, CA 94089
TEL: (408) 744-0100 • FAX: (408) 222-4895
www.supertex.com