

# Endicott Research Group, Inc. 2601 Wayne St., Endicott, NY 13760

607-754-9187 Fax 607-754-9255 http://www.ergpower.com

### DMAD3015F



### Specifications and Applications Information


12/22/10

The ERG DMAD3015F (DMA Series) DC to AC inverter features onboard connectors and can be easily dimmed using the onboard PWM Dimming or an external PWM generator.

Powered by a regulated +12 Volt DC source, the DMAD3015F is designed to power the backlight of the Sharp LQ104V1DG51 display.

#### **Product Features**


- ✓ Small Package Size, less than 13mm in height
- ✓ High Dimming Ratio
- ✓ High Efficiency
- ✓ Made in U.S.A.



Actual product may differ from that shown.

Connectors Output Input JST SM02(8.0)B-BHS-1-TB Molex 53261-0871

### Two Lamp DC to AC Inverter





## DMAD3015F



#### **Absolute Maximum Ratings**

Rating	Symbol	Value	Units	
Input Voltage Range	V <sub>in</sub>	-0.3 to +13.2	Vdc	
Storage Temperature	T <sub>stg</sub>	-40 to +85	°C	

#### **Operating Characteristics**

With a load simulating the referenced display and lamp warm-up of 5 minutes. Unless otherwise noted Vin = 12.00 Volts dc and  $Ta = 25^{\circ}\text{C}$ .

Characteristic	Symbol	Min	Тур	Max	Units		
Input Voltage	V <sub>in</sub>	+10.8	+12.0	+12.6	Vdc		
Component Surface Temperature (note 1)	Ts	-20	-	+80	°C		
Input Current (note 2)	I in	-	0.64	0.74	Adc		
Operating Frequency	F <sub>o</sub>	41	46	51	kHz		
Minimum Output Voltage (note 3)	V <sub>out</sub> (min)	1450	1	-	Vrms		
Efficiency	η	-	73	-	%		
Output Current (per lamp)	I out	-	6.0	-	mArms		
Output Voltage	V <sub>out</sub>	-	467	-	Vrms		
Enable Pin							
Turn-off Threshold	V thoff	GND	-	0.5	Vdc		
Turn-on Threshold	V <sub>thon</sub>	2.5	-	Vin	Vdc		

Specifications subject to change without notice.

- (Note 1) Surface temperature must not exceed 80 degrees C; thermal management actions may be required.
- (Note 2) Input current in excess of maximum may indicate a load/inverter mismatch condition, which can result in reduced reliability. Please contact ERG technical support.
- (Note 3) Provided data is not tested but guaranteed by design.

#### **Application Notes:**

- 1) The minimum distance from high voltage areas of the inverter to any conductive material should be .12 inches per kilovolt of starting voltage.
- 2) Mounting hardware should be non-conductive.
- 3) Open framed inverters should not be used in applications at altitudes over 10,000 feet.
- 4) ACreturn should be left floating, not grounded.
- 5) Contact ERG for possible exceptions.





#### **Onboard PWM**

Unless otherwise noted Vin = 12.00 Volts DC, Ta = 25 °C and unit has been running for 5 minutes.

Characteristic	Symbol	Min	Тур	Max	Units
Frequency	f <sub>pwm</sub>	-	160	-	H <sub>Z</sub>
Control Input Bias Current	I cbias	-	-	10	uA

#### **Pin Descriptions**

Vin Input voltage to the inverter. The two pins should be connected for optimum reliability and efficiency.

**GND** Inverter ground. The two pins should be connected for optimum reliability and efficiency.

Control Analog voltage input to the onboard pulse width modulator. Decreasing this voltage increases the ON

time of the onboard PWM resulting in increased brightness. The inverter is full ON when this voltage is

near inverter ground.

**Enable** Inverter Enable. Pull this pin low to disable inverter operation. This pin must be high to enable the

inverter. The onboard PWM is always utilized.

#### **Application information**

The DMAD series of inverters is designed to power up to two cold cathode fluorescent lamps. An external analog control interfaces with an onboard pulse width modulator to provide dimming control. The DMAD inverter can reliably dim to less than 5% duty cycle.

External shutdown of the inverter is accomplished using the Enable pin. Pulling this pin low (below Vthoff) disables the inverter. Enabling the inverter is accomplished by pulling this pin high (above Vthon).


If analog voltage dimming is required, the analog voltage is applied to the Control pin. Figure 1 shows how to connect the inverter for onboard PWM operation. Graph 1 shows the relationship of PWM duty cycle to input control voltage.

If an external PWM is used, simply connect the Enable pin to the PWM source and connect the Control pin to inverter Ground. If the onboard PWM is used, connect the analog voltage to the Control pin.



## DMAD3015F





#### Typical Application




Figure 1

Note 1 - Low ESR type input by-pass capacitor (47 uf - 150 uf) may be required to reduce reflected ripple.



Endicott Research Group, Inc. (ERG) reserves the right to make changes in circuit design and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by ERG is believed to be accurate and reliable. However, no responsibility is assumed by ERG for its use.