




PRODUCT NUMBER	DIM. A	DIM. B	DIM C WIREWRAP AREA PLATING	DIM D NOTCH LOCATION	DIM E NOTCH DEPTH	
1B-1A-B	.505	.940	None	—	—	
1B-2A-B	.555	.940	None	—	—	NOT AVAILABLE
1B-3A-B	.505	.940	.200	—	—	
1B-4A-B	.555	.940	.200	—	—	
1B-9A-B	.400	.940	.200 Ni	.325±.005	.0045±.0005	
1B-10A-B	.480	.940	.200 Ni	.325±.005	.0045±.0005	
1B-13A-B	.555	.940	.200 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-14A-B	.605	.940	.200	—	—	
1B-15A-B	.505	.940	.200 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-16A-B	.605	.940	.200 Ni	.325±.005	.0045±.0005	
1B-20A-B	.555	.695	.250	—	—	NOT AVAILABLE
1B-21A-B	.505	.695	.250	—	—	NOT AVAILABLE
1B-22A-B	.605	.695	.250	—	—	NOT AVAILABLE
1B-23A-B	.555	.695	None	—	—	NOT AVAILABLE
1B-24A-B	.505	.695	None	—	—	NOT AVAILABLE
1B-25A-B	.605	.695	None	—	—	NOT AVAILABLE
1B-26A-B	.555	.695	.250 Ni	.325±.005	.0045±.0005	
1B-27A-B	.505	.695	.250 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-28A-B	.605	.695	.250 Ni	.325±.005	.0045±.0005	NOT AVAILABLE
1B-29A-B	.555	.695	.250 Ni	.460±.005	.0060±.0005	NOT AVAILABLE
1B-30A-B	.505	.695	.250 Ni	.460±.005	.0060±.0005	NOT AVAILABLE
1B-31A-B	.555	1.085	.330	—	—	
1B-32A-B	.555	.940	.200 Ni	.480±.005	.0060±.0005	
1B-33A-B	.605	.940	.200 Ni	.480±.005	.0060±.0005	NOT AVAILABLE
1B-34A-B	.505	.940	.200 Ni	.480±.005	.0060±.0005	
1D-4A-B	.555	.695	.250	.091±.005	.0045±.0005	NOT AVAILABLE




mat'l. code	SEE NOTE 1	surface	tolerance	projection	product family
ltr	ec'n no	dr	date	tolerances unless otherwise specified	FASTECH
A	v03-0079	HTB	2006-01-16	angles	linear
B	v03-0177	HTB	2003-02-12	linear	linear
C	v06-0486	HTB	2006-05-19	0°±2°	linear
D	v06-0592	HTB	2006-06-16	dr	T. BREWBAKER
E	v08-0400	HTB	2008-09-29	engr	T. BREWBAKER
F	v09-0135	HTB	2009-03-27	chr	T. BREWBAKER
				appd	T. BREWBAKER
sheet index	revision	F	F		
	sheet	1	2		

PRODUCT NUMBER
SEE TABLE

PACKAGING TICKET
PLATED PRODUCT
TCS PART #



OPEN SIDE OF "C" DOWN



DETAIL A

NOTES:

- ① BANDOLIER MATERIAL: C26000, 1/2 HARD, .010 +/- .0005 THICK.
- ② PIN RETENTION IN BANDOLIER: 2 LBS MIN, 5 LBS MAX.
- ③ 1-TYPE CONTACTS MAY BE SLIGHTLY LOOSE IN THE BANDOLIER.
- ④ SHOULDER WIDTH AFTER BODY CARRIER REMOVAL SHALL BE .0685 MAX INCLUDING BURRS.
- ⑤ PIN WIDTH AFTER BODY CARRIER REMOVAL SHALL BE .0285 MAX INCLUDING BURRS.
- ⑥ BANDOLIERED PIN PROGRESSION TOLERANCE: .002" / INCH
- ⑦ BANDOLIERED PIN CAMBER FOR 3 FOOT LENGTH: .25 MAX.
- ⑧ NO SPLICES ARE PERMITTED, NO MORE THAN ONE BREAK PER REEL IS PERMITTED.
- ⑨ SEE CUSTOMER DRAWING A93KC4040 FOR PLATING AND ADDITIONAL PIN INFORMATION.

mat'l. code SEE NOTE 1				surface ✓		tolerance		projection 		product family FASTECH			
ltr	ecm no	dr	date	tolerances unless otherwise specified						title 1-TYPE CONTACT ON BANDOLIER			
F				angles		linear	.XX±.01		 INCH scale N.T.S.				
							.XXX±.003						
				0°±2°			.XXX±.0020						
				dr	T. BREWBAKER	2003-01-16					dwg no 63501 sheet 2 of 2 size A3		
				engr	T. BREWBAKER	2003-01-16							
				chr	T. BREWBAKER	2003-01-16							
				appd	T. BREWBAKER	2003-01-16							
sheet index		revision sheet								type Product Customer Drawing			