

1.0 SCOPE

This specification documents the detail requirements for space qualified product manufactured on Analog Devices, Inc.'s QML certified line per MIL-PRF-38535 Level V except as modified herein. The manufacturing flow described in the STANDARD SPACE LEVEL PRODUCTS PROGRAM brochure is to be considered a part of this specification <http://www.analog.com/aerospace>. This data sheet specifically details the space grade version of this product. A more detailed operational description and a complete data sheet for commercial product grades can be found at www.analog.com/SMP11.

2.0 Part Number. The complete part number(s) of this specification follow:

Part Number	Description
SMP11-803Y	Low Droop Rate/Accurate Sample and Hold

2.1 Case Outline.

Letter	Descriptive designer	Case Outline (Lead Finish per MIL-PRF-38535)
Y	GDIP1-T14	14-Lead ceramic dual-in-line package (CERDIP)




Figure 1 - Terminal connections.

3.0 Absolute Maximum Ratings. ($T_A = 25^\circ\text{C}$, unless otherwise noted)

Supply Voltage.....	$\pm 36\text{V}$
Power Dissipation	500mW
Input Voltage.....	Supply Voltage
Logic and Logic Reference Voltage	Supply Voltage
Output Short-Circuit Duration	Indefinite
Hold Capacitor Short-Circuit Duration	60 sec.
Operating Temperature Range.....	-55°C to $+125^\circ\text{C}$
Storage Temperature Range.....	-65°C to $+150^\circ\text{C}$
DICE Junction Temperature Range (T_J)	$+150^\circ\text{C}$
Lead Temperature (Soldering, 60 sec.).....	$+300^\circ\text{C}$

ASD0010979

Rev. G

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
Tel: 781.329.4700 www.analog.com
Fax: 781.326.8703 © 2011 Analog Devices, Inc. All rights reserved.

3.1 Thermal Characteristics:

Thermal Resistance, CERDIP (Y) Package

Junction-to-Case (Θ_{JC}) = 29°C/W MaxJunction-to-Ambient (Θ_{JA}) = 100 °C/W Max**4.0 Electrical Table:**

Table I						
Parameter See notes at end of table	Symbol	Conditions (Note 1)	Sub-group	Limit Min	Limit Max	Units
Zero Scale Error (Hold mode)	V_{ZS}	$V_{S/H} = 3.5V$ (500 μ S after hold) $V_{IN} = 0V$	1		± 3.0	mV
			2, 3		± 5.5	
Input Bias Current	I_B	$V_{IN} = 0V$	1		± 120	nA
			2, 3		± 280	
Input voltage range or Output Voltage swing	V_{SW}	$R_L = 2.5K\Omega$	1, 2, 3	± 10.5		V
Power Supply Rejection Ratio	PSRR	$V_+ = \pm 9V$ to $\pm 18V$ Sample mode	1	77		dB
			2, 3	72		
Differential logic threshold	V_{TH}		1	0.8	2.0	V
			2, 3	0.6	2.0	
Logic control input current	I_{LC}	$V_{LC} = 0V$	1		-3	μ A
			2, 3		-5	
Supply Current	I_{SY}		1	2	7.0	mA
			2, 3	2	8.4	
Logic input current	$I_{S/H}$	$V_{S/H} = 0.6V$ (Sample mode)	1, 2, 3		-15	μ A
		$V_{S/H} = 5V$ (Hold mode)	1, 2, 3	-1	1	
Droop Rate	$\Delta V_{CH}/\Delta t$		4		500	μ V/mS
			5		5000	
			6		2000	
Leakage (Droop) Current	I_{DR}		4		2.5	nA
			5		25	
			6		10	
Voltage Gain (sample mode)	A_V	$V_{IN} = \pm 10V$, $R_L = 5K\Omega$ or $V_{IN} = \pm 5V$, $R_L = 2.5K\Omega$	4	0.99953		V/V
			5, 6	0.99940		
Hold Capacitor Charging Current	ICH+	$V_{IN} - V_{OUT} + 3V$	4, 5, 6	15		mA
	ICH-	$V_{IN} - V_{OUT} - 3V$	4, 5, 6	-15		
Sample/Hold current ratio	I_{CH}/I_{DR}		1, 2, 3	2×10^6		mA/mA
Slew Rate	SR	$V_{IN} = \pm 10V$, $R_L = 2.5K\Omega$	9	2.5		V/ μ S
Aperture Time	Tap		9 2/		100	nS
Acquisition Time	Taq1	10V step to 0.1%	9		7	μ S
	Taq2	10V step to 0.01%	9		10	
Hold mode settling time	T_{HM}	Settling to 1mV of final value	9		4.5	

TABLE I NOTES:

1 $V_S = \pm 15V$, $C_H = 5000pF$, V_{LC} connected to ground, unless otherwise specified.

2 Subgroup 9 is sample tested.

4.1 **Electrical Test Requirements:**

Table II	
Test Requirements	Subgroups (in accordance with MIL-PRF-38535, Table III)
Interim Electrical Parameters	1
Final Electrical Parameters	1, 2, 3, 4, 5, 6 1/ 2/
Group A Test Requirements	1, 2, 3, 4, 5, 6, 9
Group C end-point electrical parameters	1 2/
Group D end-point electrical parameters	1
Group E end-point electrical parameters	1

TABLE II NOTES:

1/ PDA applies to Subgroup 1 only. No other subgroups are included in PDA.

2/ See table III for delta parameters. Exclude Delta's from PDA.

4.2 **Table III. Burn-in test delta limits:**

Table III				
TEST TITLE	BURN-IN ENDPOINT	LIFETEST ENDPOINT	DELTA LIMIT	UNITS
V_{ZS}	± 3	± 5	± 2	mV
I_E	120	132	± 12	nA
I_{SY}	7	7.7	± 0.7	mA

5.0 **Life Test/Burn-In Circuit:**

5.1 HTRB is not applicable for this drawing.

5.2 Burn-in is per MIL-STD-883 Method 1015 test condition B.

5.3 Steady state life test is per MIL-STD-883 Method 1005.

Rev	Description of Change	Date
A	Initiate	4/28/2008
B	Table III IB from 90nA to 120 nA. Delta IB from 6.5 to 12 nA. Add Delta ISY. Change subgroup 11 to 9. Delete Figs. 2 & 3. Update Table III.	8/1/2001
C	Update web address. Correct typo on Table I, V_{TH} min at temp is 0.6, not .06. Table II, add "exclude delta's from PDA" to note 2.	3/6/2002
D	Update web address.	6/20/2003
E	Update header/footer and add to 1.0 Scope description	2/15/2008
F	Remove range from DICE Junction Temperature (T_J)	4/4/2008
G	Remove obsolete part number and update ASD to ADI standard	12/1/2011