







PRODUCT NUMBER
SEE TABLE



SECTION X-X

DETAIL Z
SCALE 6/1

mat'l. code				surface		tolerance		projection		product family	
				ISO 1302 ✓		ISO 406 ISO 1101		INCH/MM		CLINCHER	
ltr ecn nodr date				tolerances unless otherwise specified						title	
AN	ELX-N-010493	ZK	06/03/12	angles		.XX±.01/0.XX±0.3		scale 3:1		CLINCHER™ RECEPTACLE ASSEMBLY	
AH	V60509	HTB	3/5/96	0°±2°		.XXX±.005/0.XX±0.13				dwg no	
AJ	M05-0087	MHT	6/15/05	dr		T.BREWBAKER		5/17/94		sheet 1 of 7	
AK	M06-0233	AGS	6/12/06	engr		T. HANNA		5/17/94		65801	
AL	M07-0088	MHT	2/06/07	chr		J.MURPHY		5/17/94		A3	
AM	M09-0062	CMR	4/09/09	appd		T. HANNA		5/17/94		type Product Customer Drawing	
sheet revision				AN	AN	AN	AN	AN	AN		
index sheet				1	2	3	4	5	6		

PLATING AVAILABLE


PLATING CODE	TERMINAL	SPRING
1	100u"/2.54u MIN. THICK PURE TIN	10u"/.25u MIN. THICK PURE TIN
2	30u"/.76u MIN. GOLD OR GXT STRIPE IN BOX AREA NOTE 12	3u"/.08u MIN. GOLD OVER 50u"/1.27u MIN. NICKLE

PRODUCT NUMBER

65801-XXXLF


LEAD FREE OPTION
NOTE 9,10NO OF POSITIONS
AND PLATING

BASE PART NUMBER



NOTES:

- MOLDING MAT'L: THERMOPLASTIC, FLAME RETARDANT PER UL 94V-0. COLOR: BLUE.
- TERMINAL MAT'L: 1/2 HARD CuNi ALLOY, UNS-C72500. PLATING: SEE TABULATION AND PLATING TABLE.
- SPRING MAT'L: 1/2 HARD BeCu ALLOY, UNS-C17200. PLATING: SEE TABULATION AND PLATING TABLE.
- LATCH SWINGS CLOSED AFTER TERMINATION MAINTAINING A MAX OVER ALL HEIGHT OF .100/2.54
- LABEL IN THIS AREA P/N AND DATE LOT CODE (WEEK AND YEAR) ON DASH No.-067 AND -167 ONLY.
- KNURL MARK INDICATES FOR USE WITH INK TERMINATION. CONSULT WITH BERG ELECTRONICS TECHNICAL REPRESENTATIVE FOR SPECIFIC APPLICATIONS.
- POSITION NUMBERS INITIATE FROM TRIANGULAR MARK ON HOUSING. SEE TABULATION FOR POSITION No CLOSED AND TERMINAL No ABSENT. FIG A SHOWS POSITION No 2 CLOSED.
- AN EIGHT DIGIT PART NUMBER FOLLOWED BY A "J" INDICATES INVENTORY FOR JAPAN ONLY.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS
- PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

FIG A
NOTE 7

mat'l. code	surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ISO 1101	product family CLINCHER
ltr ecn nodr date	tolerances unless otherwise specified	linea	INCH/MM	title CLINCHER™ RECEPTACLE ASSEMBLY
AN	angles 0°±2'	XXX±.01/0.XX±0.3 XXX±.005/0.XX±0.13 XXX±.0020/0.XX±0.05	scale 3:1	dwg no 65801
	dr T.BREWBAKER 5/17/94	enr T. HANNA 5/17/94	chr J.MURPHY 5/17/94	sheet 2 of 7 size A3
	app T. HANNA 5/17/94			type Product Customer Drawing
sheet index	revision sheet			

FCI
FCIconnect.com
Copyright FCI

PRODUCT NO. NOTE 9	NO. OF	DIM. L	DIM. L	DIM. M	DIM. M	DIM. C	DIM. C	PLATING	TERMINATION	CLOSED POS.	TERMINAL ABSENT
	POSITIONS	ENGLISH	METRIC	ENGLISH	METRIC	ENGLISH	METRIC	CODE	NOTE 6	NOTE 7	NOTE 7
65801-201	16	1.500	38.10	1.790	45.47	1.715	43.56	1	CONVENTIONAL	4	4.5.6
65801-202	5	0.400	10.16	0.690	17.53	0.615	15.62	2	CONVENTIONAL	3	3
65801-203	7	0.600	15.24	0.890	22.61	0.815	20.70	2	CONVENTIONAL	6	1.2.6.7
65801-204	10	0.900	22.86	1.190	30.23	1.115	28.32	1	CONVENTIONAL	4	4
65801-205	6	0.500	12.70	0.790	20.07	0.715	18.16	1	CONVENTIONAL	5	5
65801-206	5	0.400	10.16	0.690	17.53	0.615	15.62	1	CONVENTIONAL	4	4
65801-207	7	0.600	15.24	0.890	22.61	0.815	20.70	2	CONVENTIONAL	N/A	1.2.6.7
65801-208	4	0.300	7.62	0.590	14.99	0.515	13.08	1	CONVENTIONAL	N/A	2.3
65801-209	3	0.200	5.08	0.490	12.45	0.415	10.54	1	CONVENTIONAL	N/A	2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family CLINCHER	
ltr ecn nodr date		tolerances unless otherwise specified		linea		INCH/MM		title CLINCHER™ RECEPTACLE ASSEMBLY	
AN				angles 0°±2°		scale 3:1		dwg no 65801	
				dr T.BREWBAKER 5/17/94				sheet 7 of 7 size A3	
				engr T. HANNA 5/17/94				type Product Customer Drawing	
				chr J.MURPHY 5/17/94					
				appd T. HANNA 5/17/94					
sheet index		revision sheet							