

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

71308-4096

Status:

Active

Description:

2.54mm Pitch C-Grid® Header, Surface Mount, Dual Row, Vertical, 96 Circuits, Tin (Sn) Plating, with 3.30mm PCB Locator Pegs

Documents:

3D Model

Drawing (PDF)

Product Specification PS-71308 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Series

Application

Product Name

UPC

PCB Headers

71308

Board-to-Board, Signal, Wire-to-Board

C-Grid®

822348738946

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Compliant

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

Yes

96

96

Black

25

94V-0

No

None

Phosphor Bronze

Tin

Tin

High Temperature Thermoplastic

7.271/g

2

Vertical

Yes

Yes

Tube

2.54mm

No

No

No

Yes

-40°C to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

Voltage - Maximum

3A

250V

Solder Process Data

Lead-free Process Capability

Process Temperature max. C

Reflow Capable (SMT only)

260

Material Info

Reference - Drawing Numbers




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

71308Series

This document was generated on 07/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

71308-4096