






3M™ Solder Cup D Sub Socket, 8000 Series



POSITION	A	B	C	D
9	[.642] 16.30	[.984] 25.00	[1.213] 30.80	[.756] 19.20
15	[.969] 24.60	[1.311] 33.30	[1.543] 39.20	[1.091] 27.70
25	[1.508] 38.30	[2.248] 57.10	[2.091] 53.10	[1.618] 41.10
37	[2.157] 54.80	[2.500] 63.50	[2.732] 69.40	[2.256] 57.30
50*	[2.055] 52.20	[2.402] 61.00	[2.638] 67.00	[2.169] 55.10

*50 POSITION AVAILABLE IN STANDARD ONLY

PERFORMANCE	
OPERATION VOLTAGE:	250V MAX.
CURRENT:	3A MAX.
INSULATION RESISTANCE:	3000 MOhm MIN @ 500VDC
WITHSTANDING VOLTAGE:	1000 VAC / MIN.
TEMPERATURE RATING:	-55°C to 105°C
CONTACT RESISTANCE:	15 mOhms MAX.



8RXX-X00X

NUMBER OF CONTACTS (SEE TABLE)

PLATING
1 - AU FLASH
2 - 30μ" AU

EMI
N - STANDARD
E - EMI

Unless otherwise noted, references to industry specifications are intended to indicate substantial compliance to the material elements of the specification. Such references should not be construed as a guarantee of compliance to all requirements in a given specification.

3M ELECTRONIC SOLUTIONS DIVISION
INTERCONNET SOLUTIONS
<http://www.3mconnectors.com>



3M IS A TRADEMARK OF 3M COMPANY.
FOR TECHNICAL, SALES OR ORDERING
INFORMATION, CALL 800-225-5373


NOTES

- 1 MATERIAL:
THERMAL PLASTIC UL94V-0
CONTACTS:
COPPER ALLOY
SHELL:
G3141 SPCC OR EQUIVALENT
- 2 PLATING:
50μ" NICKEL UNDERPLATE
1μ" AU WIPING AREA OR
30μ" AU WIPING AREA
100-200μ" TIN (BRIGHT TIN) SOLDER TAIL
- 3 MATES WITH:
BPXX-X00X
- 4 SEE THE REGULATORY INFORMATION
APPENDIX (RIA) IN "RoHS"
COMPLIANCE SECTION OF
WWW.3MCONNECTOR.COM FOR
COMPLIANCE INFORMATION
(RIA E1 & C1 APPLY)

DESIGN REFERENCE		NEXT ASSEMBLY		REV	ECO	ISSUE DATE AND DESCRIPTION		DRFT	CHKD
				DRFT SJS		DATE MAY 18, 2011	MFG	DATE	
				CHKD ARM		DATE MAY 18, 2011	APPL	DATE	
DIVISION		DIVISION CODE		© 3M COPYRIGHT 2013					
DO NOT SCALE DRAWING		SCALE 1		TOLERANCES EXCEPT AS NOTED		3M 3M Center St. Paul, MN 55144 This document and the information it contains are 3M property and may not be reproduced or further distributed without the express permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.			
THIRD ANGLE PROJECTION				INCHES :<					

POSITION	MOUNTING METHOD	A	B	C	D	E	F	G	H	J
9	FRONT	.874[22.2]	.437[11.1]	.984[25.0]	.492[12.5]	.513[13.0]	.257[6.5]	.120[3.1]	.060[1.5]	.083[2.1]
	REAR	.806[20.5]	.403[10.2]	.984[25.0]	.492[12.5]	.449[11.4]	.225[5.7]	.120[3.1]	.060[1.5]	.132[3.4]
15	FRONT	1.202[30.5]	.601[15.3]	1.312[33.3]	.656[16.7]	.513[13.0]	.257[6.5]	.120[3.1]	.060[1.5]	.083[2.1]
	REAR	1.134[28.8]	.567[14.4]	1.312[33.3]	.656[16.7]	.449[11.4]	.225[5.7]	.120[3.1]	.060[1.5]	.132[3.4]
25	FRONT	1.743[44.3]	.872[22.2]	1.852[47.0]	.926[23.5]	.513[13.0]	.257[6.5]	.120[3.1]	.060[1.5]	.083[2.1]
	REAR	1.674[42.5]	.837[21.3]	1.852[47.0]	.926[23.5]	.449[11.4]	.225[5.7]	.120[3.1]	.060[1.5]	.132[3.4]
37	FRONT	2.391[60.7]	1.196[30.4]	2.500[63.5]	1.250[31.8]	.513[13.0]	.257[6.5]	.120[3.1]	.060[1.5]	.083[2.1]
	REAR	2.326[59.1]	1.163[29.5]	2.500[63.5]	1.250[31.8]	.449[11.4]	.225[5.7]	.120[3.1]	.060[1.5]	.132[3.4]
50	FRONT	2.297[58.3]	1.149[29.2]	2.406[61.1]	1.203[30.6]	.623[15.8]	.312[7.9]	.120[3.1]	.060[1.5]	.083[2.1]
	REAR	2.218[56.3]	1.109[28.2]	2.406[61.1]	1.203[30.6]	.555[14.1]	.278[7.1]	.120[3.1]	.060[1.5]	.132[3.4]



C		46292		MAR 28, 2013		SJS		ARM									
B		34516		CORRECT SHELL MATL AUG 29, 2011		SJS		ARM									
A		34511		CHANGE MOHMS TO MOHMS, UPDATE ROHS MAY 18, 2011		SJS		ARM									
				MAY 18, 2011													
DESIGN REFERENCE		NEXT ASSEMBLY		REV		ECO		ISSUE DATE AND DESCRIPTION		DRFT		CHKD					
XREF CODES				DRP		SJS		DATE		MAY 18, 2011		MFG		DATE			
				CHKD		ARM		DATE		MAY 18, 2011		APPRVL		DATE			
DIVISION				DIVISION CODE													
DO NOT SCALE DRAWING		SCALE 1 1		TOLERANCES EXCEPT AS NOTED		3M Center St. Paul, MN 55144		© 3M. COPYR[IGHT] 2013 This document and the information it contains are 3M property and may not be reproduced or further distributed without 3M permission, or used or disclosed other than for 3M authorized purposes. All rights reserved.									
		THIRD ANGLE PROJECTION		INCHES 0 ± .00 ± .002 ± .0000		TITLE		8RXX-X00X D-SUB SOLDER CUP SOCKET TS-2402									
INTERPRET PER ASME Y14.5 - 1994		MILLIMETERS 0 ± .1 ± .00 ± .05 ± .0005				CAGE NUMBER		SIZE		DRAWING NO.		REV.					
MAX SURFACE ROUGHNESS 125 ✓		□ ALL SURFACES ☒ MARKED ONLY		ANGLES ± 1 °		D		78-5100-2402-5		C							
						MODEL		BR		DET		LISTS		YES ☐ NO ☒		SHT 2 OF 2	