





# FEMALE THREADED STANDOFFS



| CHOICE OF:                   |                           |                         |                               |
|------------------------------|---------------------------|-------------------------|-------------------------------|
| Nylon V2: 6/6 UL Rated 94V-2 | Stainless: ASTM A581/A582 | Brass: per ASTM-B16     | Aluminum: ASTM B211           |
| Nylon V0: 6/6 UL Rated 94V-0 |                           | Plating: Zinc ASTM B633 | Plating: Clear Iridite Finish |

| HEX           | HEX               |                   |                    |                |                   | LENGTH       | ROUND          |                   | O.D.          |
|---------------|-------------------|-------------------|--------------------|----------------|-------------------|--------------|----------------|-------------------|---------------|
|               | NYLON V2 CAT. NO. | NYLON V0 CAT. NO. | STAINLESS CAT. NO. | BRASS CAT. NO. | ALUMINUM CAT. NO. |              | BRASS CAT. NO. | ALUMINUM CAT. NO. |               |
| 2-56 THREAD   |                   |                   |                    |                |                   |              |                |                   |               |
| .156<br>(3.9) | —                 | —                 | —                  | 1798A          | 1797A             | .187 (4.7)   | 1802A          | 1801A             | .156<br>(3.9) |
|               | —                 | —                 | —                  | 1798B          | 1797B             | .250 (6.4)   | 1802B          | 1801B             |               |
|               | —                 | —                 | —                  | 1798C          | 1797C             | .312 (7.9)   | 1802C          | 1801C             |               |
|               | —                 | —                 | —                  | 1798D          | 1797D             | .375 (9.5)   | 1802D          | 1801D             |               |
| 4-40 THREAD   |                   |                   |                    |                |                   |              |                |                   |               |
| .187<br>(4.7) | —                 | —                 | —                  | 1450           | 1891              | .250 (6.4)   | 1547           | 2025              | .187<br>(4.7) |
|               | —                 | —                 | —                  | 1803           | 1892              | .375 (9.5)   | 1864           | 2026              |               |
|               | —                 | —                 | —                  | 1656           | 1893              | .500 (12.7)  | 1657           | 2027              |               |
|               | —                 | —                 | —                  | 1804           | 1894              | .625 (15.9)  | 1865           | 2028              |               |
|               | —                 | —                 | —                  | 1656A          | 1895              | .750 (19.1)  | 1657A          | 2029              |               |
|               | —                 | —                 | —                  | 1805           | 1896              | .875 (22.2)  | 1866           | 2030              |               |
| —             | —                 | —                 | 1656B              | 1897           | 1.000 (25.4)      | 1657B        | 2031           |                   |               |
| .250<br>(6.3) | 1902A             | 8440A             | 1921               | 1450A          | 2201              | .250 (6.4)   | 1547A          | 3478              | .250<br>(6.3) |
|               | 1902B             | 8440B             | 1921A              | 1450B          | 2202              | .375 (9.5)   | 1547B          | 3479              |               |
|               | 1902C             | 8440C             | 1921B              | 1450C          | 2203              | .500 (12.7)  | 1547C          | 3480              |               |
|               | 1902F             | 8440D             | —                  | 1829           | 1808              | .625 (15.9)  | 1867           | 1839              |               |
|               | 1902D             | 8440E             | 1921C              | 1450D          | 2204              | .750 (19.1)  | 1547D          | 3481              |               |
|               | 1902G             | 8440F             | —                  | 1830           | 1809              | .875 (22.2)  | 1876           | 1846              |               |
|               | 1902E             | 8440G             | 1921D              | 1450E          | 2205              | 1.000 (25.4) | 1547E          | 3482              |               |
|               | —                 | —                 | 1921E              | 1831           | 2206              | 1.500 (38.1) | 1877           | 3483              |               |
| —             | —                 | 1921F             | 1832               | 2207           | 2.000 (50.8)      | 1878         | 3484           |                   |               |
| 6-32 THREAD   |                   |                   |                    |                |                   |              |                |                   |               |
| .250<br>(6.3) | 1903A             | 8441A             | 1922               | 1451A          | 2208              | .250 (6.4)   | 1548A          | 3485              | .250<br>(6.3) |
|               | 1903B             | 8441B             | 1922A              | 1451B          | 2209              | .375 (9.5)   | 1548B          | 3486              |               |
|               | 1903C             | 8441C             | 1922B              | 1451C          | 2210              | .500 (12.7)  | 1548C          | 3487              |               |
|               | 1903F             | 8441D             | —                  | 1451D          | 1813              | .625 (15.9)  | 1548D          | 1847              |               |
|               | 1903D             | 8441E             | 1922C              | 1451E          | 2211              | .750 (19.1)  | 1548E          | 3488              |               |
|               | 1903G             | 8441F             | —                  | 1833           | 1816              | .875 (22.2)  | 1879           | 1848              |               |
|               | 1903E             | 8441G             | 1922D              | 1635           | 2212              | 1.000 (25.4) | 1548F          | 3489              |               |
|               | —                 | —                 | —                  | 1636           | 1818              | 1.250 (31.8) | 1881           | 1853              |               |
|               | —                 | —                 | 1922E              | 1637           | 2213              | 1.500 (38.1) | 1882           | 3490              |               |
|               | —                 | —                 | —                  | 1638           | 1819              | 1.750 (44.5) | 1883           | 1855              |               |
|               | —                 | —                 | 1922F              | 1639           | 2214              | 2.000 (50.8) | 1884           | 3491              |               |
|               | —                 | —                 | —                  | 1642           | 1820              | 2.250 (57.2) | 1885           | 1856              |               |
|               | —                 | —                 | —                  | 1643           | 1825              | 2.500 (63.5) | 1886           | 1857              |               |
| 8-32 THREAD   |                   |                   |                    |                |                   |              |                |                   |               |
| .250<br>(6.3) | 1904A             | 8442A             | 1923               | 1474A          | 2215              | .250 (6.4)   | 1692A          | 3492              | .250<br>(6.3) |
|               | 1904B             | 8442B             | 1923A              | 1474B          | 2216              | .375 (9.5)   | 1692B          | 3493              |               |
|               | 1904C             | 8442C             | 1923B              | 1474C          | 2217              | .500 (12.7)  | 1692C          | 3494              |               |
|               | 1904F             | 8442D             | —                  | 1834           | 1827              | .625 (15.9)  | 1887           | 1858              |               |
|               | 1904D             | 8442E             | 1923C              | 1474D          | 2218              | .750 (19.1)  | 1692D          | 3495              |               |
|               | 1904G             | 8442F             | —                  | 1836           | 1828              | .875 (22.2)  | 1888           | 1859              |               |
|               | 1904E             | 8442G             | 1923D              | 1474E          | 2219              | 1.000 (25.4) | 1692E          | 3496              |               |
|               | —                 | —                 | 1923E              | 1837           | 2220              | 1.500 (38.1) | 1889           | 3497              |               |
|               | —                 | —                 | 1923F              | 1838           | 2221              | 2.000 (50.8) | 1899           | 3498              |               |
| 10-32 THREAD  |                   |                   |                    |                |                   |              |                |                   |               |
| .312<br>(7.9) | —                 | —                 | 1475A              | 1822A          | 1821A             | .375 (9.5)   | 3499A          | 3500A             | .312<br>(7.9) |
|               | —                 | —                 | 1475B              | 1822B          | 1821B             | .500 (12.7)  | 3499B          | 3500B             |               |
|               | —                 | —                 | 1475C              | 1822C          | 1821C             | .625 (15.9)  | 3499C          | 3500C             |               |
|               | —                 | —                 | 1475D              | 1822D          | 1821D             | .750 (19.1)  | 3499D          | 3500D             |               |
|               | —                 | —                 | 1475F              | 1822F          | 1821F             | 1.000 (25.4) | 3499F          | 3500F             |               |

NOTE: All standoffs over 1.000 (25.4) are tapped .375 (9.5) min. both ends, except 4-40 standoffs which are tapped .250 (6.4) min.