




4

3

2

1



NOTES:

- Unless otherwise noted, all dimensions are in inches.
- Foil Material: .002 thick 1145 aluminum
- Interface Material: .0005 thick phase-change thermal compound, both sides.
Maximum shipping & storage temperature - 40°C
Reflow temperature - 60°C
Maximum recommended service temperature - 200°C
- Thermal impedance: .030 °C/W-in² (.194 °C/W-cm²) @ 20psi
- Thermal washers shall be packaged in quantities of 10 with oversize separators between them.
- Used with 10-pin Power DIP package (Apex designator: DE).
- Power Devices part no. AL-199-131-APX
- Supplier is to label each plastic box with the Apex part number.

TOLERANCES - UNLESS
OTHERWISE SPECIFIED

.XX = $\pm .05$ [.002]
.XXX = $\pm .005$ [.0002]
ANG. = $\pm 2^\circ$



TITLE:

THERMAL WASHER, P-DIP

SUBJECT:

MECHANICAL DRAWING

ENGINEER:

D-M P.ECK

DCAL:

12438

SHL:

1

OF

1

MODEL:

TW10

FILENAME:

TW10

REV:

G

DATE:

14NOV12

4

3

2

1