




P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED PER EC 0G3B-0387-03	21MAY03	SC	CJ
H		REVISED PER ECR-13-011437	10OCT2013	AV	RP





1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254-0.00635 [.000100-.000250] BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.

- WIRE RANGE: 0.5-1.4MM² (20-16 AWG).
- INSULATION RANGE: 2.01-3.20[.079-.126] DIA.
- DIMENSIONS IN BRACKETS ARE IN INCHES.

5 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254-0.00635 [.000100-.000250] BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.



SECTION A-A
SCALE 20:1



SECTION C-C
SCALE 20:1

5	0.25[.010] BRASS	1-794223-0
1	0.25[.010] BRASS	794223-3
PRE-TIN	0.25[.010] BRASS	794223-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 21MAY2003	TE Connectivity			
DIMENSIONS: INCHES		CHK C. JONES 21MAY2003				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. JONES 21MAY2003	NAME			
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.30 [.012] 4 PLC ± ANGLES ±	PRODUCT SPEC	SOCKET, MINI UNIVERSAL MATE-N-LOK™ 2			
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=794223	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 of 1	REV H	