


RF & MICROWAVE TRANSISTORS

UHF BASE STATION APPLICATIONS

PRELIMINARY DATA

- 470 MHZ
- 24 VOLTS
- EFFICIENCY 50% MIN.
- $P_{OUT} = 15\text{ W}$ WITH 11.0 dB MIN. GAIN
- CLASS AB
- COMMON EMITTER



.230 x .360 6LFL (M142)

 ORDER CODE
SD1391


 BRANDING
SD1391

DESCRIPTION

The SD1391 is a gold metallized NPN planar transistor using diffused emitter ballast resistors for reliability and ruggedness.

The SD1391 is specifically designed as a low power, high gain driver and can be operated in Class A, B or C.

PIN CONNECTION



1. Collector 3. Emitter
2. Base

ABSOLUTE MAXIMUM RATINGS ($T_{case} = 25^{\circ}\text{C}$)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	48	V
V_{CEO}	Collector-Emitter Voltage	25	V
V_{EBO}	Emitter-Base Voltage	3.5	V
I_C	Collector Current	2.5	A
P_{DISS}	Power Dissipation (+25°C)	29	W
T_J	Junction Temperature	+200	°C
T_{STG}	Storage Temperature	- 65 to +150	°C

THERMAL DATA

$R_{TH(j-c)}$	Junction-Case Thermal Resistance	6.0	°C/W
---------------	----------------------------------	-----	------


ELECTRICAL SPECIFICATIONS ($T_{\text{case}} = 25^{\circ}\text{C}$)**STATIC**

Symbol	Test Conditions		Value			Unit
			Min.	Typ.	Max.	
BV_{CBO}	$I_{\text{C}} = 50 \text{ mA}$	$I_{\text{E}} = 0 \text{ mA}$	48	—	—	V
BV_{CEO}	$I_{\text{C}} = 20 \text{ mA}$	$I_{\text{B}} = 0 \text{ mA}$	25	—	—	V
BV_{EBO}	$I_{\text{E}} = 5 \text{ mA}$	$I_{\text{C}} = 0 \text{ mA}$	3.5	—	—	V
I_{CBO}	$V_{\text{CB}} = 24 \text{ V}$	$I_{\text{E}} = 0 \text{ mA}$	—	—	1.0	mA
h_{FE}	$V_{\text{CE}} = 10 \text{ V}$	$I_{\text{C}} = 0.1 \text{ A}$	10	—	100	—


DYNAMIC

Symbol	Test Conditions				Value			Unit
					Min.	Typ.	Max.	
P_{OUT}	$f = 470 \text{ MHz}$	$P_{\text{IN}} = 6.3 \text{ W}$	$V_{\text{CC}} = 24\text{V}$	$I_{\text{CQ}} = 50 \text{ mA}$	15	—	—	W
η_{C}	$f = 470 \text{ MHz}$	$P_{\text{IN}} = 6.3 \text{ W}$	$V_{\text{CC}} = 24\text{V}$	$I_{\text{CQ}} = 50 \text{ mA}$	50	60		%
R_{TL}	$f = 470 \text{ MHz}$	$P_{\text{IN}} = 6.3 \text{ W}$	$V_{\text{CC}} = 24\text{V}$	$I_{\text{CQ}} = 50 \text{ mA}$	10	—		dB
C_{OB}	$f = 1 \text{ MHz}$	$V_{\text{CB}} = 24 \text{ V}$			—	—	24	pF


POWER GAIN vs FREQUENCY




EFFICIENCY vs FREQUENCY




OUTPUT POWER vs INPUT POWER



INPUT RETURN LOSS vs FREQUENCY



TEST CIRCUIT




C1 : 2200pf Chip Capacitor
 C2 : 22pf Chip Capacitor + 2-10pf Trim Capacitor
 C3 : 2 x 33pf + 2-22pf Trim Capacitor
 C5 : 8.2pf + 2-10pf Trim Capacitor
 C6 : 330pf Chip Capacitor
 C7,C8 : 1nF + 10nF + 100nF + 10mF

L1 : 50 ohms microstrip line, L = 6mm
 L2 : 50 ohms microstrip line, L = 19mm
 L3 : 50 ohms microstrip line, L = 25mm
 L4 : 50 ohms microstrip line, L = 14mm
 L5 : 50 ohms microstrip line, L = 20mm
 L6 : 50 ohms microstrip line, L = 7.5mm
 L7 : 50 ohms microstrip line, L = 8.5mm
 L8,L9 : 5 Turns, ID = 33mm, 0.5mm Wire diameter


Board Material: Teflon H = 30mils, Er = 2.55

IMPEDANCE DATA

TYPICAL INPUT
IMPEDANCE




TYPICAL COLLECTOR LOAD
IMPEDANCE



FREQ.	$Z_{IN}(\Omega)$	$Z_{CL}(\Omega)$
420 MHz	$4.0 + j 2.2$	$7.2 + j 1.0$
450 MHz	$5.4 + j 3.9$	$6.8 + j 3.0$
470 MHz	$4.9 + j 5.7$	$6.6 + j 4.3$

PACKAGE MECHANICAL DATA

Ref.: Dwg. No. 12-0142 rev. C
UDCS No. 1010968



SGS-THOMSON MICROELECTRONICS			CONT'D		
	MINIMUM Inches/mm	MAXIMUM Inches/mm		MINIMUM Inches/mm	MAXIMUM Inches/mm
A	.355/9,02	.365/9,27	K	.160/4,06	.180/4,57
B	.115/2,92	.125/3,18	L	.230/5,84	.260/6,60
C	.075/1,91	.085/2,16			
D	.225/5,72	.235/5,97			
E	.090/2,29	.110/2,79			
F	.720/18,29	.730/18,54			
G	.970/24,64	.980/24,89			
H	.355/9,02	.365/9,27			
I	.004/0,10	.006/0,15			
J	.120/3,05	.130/3,30			

Information furnished is believed to be accurate and reliable. However, SGS-THOMSON Microelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of SGS-THOMSON Microelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. SGS-THOMSON Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of SGS-THOMSON Microelectronics.

©1996 SGS-THOMSON Microelectronics - All Rights Reserved

SGS-THOMSON Microelectronics GROUP OF COMPANIES

Australia - Brazil - France - Germany - Hong Kong - Italy - Japan - Korea - Malaysia -
Malta - Morocco - The Netherlands - Singapore - Spain - Sweden - Switzerland - Taiwan -
Thailand - United Kingdom - U.S.A.