





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1							
			C1	ECR-10-023156	11NOV2010	SR	OH

PN 0-1 As Shown

Contact arrangement
view from connecting side




Contact arrangement
view from termination side



NOTES

- SUITABLE CRIMP CONTACTS: SERIES HSK
CUSTOMER DRAWING: 1108756
OUTER DIMENSIONS OF INSULATION: MAX. Ø8mm
- SUITABLE MODULE FIXING FRAME: SERIES HVS SIZE 3 TO 8
CUSTOMER DRAWING: 1103250
- SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 1102855
- SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 1102855
- STANDARDS:
DIN EN 61984; DIN EN 60664-1
-  POLARIZATION RIPS
-  MARKING OF POLARIZATION ACCORDING TO MARKING OF
MODULE FRAME
- PACKAGING:
10 PIECES IN A CARTON

PN 0-1 As Shown




1	FEMALE INSERT	PC-GF20	LYGHT GREY	1
0-1	DESCRIPTION	MATERIAL	COLOR	ITEM NO
HVS-HSK.2.BU.C				



Tyco Electronics AMP GmbH
53757 Sankt Augustin, Germany

NAME FEMALE INSERT ASSY HVS-HSK.2.BU.C				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C=1103271		
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1
			REV C1	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8075 DIN ISO 2768 mH-E DIN 16901-120
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL	FINISH
	

DWN	20.02.2006
CHK	20.02.2006
APVD	20.02.2006
PRODUCT SPEC	108-74081
APPLICATION SPEC	114-74083
WEIGHT	0.008 kg
CUSTOMER DRAWING	