


PART NO.	HOLDING CAPACITY "A"	"B" ±.015(0.4)	"C" ±.02(0.5)	"D" AT MAX CAPACITY REF.
KKU-2-RT	1/8 (3.2)	3/4 (19.1)	3/4 (19.1)	9/32 (7.1)
KKU-4-RT	1/4 (6.4)			15/32 (11.9)
KKU-6-RT	3/8 (9.5)			19/32 (15.1)
KKU-8-RT	1/2 (12.7)	1 (25.4)	1 (25.4)	11/16 (17.5)
KKU-9-RT	9/16 (14.3)			3/4 (19.1)
KKU-12-RT	3/4 (19.1)			29/32 (23.0)
KKU-14-RT	7/8 (22.2)			31/32 (24.6)



NOTES:

1. MAT'L: RIGID PVC (RMS-04).
AVAILABLE IN CLEAR PVC (RMS-32) BY
SPECIAL ORDER.
2. COLOR: GRAY
3. TAPE: 1/16" THICK DOUBLE SIDED
ADHESIVE (RMS-15), WHITE LINER.
4. CUSTOM LENGTHS AVAILABLE BY SPECIAL
ORDER.

			TITLE: KWIK—KLIP, TYPE "U"						DWG IN IN(MM)	
D	SEE ECN #491 FOR CHANGES	SM 10.16.02	TOLERANCES UNLESS NOTED .XX=±.020 .XXX=±.015 FRAC=±1/64 ANG=±1°	FILE # KKU		DWN: S.M.	APP:	FINAL		
C	EDITED NOTE 1 & ADDED NOTE 4	SJ 03.14.02		MAT'L: SEE NOTES		DT: 11/20/00	DT:	PART #		PRINT TYPE CA
B	COMPLETELY RE—DRAWN & CHANGED FILE #	S.M.11.20.00		RE: RICHCO INC.		RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539—4060		SEE TABLE		
A	ADDED NOTES, CORRECTED TAPE THICKNESS TO 1/16"	JK 2.10.00								
REV	DESCRIPTION	ENGR DATE								