

IGBT MODULE (N series)


n Features

- Square RBSOA
- Low Saturation Voltage
- Less Total Power Dissipation
- Improved FWD Characteristic
- Minimized Internal Stray Inductance
- Overcurrent Limiting Function (~3 Times Rated Current)

n Applications

- High Power Switching
- A.C. Motor Controls
- D.C. Motor Controls
- Uninterruptible Power Supply

n Outline Drawing




n Maximum Ratings and Characteristics

• Absolute Maximum Ratings (T_c=25°C)

Items	Symbols	Ratings	Units
Collector-Emitter Voltage	V _{GES}	600	V
Gate-Emitter Voltage	V _{GES}	± 20	V
Collector Current	Continuous	I _C	300
	1ms	I _{C PULSE}	600
	Continuous	-I _C	300
	1ms	-I _{C PULSE}	600
Max. Power Dissipation	P _C	1100	W
Operating Temperature	T _J	+150	°C
Storage Temperature	T _{stg}	-40 ~ +125	°C
Isolation Voltage	A.C. 1min.	V _{is}	2500
Screw Torque	Mounting *1	3.5	Nm
	Terminals *2	4.5	

Note: *1: Recommendable Value; 2.5 ~ 3.5 Nm (M5) or (M6)
*2: Recommendable Value; 3.5 ~ 4.5 Nm (M6)

n Equivalent Circuit




• Electrical Characteristics (at T_J=25°C)

Items	Symbols	Test Conditions	Min.	Typ.	Max.	Units
Zero Gate Voltage Collector Current	I _{GES}	V _{GE} =0V V _{CE} =600V			2.0	mA
Gate-Emitter Leakage Current	I _{GES}	V _{GE} =0V V _{GE} =± 20V			30	μA
Gate-Emitter Threshold Voltage	V _{GE(th)}	V _{GE} =20V I _C =300mA	4.5		7.5	V
Collector-Emitter Saturation Voltage	V _{CE(sat)}	V _{GE} =15V I _C =300A			2.8	V
Input capacitance	C _{ies}	V _{GE} =0V		19800		pF
Output capacitance	C _{oes}	V _{CE} =10V		4400		
Reverse Transfer capacitance	C _{res}	f=1MHz		2000		
Turn-on Time	t _{ON}	V _{CE} =300V		0.6	1.2	μs
	t _r	I _C =300A		0.2	0.6	
Turn-off Time	t _{OFF}	V _{GE} =± 15V		0.6	1.0	
	t _f	R _G =6.8Ω		0.2	0.35	
Diode Forward On-Voltage	V _F	I _F =300A V _{GE} =0V			3.0	V
Reverse Recovery Time	t _{rr}	I _F =300A			300	ns


• Thermal Characteristics

Items	Symbols	Test Conditions	Min.	Typ.	Max.	Units
Thermal Resistance	R _{th(j-c)}	IGBT			0.11	°C/W
	R _{th(j-g)}	Diode			0.15	
	R _{th(j-d)}	With Thermal Compound		0.025		


Collector current vs. Collector-Emitter voltage
 $T_j = 25^\circ\text{C}$




Collector current vs. Collector-Emitter voltage
 $T_j = 125^\circ\text{C}$




Collector-Emitter vs. Gate-Emitter voltage
 $T_j = 25^\circ\text{C}$




Collector-Emitter vs. Gate-Emitter voltage
 $T_j = 125^\circ\text{C}$



Switching time vs. Collector current
 $V_{CC}=300\text{V}$, $R_G=6.8\Omega$, $V_{GE}=\pm 15\text{V}$, $T_j=25^\circ\text{C}$




Switching time vs. Collector current
 $V_{CC}=300\text{V}$, $R_G=6.8\Omega$, $V_{GE}=\pm 15\text{V}$, $T_j=125^\circ\text{C}$




Switching time vs. R_G

$V_{CC}=300V$, $I_C=300A$, $V_{GE}=\pm 15V$, $T_J=25^\circ C$




Dynamic input characteristics

$T_J=25^\circ C$




Forward current vs. Forward voltage

$V_{GE}=0V$




Reverse recovery characteristics


t_{rr} , I_{rr} vs. I_F




Transient thermal resistance




Reversed biased safe operating area
 $+V_{GE}=15V$, $-V_{GE}\leq 15V$, $T_J\leq 125^\circ C$, $R_G\geq 6.8\Omega$



Switching loss vs. Collector current

 $V_{CC}=300V, R_G=6.8\Omega, V_{GE}=\pm 15V$


Capacitance vs. Collector-Emitter voltage

 $T_J=25^\circ C$

Fuji Electric GmbH

Lyoner Straße 26

D-60528 Frankfurt/M

Tel.: 069 - 66 90 29 - 0

Fax.: 069 - 66 90 29 - 56

Fuji Electric (UK) Ltd.

 Commonwealth House
 2 Chalkhill Road Hammersmith

London W6 8DW, UK

Tel.: 0181 - 233 11 30

Fax.: 0181 - 233 11 60

P.O. Box 702708 - Dallas, TX - (972) 733-1700 - (972) 381-9991 (fax)