

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC DIST
G 14

P F ZONE LTR

REVISED & REDRAWN PER 0720-0303-93

DATE APPD
8-30-93

REVISIONS

DESCRIPTION

DATE APPD

REVISED & REDRAWN PER 0720-0303-93

DATE APPD
8-30-93


AMP
WIRE RANGE

6 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

- NOTE:
1. WIRE INSULATION DIA INSULATION SUPPORT "A" 7.87[.310] MAX
 2. WIRE INSULATION DIA INSULATION SUPPORT "B" 10.54[.415] MAX



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C

VOLTAGE RATING:
600 V MAX

CIRCULAR MIL AREA:
10.54-16.77mm² (20,800-33,100)

STRANDED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
TOLERANCES ON:
2 P/LC DEC ± 0.20(.008)
3 P/LC DEC ± .
ANGLES ± .

MATERIAL
COPPER PER ASTM B-152
NYLON, COLOR: BLUE

FINISH TIN PLATE
PER MIL-T-10727

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
SPLICE, BUTT, SINGLE TO MULTIPLE, TERMINYL,
WIRE SIZE: 6 AWG

SIZE CAGE CODE DRAWING NO
B 00779 C-324621

SCALE NTS 1 OF 1

CUSTOMER DRAWING

AMP 1470-15 REV 3-82 05 JAN 1994 16:15:46 AMP10744 <UJ128A>DEPT1132>AMP10744>U. TERMINYL-SPLICE-CUST