

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		A	REVISED PER ECO-11-023039	21FEB12	KH	MS

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-2, BLACK.
TERMINAL: BRASS, BRIGHT TIN PLATED.
SCREWS: 6-32, STEEL, ZINC PLATED W/ CLEAR CHROMATE, UNLESS OTHERWISE SPECIFIED.

ELECTRICAL:
MAXIMUM CURRENT: 20A.
OPERATING VOLTAGE: 600V.
WIRE RANGE: 12-22 AWG MAX.

ENVIRONMENT:
OPERATING TEMP.: -60°C TO +105°C.


- 1
- INK MARKED AS SHOWN.
- 2
- PRELIMINARY PART NUMBER.
- 3
- ALL SCREWS BOTTOMED,TORQUE 2 TO 4 IN-LBS.



11.937	27	SSB7FP270402	2-1546965-7
11.500	26	SSB7FP260402	2-1546965-6
11.062	25	SSB7FP250402	2-1546965-5
10.625	24	SSB7FP240402	2-1546965-4
10.187	23	SSB7FP230402	2-1546965-3
9.750	22	SSB7FP220402	2-1546965-2
9.312	21	SSB7FP210402	2-1546965-1
8.875	20	SSB7FP200402	2-1546965-0
8.437	19	SSB7FP190402	1-1546965-9
8.000	18	SSB7FP180402	1-1546965-8
7.562	17	SSB7FP170402	1-1546965-7
7.125	16	SSB7FP160402	1-1546965-6
6.687	15	SSB7FP150402	1-1546965-5
6.250	14	SSB7FP140402	1-1546965-4
5.812	13	SSB7FP130402	1-1546965-3
5.375	12	SSB7FP120402	1-1546965-2
4.937	11	SSB7FP110402	1-1546965-1
4.500	10	SSB7FP100402	1-1546965-0
4.062	9	SSB7FP090402	1546965-9
4.500	8	SSB7FM08040211	2-1546965-9
3.625	8	SSB7FP080402	1546965-8
3.187	7	SSB7FP070402	8-796602-8
2.750	6	SSB7FP06060213	2-1546965-8
2.750	6	SSB7FP060402	1546965-6
2.312	5	SSB7FP050402	1-1437416-9
1.875	4	SSB7FP040402	1546965-4
1.437	3	SSB7FP030402	1546965-3
1.000	2	SSB7FP020402	1546965-2
DIM A	NO. OF POS.	CATALOG NUMBER	PART NUMBER

SEE FIGURE 1 2

SEE FIGURE 1 2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLGEL 6/22/04		 TE Connectivity							
		CHK S YODER 6/22/04									
		APVD S YODER 6/22/04									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SSB7FPXX0402							
		0 PLC ± —									
		1 PLC ± —									
		2 PLC ± .02									
		3 PLC ± .010									
		4 PLC ± —		SIZECAGE CODEDRAWING NORESTRICTED TO							
		ANGLES ± 1°									
MATERIAL		FINISH		PRODUCT SPEC		—		—			
—		—		APPLICATION SPEC		—		—			
				WEIGHT		—		A300779C-8-796602-8			
CUSTOMER DRAWING						SCALE		SHEET		REV	
						NTS		1 OF 1		A	