






- 1 MATERIAL: HOUSING-PCT POLYESTER, BLACK,
IR COMPATIBLE, UL 94V-0.
TERMINALS-0.33[.013] THICK PHOS BRONZE
PLATED WITH 1.27 μ m [.000050] MINIMUM
HARD GOLD IN LOCALIZED AREA AND 3.81 μ m
[.000150] MINIMUM TIN-LEAD SOLDER AREA
OVER 1.27 μ m [.000050] MINIMUM
NICKEL UNDERPLATE.
SHIELD-0.254 [.010] THICK COPPER ALLOY
PLATED WITH 2.03 μ m [.000080] MINIMUM
TIN-LEAD OVER 2.54 μ m [.000100] MINIMUM
COPPER.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS ARE NOMINAL UNLESS
OTHERWISE SPECIFIED.
- 4 CAUTION: CATEGORY 5 JACK SOLDER TAIL
POSITIONS DO NOT FOLLOW SAME NUMBER
SEQUENCE AS THAT OF THE TRADITIONAL
JACKS.



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SEE APPLICATION SPECIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN W. LONG		08MARS94		AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK B. FOX		16MARS94	
		0 PLC ±- 1 PLC ±- 2 PLC ±0.254 (.010) 3 PLC ±0.127 (.005) 4 PLC ±- ANGLES ±-		APVD G. REED		16MARS94	
MATERIAL		FINISH		PRODUCT SPEC 108-1392		NAME MODULAR JACK ASSEMBLY, 8 PORT, 8 POSITION, RIGHT ANGLE, CATEGORY 5	
				APPLICATION SPEC 114-2048		SIZE A2	
				WEIGHT -		CAGE CODE 00779	
CUSTOMER DRAWING				DRAWING NO C-558526		SCALE 2.1	
				SHEET 1		OF 1	
				REV B			