

MLG1608B39NJT000

Multilayer Inductor for Ultra High Frequency Range

Category : Inductors (Coils)

Sub Category : Inductor Coils

TDK Series Name : MLG Series

Application : No Data Available.

Function : No Data Available.

Description : No Data Available.

▶ Submit Sample Request

▶ Check Distributor Inventory

▶ Print Page

MLG1608 TYPE
APPEARANCE PHOTOGRAPH



< Prev | No PDF Available | Next >

Additional Search Tools:

▶ Application

▶ Catalog

▶ SEAT

▶ CCV

▶ TVCL

▶ Tech Notes

Property Name

Property Description

Product Lifecycle Stage	Production
Part Number Replacement	No Data Available.
Lead (Pb) Free	Yes
Surface Mount	Yes
Construction Type	multilayer type
Mounting	SMD
Body Length (L)	Nom 1.6 mm
Body Width (W)	Nom 0.8 mm
Body Height (T)	Max No Data Available.
Inductance	Nom 0.039 μH
Inductance Tolerance (%)	Min -5 % Max 5 %
Frequency of Inductance	Nom 100 MHz
Q	Min 12
Frequency of Q	Nom 100 MHz
Self Resonant Frequency	Min 1.6 GHz
D.C. Resistance	Nom 0.26 Ohm
D.C. Resistance	Max 0.55 Ohm
Rated Current	Max 0.4 A
Terminal Material	Ag(100%)/Sn plating
Polarity Marking	Yes
Magnetic Shielding	No
Soldering Method	Reflow
Measuring Equipment(Q)	HP4291A+16193A, or equivalent
Category Temperature Range	Min -55 Cel Max 125 Cel
Storage Temperature Range	Min -55 Cel Max 125 Cel
Country of Origin	JPN
Packing	Punched (Paper)Taping [180mm Reel]
Minimum Package Qty	Nom 4000 Pcs
Minimum Order Qty	Nom 4000 Pcs
Weight	Nom 0.004 g

Disclaimer: This information is to be used for reference purposes only and is subject to change by TDK without notice. It reflects an overview of the product characteristics/performance for the particular part number. For product specification information, please refer to TDK's general product specification. Please note that this standard part is not designed or warranted to meet any specifications of any intermediate or end user different from or in addition to the specifications set fort in TDK's general product specification. Note also that this standard part has not been specially designed or manufactured for, nor is it intended or warranted for use in , or permitted to be resold for, specialized applications such as aviation, medical, and/or governmental/military applications (collectively, "Excluded Applications").