




Features


- JA version available to 100K ohms
- 10 pin with 8 resistors in bussed type for pull up/down circuit
- RoHS compliant*
- Convex termination style
- Resistance tolerance $\pm 5\%$
- E24 Series from 10 ohms to 43K ohms
- Suitable for all types of soldering processes
- Paper tape on plastic reel for automatic placement

Model CAY17 - Bussed Resistor Array

Characteristics

Number of Resistors .. 8 (bussed circuit)
 Power Rating per Resistor @ 70 °C
 0.0625 W
 Package Power Rating @ 70 °C
0.250 W
 Operating Temperature Range
 -55 °C to +155 °C
 Derated to 0 Load @.....+125 °C
 Max. Working Voltage.....25 V
 Max. Overload Voltage.....50 V
 Resistance Tolerance $\pm 5\%$
 Resistance Range/E24 Series
 JA version 10 ohms to 100K ohms
 JB version 10 ohms to 43K ohms
 T.C.R..... ± 250 ppm/°C

Construction




How To Order

CA Y 17 - 103 J A LF


- Chip Arrays _____
 Type _____
 • Y = Convex
 Model _____
 • 17 = 1206 Package Size
 Resistance Code _____
 • <10 ohms: "R" represents decimal point (example: 4R7 = 4.7 ohms).
 • ≥ 10 ohms: First two digits are significant, third digit represents number of zeros to follow (example: 474 = 470k ohms)
 (JA range: 10 ohms to 100K ohms;
 JB range: 10 ohms to 43K ohms)
 Resistance Tolerance _____
 • J = $\pm 5\%$
 Resistors _____
 • A = Common from terminal 5 to 10
 • B = Common from terminal 1 to 6
 Terminations _____
 • LF = Tin-plated (RoHS compliant)

For Standard Values Used in Capacitors, Inductors, and Resistors, [click here](#).


Product Dimensions





Derating Curve



Bussed Circuits - Option A



Packaging Dimensions



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$


*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011. Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

Model CAY17 - Bussed Resistor Array

BOURNS®

Soldering Profile for RoHS Compliant Chip Resistors and Arrays



REV. 01/15

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[CAY17-471JALF](#) [CAY17-103JAGLF](#) [CAY17-100JBLF](#) [CAY17-750JALF](#) [CAY17-510JALF](#) [CAY17-152JALF](#) [CAY17-183JALF](#) [CAY17-512JALF](#) [CAY17-390JALF](#) [CAY17-102JBLF](#) [CAY17-822JALF](#) [CAY17-561JALF](#) [CAY17-562JALF](#) [CAY17-333JALF](#) [CAY17-433JALF](#) [CAY17-182JALF](#) [CAY17-221JALF](#) [CAY17-121JALF](#) [CAY17-433JBLF](#) [CAY17-472JBLF](#) [CAY17-102JALF](#) [CAY17-202JALF](#) [CAY17-222JALF](#) [CAY17-681JALF](#) [CAY17-470JALF](#) [CAY17-101JALF](#) [CAY17-272JALF](#) [CAY17-472JALF](#) [CAY17-123JALF](#) [CAY17-240JALF](#) [CAY17-360JALF](#) [CAY17-393JALF](#) [CAY17-513JALF](#) [CAY17-623JALF](#) [CAY17-680JALF](#) [CAY17-472JAGLF](#) [CAY17-102JAGLF](#) [CAY17-103JALF](#) [CAY17-203JALF](#) [CAY17-221JBLF](#) [CAY17-103JBLF](#) [CAY17-151JALF](#) [CAY17-511JALF](#) [CAY17-332JALF](#) [CAY17-223JALF](#) [CAY17-511JBLF](#) [CAY17-331JALF](#) [CAY17-220JALF](#) [CAY17-100JALF](#) [CAY10-820J4LF](#) [CAY17-104JALF](#) [CAY17-122JALF](#) [CAY17-473JALF](#) [CAY17-560JALF](#) [CAY17-563JALF](#) [CAY17-682JALF](#) [CAY17-683JALF](#) [CAY17-330JALF](#) [CAY17-153JALF](#) [CAY17-620JALF](#)