







LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			R1	REVISED PER ECO-11-004917	11MAR11	RK	HMR



1. 0.0013 MIN NICKEL OVER ENTIRE RECEPTACLE WITH 0.0008 MIN GOLD INSIDE RECEPTACLE IN LOCALIZED PLATE AREA.
2. EITHER CAVITY WILL ACCEPT RECEPTACLE 350628,640392 OR PIN 350629,640391.

.660	16.76
.375	9.53
.330	8.38
.200	5.08
.115	2.92
.110	2.79
.105	2.67
.095	2.41
.090	2.29
.085	2.16
.084	2.13
.082	2.08
.081	2.06
.079	2.01
.076	1.93
.075	1.91
.062	1.57
.060	1.52
.055	1.40
.054	1.37
.040	1.02
.025	0.63
.008	0.20
.005	0.13
.000050	0.0013
.000030	0.0008
IN	MM
CONVERSION TABLE	



METRIC

	0.20 BRASS	1.52 MAX	30-24	640392-5
PRE-TIN	0.20 PH.BRZ.	1.52 MAX	30-24	640392-2
PRE-TIN	0.20 BRASS	1.52 MAX	30-24	640392-1
FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 9-30-91	TE Connectivity	
DIMENSIONS: mm(INCHES)		CHK R. SWING 9-30-91		
		APVD C. CASH 10-1-91	NAME PRODUCT SPEC APPLICATION SPEC RESTRICTED TO	
		WEIGHT —	SIZE CAGE CODE DRAWING NO A1 00779 C-640392	
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT —	SCALE 5:1	SHEET 1 OF 1
CUSTOMER DRAWING		REV R1		