

Mobile Intel® HM76 Express Chipset (Intel® BD82HM76 PCH)

- Specifications
- Essentials
- Graphics Specifications
- Expansion Options
- I/O Specifications
- Package Specifications
- Advanced Technologies
- Intel® Platform Protection Technology
- Compatible Products
- Ordering / sSpecs / Steppings

Specifications	
Essentials	
Status	Launched
Launch Date	Q2'12
Embedded Options Available	Yes
TDP	4.1 W
Recommended Customer Price	T&R : \$43.00
Datasheet	Link
Product Brief	Link
Additional Information URL	Link
Graphics Specifications	
# of Displays Supported *	2
Expansion Options	
PCI Express Revision	2.0
Max # of PCI Express Lanes	8
I/O Specifications	
USB Revision	3.0/2.0
# of USB Ports	12
USB 3.0	4
USB 2.0	8
Total # of SATA Ports	6
Max # of SATA 6.0 Gb/s Ports	2
Package Specifications	
Package Size	25mm x 25mm
Low Halogen Options Available	See MDDS
Advanced Technologies	
Intel® Virtualization Technology for Directed I/O (VT-d) *	No
Intel® vPro Technology *	No
Intel® ME Firmware Version	No
Intel® HD Audio Technology	Yes
Intel® Rapid Storage Technology	Yes
Intel® Platform Protection Technology	
Trusted Execution Technology *	No
Anti-Theft Technology	Yes

Compare +

Related Products

Products formerly Panther Point



Visit the Embedded Design Center >

Quick Links

[Export Full Specifications >](#)

[Additional Information >](#)

[Search Distributors >](#)

[Support Overview >](#)

[Search all of intel.com >](#)

PCN/MDDS Information

SLJ8E

915666: PCN | MDDS

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is" and Intel does not make any representations or warranties whatsoever regarding accuracy of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

"Intel classifications" consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company may be the exporter of record, and as such, your company is responsible for determining the correct classification of any item at the time of export.

Refer to Datasheet for formal definitions of product properties and features.

"Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

* This feature may not be available on all computing systems. Please check with the system vendor to determine if your system delivers this feature, or reference the system specifications (motherboard, processor, chipset, power supply, HDD, graphics controller, memory, BIOS, drivers, virtual machine monitor-VMM, platform software, and/or operating system) for feature compatibility. Functionality, performance, and other benefits of this feature may vary depending on system configuration.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers, typically represent 1,000-unit purchase quantities, and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and shipment quantities, and special promotional arrangements may apply. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

System and Maximum TDP is based on worst case scenarios. Actual TDP may be lower if not all I/Os for chipsets are used.

Low Halogen: Applies only to brominated and chlorinated flame retardants (BFRs/CFRs) and PVC in the final product. Intel components as well as purchased components on the finished assembly meet JS-709 requirements, and the PCB / substrate meet IEC 61249-2-21 requirements. The replacement of halogenated flame retardants and/or PVC may not be better for the environment.

WARNING: Altering clock frequency and/or voltage may: (i) reduce system stability and useful life of the system and processor; (ii) cause the processor and other system components to fail; (iii) cause reductions in system performance; (iv) cause additional heat or other damage; and (v) affect system data integrity. Intel has not tested, and does not warranty, the operation of the processor beyond its specifications. Intel assumes no responsibility that the processor, including if used with altered clock frequencies and/or voltages, will be fit for any particular purpose. For more information, visit <http://www.intel.com/content/www/us/en/gaming/overclocking/overclocking-intel-processors.html>

 Send us your feedback!

- About

Company Information

Investor Relations

Contact Us

Newsroom

Site Map

Jobs
- Support

Support Home

Download Center

Product Specifications (ARK)
- Legal

Terms of Use

*Trademarks

Privacy

Cookies
- Social

 Intel Communities

 Intel on Twitter

 Intel on Facebook

 Intel on LinkedIn

 Intel on Instagram

 Intel on YouTube