

The RF GaAs Line

Gallium Arsenide PHEMT


RF Power Field Effect Transistor

Designed for WLL base station applications with frequencies from 3400 to 3600 MHz. Suitable for TDMA and CDMA amplifier applications. To be used in Class AB applications.

- Typical Single-Carrier W-CDMA Performance: $V_{DD} = 12$ Volts, $I_{DQ} = 650$ mA, $P_{out} = 3$ Watts Avg., $f = 3550$ MHz, Channel Bandwidth = 3.84 MHz, Peak/Avg. = 8.5 dB @ 0.01% Probability on CCDF.
Power Gain — 12 dB
Drain Efficiency — 21%
ACPR @ 5 MHz Offset — -41 dBc @ 3.84 MHz Channel Bandwidth
- Internally Matched, Controlled Q, for Ease of Use
- High Gain, High Efficiency and High Linearity
- Excellent Thermal Stability
- In Tape and Reel. R5 Suffix = 50 Units per 56 mm, 13 inch Reel.

MRFG35030R5

3550 MHz, 30 W, 12 V
SINGLE W-CDMA
POWER FET
GaAs PHEMT



CASE 1490-01, STYLE 1

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Drain-Source Voltage	V_{DSS}	15	Vdc
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	79 0.53	Watts W/ $^\circ\text{C}$
Gate-Source Voltage	V_{GS}	- 5	Vdc
RF Input Power	P_{in}	37	dBm
Storage Temperature Range	T_{stg}	- 40 to +175	$^\circ\text{C}$
Channel Temperature ⁽¹⁾	T_{ch}	175	$^\circ\text{C}$
Operating Case Temperature Range	T_C	- 20 to +90	$^\circ\text{C}$

THERMAL CHARACTERISTICS

Characteristic	Symbol	Value	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	1.9	$^\circ\text{C}/\text{W}$

(1) For reliable operation, the operating channel temperature should not exceed 150°C .

Freescale Semiconductor, Inc.

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

DC CHARACTERISTICS

Characteristic	Symbol	Min	Typ	Max	Unit
Off State Drain Current (V _{DS} = 3.5 Vdc, V _{GS} = -2 Vdc)	I _{DSO}	—	15	425	μAdc
Off State Current (V _{DS} = 28.5 Vdc, V _{GS} = -2.5 Vdc)	I _{DSX}	—	5	42.5	mAdc
Gate-Source Cut-off Voltage (V _{DS} = 3.5 Vdc, I _{DS} = 1 mA/mm)	V _{GS(th)}	-0.7	-0.85	-1.1	Vdc

FUNCTIONAL TESTS (In Motorola Test Fixture, 50 ohm system) (1) V_{DD} = 12 Vdc, I_{DQ} = 650 mA, P_{out} = 3 W Avg., f = 3550 MHz, Single-carrier W-CDMA, 3.84 MHz Channel Bandwidth Carrier. ACPR measured in 3.84 MHz Channel Bandwidth @ ±5 MHz Offset. Peak/Avg. = 8.5 dB @ 0.01% Probability on CCDF.

Power Gain	G _{ps}	10	12	—	dB
Drain Efficiency	η _D	17	21	—	%
Adjacent Channel Power Ratio	ACPR	—	-41	-36	dBc

TYPICAL RF PERFORMANCE (In Motorola Test Fixture, 50 ohm system) V_{DD} = 12 Vdc, I_{DQ} = 650 mA, f = 3550 MHz

Output Power, 1 dB Compression Point, CW	P1dB	—	30	—	W
--	------	---	----	---	---

(1) Measurements made with device in test fixture.

Freescale Semiconductor, Inc.




Figure 1. MRFG35030 Test Circuit Schematic

Table 1. MRFG35030 Test Circuit Component Designations and Values

Part	Description	Part Number	Manufacturer
C1, C2, C17	6.8 pF Chip Capacitors, A Case	100A6R8CP500X	ATC
C3, C16	10 pF Chip Capacitors, A Case	100A100JP500X	ATC
C4, C15	100 pF Chip Capacitors, A Case	100A101JP500X	ATC
C5, C14	100 pF Chip Capacitors, B Case	100B101JP500X	ATC
C6, C13	1000 pF Chip Capacitors, B Case	100B102JP500X	ATC
C7, C12	0.1 μ F Chip Capacitors, B Case	CDR33BX104AKWS	Newark
C8, C11	39K Chip Capacitors, B Case	200B393KP50X	ATC
C9, C10	22 μ F, 35 V Tantalum Capacitors	T491X226K035AS	ATC
C18	1.0 pF Chip Capacitor	08051J1R0BBT	AVX
C19	0.7 pF Chip Capacitor	08051J0R7BBT	AVX
C20	0.3 pF Chip Capacitor	08051J0R3BBT	AVX
R1	10 Ω , 1/4 W, 1% Resistor	D55342M07B10J0R	Dale




Figure 2. MRFG35030 Test Circuit Component Layout

Freescale Semiconductor, Inc.

TYPICAL CHARACTERISTICS




Figure 3. Single-Carrier W-CDMA Power Gain and Drain Efficiency versus Output Power




Figure 4. Single-Carrier W-CDMA Adjacent Channel Power Ratio and Input Return Loss versus Output Power




Figure 5. CCDF W-CDMA 3GPP, Test Model 1, 64 DPCH, 67% Clipping, Single-Carrier Test Signal





Figure 6. Single-Carrier W-CDMA Spectrum



$V_{DD} = 12$ Vdc, $I_{DQ} = 650$ mA, $P_{out} = 3$ W Avg.

f MHz	Z_{source} Ω	Z_{load} Ω
3500	$34.459 + j13.83$	$10.322 + j5.42$
3550	$35.460 + j14.19$	$10.400 + j5.44$
3600	$36.000 + j14.12$	$10.100 + j5.72$

Z_{source} = Test circuit impedance as measured from gate to ground.

Z_{load} = Test circuit impedance as measured from drain to ground.




Figure 7. Series Equivalent Source and Load Impedance

Freescale Semiconductor, Inc.

Table 2. Class AB Common Source S-Parameters at $V_{DD} = 12 \text{ Vdc}$, $I_{DQ} = 650 \text{ mA}$

f GHz	S ₁₁		S ₂₁		S ₁₂		S ₂₂	
	S ₁₁	∠ φ	S ₂₁	∠ φ	S ₁₂	∠ φ	S ₂₂	∠ φ
1.00	0.96	146.14	0.80	26.33	0.01	-26.74	0.88	164.54
1.05	0.96	143.94	0.80	22.43	0.01	-28.86	0.88	162.97
1.10	0.96	141.83	0.80	18.46	0.01	-31.83	0.88	161.29
1.15	0.96	139.54	0.80	14.44	0.01	-34.90	0.88	159.77
1.20	0.96	137.28	0.80	10.43	0.01	-37.88	0.88	158.47
1.25	0.96	134.74	0.80	6.28	0.01	-40.90	0.88	157.36
1.30	0.95	132.06	0.81	2.08	0.01	-44.27	0.88	156.46
1.35	0.95	129.35	0.82	-2.17	0.01	-47.36	0.87	155.56
1.40	0.95	126.57	0.84	-6.49	0.01	-51.09	0.86	154.65
1.45	0.95	123.71	0.86	-10.87	0.01	-55.57	0.85	153.72
1.50	0.95	120.59	0.89	-15.96	0.01	-59.77	0.84	151.32
1.55	0.94	117.35	0.92	-20.65	0.01	-64.36	0.83	150.22
1.60	0.94	113.90	0.95	-25.47	0.01	-68.43	0.82	149.03
1.65	0.94	110.38	0.99	-30.41	0.01	-72.98	0.80	147.80
1.70	0.93	106.54	1.03	-35.59	0.01	-78.34	0.79	146.32
1.75	0.93	102.65	1.08	-41.07	0.01	-83.48	0.78	144.63
1.80	0.93	98.32	1.14	-46.87	0.01	-88.75	0.77	142.65
1.85	0.92	93.83	1.19	-53.00	0.01	-94.75	0.76	140.48
1.90	0.92	89.08	1.26	-59.40	0.01	-100.91	0.75	138.36
1.95	0.91	84.07	1.32	-66.00	0.01	-106.97	0.73	136.24
2.00	0.91	78.68	1.39	-72.86	0.02	-113.46	0.72	134.10
2.05	0.90	73.15	1.46	-79.86	0.02	-120.27	0.70	132.02
2.10	0.90	67.33	1.54	-87.14	0.02	-127.45	0.68	130.09
2.15	0.89	61.07	1.62	-94.66	0.02	-135.04	0.65	127.98
2.20	0.89	54.56	1.71	-102.36	0.02	-142.85	0.63	125.90
2.25	0.89	47.64	1.80	-110.40	0.02	-150.91	0.60	123.85
2.30	0.89	40.29	1.89	-118.62	0.02	-159.34	0.56	121.74
2.35	0.89	32.60	1.99	-127.18	0.03	-168.04	0.53	119.56
2.40	0.89	24.42	2.09	-135.99	0.03	-177.20	0.49	117.39
2.45	0.88	16.02	2.20	-145.15	0.03	173.58	0.44	115.36
2.50	0.88	7.28	2.30	-154.53	0.03	163.81	0.40	113.49
2.55	0.88	-1.82	2.40	-164.19	0.03	153.87	0.35	111.97
2.60	0.88	-10.92	2.49	-174.07	0.03	143.74	0.30	111.53
2.65	0.88	-20.24	2.58	175.96	0.04	133.49	0.25	112.88
2.70	0.88	-29.71	2.66	165.78	0.04	122.87	0.21	117.12
2.75	0.87	-39.08	2.73	155.55	0.04	112.29	0.16	126.44
2.80	0.86	-48.39	2.79	145.30	0.04	101.82	0.14	143.32
2.85	0.85	-57.62	2.84	135.00	0.04	91.15	0.13	165.50
2.90	0.83	-66.46	2.89	124.74	0.04	80.47	0.16	-175.99
2.95	0.81	-75.13	2.93	114.46	0.05	69.79	0.20	-164.66
3.00	0.79	-83.52	2.98	104.21	0.05	59.07	0.24	-158.95
3.05	0.76	-91.51	3.02	93.91	0.05	48.50	0.29	-156.30
3.10	0.72	-99.34	3.06	83.64	0.05	37.72	0.35	-155.52
3.15	0.69	-106.90	3.11	73.20	0.05	26.81	0.40	-156.12
3.20	0.64	-114.08	3.17	62.60	0.05	15.81	0.45	-157.58
3.25	0.59	-120.87	3.24	51.75	0.06	4.40	0.50	-160.01
3.30	0.53	-127.33	3.31	40.49	0.06	-7.27	0.55	-163.32

Freescale Semiconductor, Inc.

Table 2. Class AB Common Source S-Parameters at $V_{DD} = 12 \text{ Vdc}$, $I_{DQ} = 650 \text{ mA}$ (continued)



f GHz	S ₁₁		S ₂₁		S ₁₂		S ₂₂	
	S ₁₁	∠ φ	S ₂₁	∠ φ	S ₁₂	∠ φ	S ₂₂	∠ φ
3.35	0.46	-132.64	3.37	28.77	0.06	-19.38	0.59	-167.40
3.40	0.38	-136.44	3.44	16.54	0.06	-32.21	0.64	-172.25
3.45	0.29	-136.21	3.48	3.73	0.06	-45.19	0.68	-177.89
3.50	0.22	-127.35	3.51	-9.59	0.07	-58.78	0.71	175.79
3.55	0.18	-102.40	3.50	-23.47	0.07	-73.20	0.73	168.90
3.60	0.22	-76.34	3.45	-37.84	0.07	-88.01	0.73	161.51
3.65	0.32	-66.79	3.36	-52.56	0.07	-103.17	0.71	153.97
3.70	0.43	-66.93	3.22	-67.50	0.06	-118.63	0.66	146.50
3.75	0.54	-71.16	3.03	-82.42	0.06	-134.11	0.59	139.64
3.80	0.64	-77.27	2.80	-97.34	0.06	-149.56	0.50	133.98
3.85	0.73	-84.04	2.55	-111.69	0.05	-164.55	0.40	130.85
3.90	0.80	-90.75	2.29	-125.67	0.05	-179.15	0.29	133.09
3.95	0.85	-97.18	2.03	-138.92	0.04	166.69	0.20	146.65
4.00	0.90	-103.05	1.79	-151.47	0.04	153.98	0.17	177.35
4.05	0.93	-108.56	1.56	-163.31	0.03	141.83	0.22	-158.21
4.10	0.95	-113.68	1.35	-174.50	0.03	130.44	0.29	-149.29
4.15	0.96	-118.39	1.17	175.04	0.03	119.35	0.38	-147.85
4.20	0.97	-122.39	1.01	165.37	0.02	108.97	0.45	-149.63
4.25	0.98	-126.23	0.87	156.24	0.02	99.25	0.52	-152.98
4.30	0.98	-129.72	0.75	147.79	0.02	90.59	0.58	-157.04
4.35	0.98	-132.86	0.65	139.97	0.02	83.55	0.63	-161.14
4.40	0.99	-135.98	0.57	132.62	0.01	76.85	0.68	-165.09
4.45	0.99	-138.73	0.49	125.76	0.01	69.46	0.72	-168.90
4.50	0.99	-141.42	0.43	119.49	0.01	62.85	0.76	-172.28
4.55	0.99	-144.00	0.37	113.69	0.01	56.84	0.79	-175.36
4.60	0.99	-146.52	0.33	108.35	0.01	51.52	0.82	-178.09
4.65	0.99	-148.89	0.29	103.42	0.01	46.39	0.85	179.48
4.70	0.99	-151.15	0.26	98.73	0.01	42.21	0.87	177.24
4.75	1.00	-153.53	0.24	94.28	0.01	37.59	0.89	175.01
4.80	1.00	-155.94	0.21	89.98	0.01	34.26	0.90	172.99
4.85	1.00	-158.19	0.19	85.78	0.01	30.24	0.91	170.86
4.90	1.00	-160.43	0.18	81.45	0.01	27.16	0.92	168.57
4.95	0.99	-162.40	0.16	78.17	0.01	25.24	0.92	165.89
5.00	1.00	-164.61	0.15	74.76	0.01	22.43	0.93	163.33

NOTES

NOTES

Freescale Semiconductor, Inc.

PACKAGE DIMENSIONS



CASE 1490-01
ISSUE O

NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION H IS MEASURED .030 (0.762) AWAY FROM PACKAGE BODY.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.948	0.958	24.08	24.33
B	0.680	0.690	17.27	17.53
C	0.147	0.182	3.73	4.62
D	0.055	0.065	1.40	1.65
E	0.035	0.045	0.89	1.14
F	0.003	0.006	0.08	0.15
G	0.803 BSC		20.40 BSC	
H	0.057	0.067	1.45	1.70
J	0.315 BSC		8.00	
K	0.095	0.125	2.41	3.18
M	0.595	0.605	15.11	15.37
N	0.594	0.606	15.09	15.39
Q	0.092	0.112	2.34	2.84
R	0.678	0.692	17.22	17.58
S	0.680	0.690	17.27	17.23
aaa	0.004		0.10	
bbb	0.015		0.38	

STYLE 1:

- PIN 1. GATE
- DRAIN
- SOURCE

Information in this document is provided solely to enable system and software implementers to use Motorola products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part.

MOTOROLA and the Stylized M Logo are registered in the US Patent and Trademark Office. All other product or service names are the property of their respective owners. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

© Motorola Inc. 2004

HOW TO REACH US:

USA/EUROPE/LOCATIONS NOT LISTED:
Motorola Literature Distribution
P.O. Box 5405, Denver, Colorado 80217
1-800-521-6274 or 480-768-2130

JAPAN: Motorola Japan Ltd.; SPS, Technical Information Center,
3-20-1, Minami-Azabu, Minato-ku, Tokyo 106-8573, Japan
81-3-3440-3569

ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd.; Silicon Harbour Centre,
2 Dai King Street, Tai Po Industrial Estate, Tai Po, N.T., Hong Kong
852-26668334

HOME PAGE: <http://motorola.com/semiconductors>

**MOTOROLA**

◇ **For More Information On This Product,
Go to: www.freescale.com**

MRFG35030R5/D