



Series C82/C92 Standard Dual Beam Solder Tail Edge-Grip Sockets

FEATURES:

- Dual beam, edge-grip contacts provide high retention with positive wiping action.
- Removable cover provides lower profile.
- Side-to-side stackable.


SPECIFICATIONS:

- Body is black UL-94V-0 Glass-filled 4/6 Nylon.
- Contact is Grade A spring-tempered Phosphor Bronze.
- Contact plating: (all over 50µ" [1.27µm] Nickel per SAE-AMS-QQ-N-290)
Tin = 200µ" [5.08µm] min Matte Tin per ASTM B545-97.
Tin/Lead = 50-150µ" [1.27-3.81µm] min. 90/10 Tin/Lead per MIL-P-81728.
Gold = 10µ" [0.25µm] min. Gold per MIL-G-45204.
- Contact current rating=1 Amp.
- Contact resistance=20 mOhms initial.
- Insulation resistance=100 MOhms @ 500 VDC per MIL-STD-1344, method 3003.1.
- Dielectric withstanding voltage=1000 VAC.
- Operating temperature= -67°F to 221°F [-55°C to 105°C] Tin
= -67°F to 257°F [-55°C to 125°C] Gold
- Solderability: MIL-STD-202, method 208 less heat aging.
- Accepts leads up to .011 x .018 ± .003 [.28 x .46 ± .08] or .021 [.53] diameter.
- Accepts leads .100-.200 [2.54-5.08] long with cover.


MOUNTING CONSIDERATIONS:

- Suggested PCB hole size=.036 ± .002 [.91 ± .05] dia.

ALL DIMENSIONS: INCHES [MILLIMETERS]



Pin tails can be bent over without breaking for mounting on PCB



Note: Aries specializes in custom design and production. In addition to the standard products shown on this page, special materials, platings, sizes, and configurations can be furnished, depending on quantities. Aries reserves the right to change product specifications without notice.

ORDERING INFORMATION

Socket series: C XX XX - XX TL

Pin plating: 82 = Tin, 92 = Gold


No. of pins (see table)

Plating option: Tin/Lead

C82 series: -04 = closed entry, -54 = open entry

C92 series: -00 = closed entry, -50 = open entry

All tolerances ± .005 [.13] unless otherwise specified



No. of Pins	Dim. "A"	Dim. "B"	Centers "C"	Dim. "D" (max)	Dim. "E"
8	.465 [11.81]	.300 [7.62]	.300 [7.62]	.400 [10.16]	---
14	.765 [19.43]	.600 [15.24]	.300 [7.62]	.400 [10.16]	.300 [7.62]
16	.865 [21.97]	.700 [17.78]	.300 [7.62]	.400 [10.16]	.400 [10.16]
18	.965 [24.51]	.800 [20.32]	.300 [7.62]	.400 [10.16]	.400 [10.16]
20	1.065 [27.05]	.900 [22.86]	.300 [7.62]	.400 [10.16]	.400 [10.16]
22	1.180 [29.97]	1.000 [25.40]	.400 [10.16]	.500 [12.70]	.500 [12.70]
24	1.280 [32.51]	1.100 [27.94]	.600 [15.24]	.700 [17.78]	.500 [12.70]
28	1.480 [37.59]	1.300 [33.02]	.600 [15.24]	.700 [17.78]	.500 [12.70]
36	1.880 [47.75]	1.700 [43.18]	.600 [15.24]	.700 [17.78]	.800 [20.32]
40	2.080 [52.83]	1.900 [48.26]	.600 [15.24]	.700 [17.78]	.800 [20.32]



ARIES
ELECTRONICS, INC.

Bristol, PA 19007-6810 USA
TEL (215) 781-9956 • FAX (215) 781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



12002
REV. D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aries:

[C8208-54](#) [C9208-50](#) [C8208-04](#) [C9208-00](#) [C8236-54](#) [C9236-50](#) [C8236-04](#) [C9236-00](#) [C9218-00](#) [C8218-04](#)
[C8218-54](#) [C9218-50](#) [C9222-00](#) [C8222-04](#) [C8222-54](#) [C9222-50](#) [C8216-54](#) [C9216-50](#) [C8214-54](#) [C9214-50](#) [C9214-00](#)

Aries Electronics:

[C8220-54](#) [C9220-50](#) [C9220-00](#) [C8220-04](#) [C8240-54](#) [C9240-50](#) [C8240-04](#) [C9240-00](#) [C82-28-04](#) [C8214-04](#)
[C8216-04](#) [C8224-04](#) [C9224-00](#) [C9224-50](#) [C8224-54](#) [C8228-54](#) [C9228-50](#) [C9228-00](#) [C9216-00](#)