





# Easy Selection Guide For ~~Panduit~~ Adhesive Backed Cable Tie Mounts

Panduit Corp.  
17301 Ridgeland Avenue  
Tinley Park, IL 60477-3091  
Phone: 888-506-5400 Ext. 7346  
Fax: 770-781-9076  
Email: info@panduit.com  
Website: www.panduit.com


ABM1M-A  
ABM1M-AT




ABMM-A  
ABMM-AT




ABM2S




ABM100



ABM112




ABM3H  
ABM4H




| Part Number  | Used With Cable Ties** | Dimensions Inches (mm) |                |              | Material | Color | Where Used              | Adhesive Type/Static Load lbs. (g) | Packaging*     |                |                |                |
|--------------|------------------------|------------------------|----------------|--------------|----------|-------|-------------------------|------------------------------------|----------------|----------------|----------------|----------------|
|              |                        | A                      | B              | C            |          |       |                         |                                    | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| ABM1M-A-C    | M                      | .50<br>(12.7)          | .50<br>(12.7)  | .16<br>(4.0) | Nylon    | White | Indoors                 | Rubber<br>.13 (59)                 | 100            | 500            | 1000           | 5000           |
| ABM1M-AT-C   | M                      | .50<br>(12.7)          | .50<br>(12.7)  | .16<br>(4.0) | Nylon    | White | Indoors/<br>High Temp.  | Acrylic<br>.13 (59)                | 100            | 500            | 1000           | 5000           |
| ABMM-A-C     | M, I                   | .75<br>(19.1)          | .75<br>(19.1)  | .18<br>(4.6) | ABS      | White | Indoors                 | Rubber<br>.30 (136)                | 100            | 500            | 500            | 5000           |
| ABMM-AT-C    | M, I                   | .75<br>(19.1)          | .75<br>(19.1)  | .18<br>(4.6) | ABS      | White | Indoors/<br>High Temp.  | Acrylic<br>.30 (136)               | 100            | 500            | 500            | 5000           |
| ABMM-AT-C0   | M, I                   | .75<br>(19.1)          | .75<br>(19.1)  | .18<br>(4.6) | ABS      | Black | Outdoors/<br>High Temp. | Acrylic<br>.30 (136)               | 100            | 500            | 500            | 5000           |
| ABM2S-A-C    | M, I, S                | 1.00<br>(25.4)         | 1.00<br>(25.4) | .20<br>(5.1) | ABS      | White | Indoors                 | Rubber<br>.50 (227)                | 100            | 500            | 500            | 5000           |
| ABM2S-AT-C   | M, I, S                | 1.00<br>(25.4)         | 1.00<br>(25.4) | .20<br>(5.1) | ABS      | White | Indoors/<br>High Temp.  | Acrylic<br>.50 (227)               | 100            | 500            | 500            | 5000           |
| ABM100-A-C   | M, I, S                | 1.00<br>(25.4)         | 1.00<br>(25.4) | .24<br>(6.1) | Nylon    | White | Indoors                 | Rubber<br>.50 (227)                | 100            | 500            | 500            | 5000           |
| ABM100-AT-C0 | M, I, S                | 1.00<br>(25.4)         | 1.00<br>(25.4) | .24<br>(6.1) | Nylon    | Black | Outdoors/<br>High Temp. | Acrylic<br>.50 (227)               | 100            | 500            | 500            | 5000           |
| ABM112-A-C   | M, I, S                | 1.12<br>(28.6)         | 1.12<br>(28.6) | .16<br>(4.2) | Nylon    | White | Indoors                 | Rubber<br>.63 (286)                | 100            | 500            | 500            | 5000           |
| ABM112-AT-C  | M, I, S                | 1.12<br>(28.6)         | 1.12<br>(28.6) | .16<br>(4.2) | Nylon    | White | Indoors/<br>High Temp.  | Acrylic<br>.63 (286)               | 100            | 1000           | 500            | 5000           |
| ABM112-AT-C0 | M, I, S                | 1.12<br>(28.6)         | 1.12<br>(28.6) | .16<br>(4.2) | Nylon    | Black | Outdoors/<br>High Temp. | Acrylic<br>.63 (286)               | 100            | 1000           | 500            | 5000           |
| ABM3H-A-L    | M, I, S<br>LH, H, HLM  | 1.50<br>(38.1)         | 1.50<br>(38.1) | .25<br>(6.4) | Nylon    | White | Indoors                 | Rubber<br>1.12 (508)               | 50             | 500            | 200            | 1000           |
| ABM3H-AT-L   | M, I, S<br>LH, H, HLM  | 1.50<br>(38.1)         | 1.50<br>(38.1) | .25<br>(6.4) | Nylon    | White | Indoors/<br>High Temp.  | Acrylic<br>1.12 (508)              | 50             | 500            | 200            | 1000           |
| ABM4H-A-L    | M, I, S<br>LH, H, HLM  | 2.00<br>(50.8)         | 2.00<br>(50.8) | .25<br>(6.4) | Nylon    | White | Indoors                 | Rubber<br>1.12 (508)               | 50             | 500            | 200            | 1000           |
| ABM4H-AT-L   | M, I, S<br>LH, H, HLM  | 2.00<br>(50.8)         | 2.00<br>(50.8) | .25<br>(6.4) | Nylon    | White | Indoors/<br>High Temp.  | Acrylic<br>1.12 (508)              | 50             | 500            | 200            | 1000           |

\*Order Number of Pieces Required in Multiples of Packaging Quantities.

\*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, LH = Light Heavy, H = Heavy and HLM denotes TAK-TY™ Hook & Loop Cable Ties.




TM



## Tie Mounts Mechanically Applied



TMEH



| Part Number | Used With Cable Ties** | Dimensions Inches (mm) |                |               | Material                | Color   | Where Used | Mounting Method | Packaging*     |                |                |                |
|-------------|------------------------|------------------------|----------------|---------------|-------------------------|---------|------------|-----------------|----------------|----------------|----------------|----------------|
|             |                        | A                      | B              | C             |                         |         |            |                 | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| TM1S4-C     | M                      | .513<br>(13.0)         | .316<br>(8.0)  | .230<br>(5.8) | Nylon                   | Natural | Indoors    | #4 (M2.5) Screw | 100            | 500            | 1000           | 5000           |
| TM1S6-C     | M                      | .513<br>(13.0)         | .316<br>(8.0)  | .230<br>(5.8) |                         |         | Indoors    | #6 (M3) Screw   | 100            | 500            | 1000           | 5000           |
| TM2S8-C     | M, I, S                | .630<br>(16)           | .425<br>(10.8) | .275<br>(7.0) |                         |         | Indoors    | #6 (M3) Screw   | 100            | 500            | 1000           | 5000           |
| TM3S10-C    | M, I, S, LH            | .875<br>(22.2)         | .620<br>(15.8) | .375<br>(9.5) |                         |         | Indoors    | #10 (M5) Screw  | 100            | 500            | 1000           | 5000           |
| TMEH-S8-Q0  | EH, HLT                | 1.65<br>(42)           | .74<br>(19)    | .61<br>(15)   | Weather Resistant Nylon | Black   | Outdoors   | #8 (M4) Screw   | 25             | 250            | 100            | 500            |
| TMEH-S10-Q0 | EH, HLT                | 1.65<br>(42)           | .74<br>(19)    | .61<br>(15)   |                         |         | Outdoors   | #10 (M5) Screw  | 25             | 250            | 100            | 500            |
| TMEH-S25-Q0 | EH, HLT                | 1.65<br>(42)           | .74<br>(19)    | .61<br>(15)   |                         |         | Outdoors   | 1/4" (M6) Screw | 25             | 250            | 100            | 500            |

\*Order Number of Pieces Required in Multiples of Packaging Quantities.

\*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, LH = Light Heavy, H = Heavy and HLT denotes TAK-TY™ Hook & Loop Cable Ties.

## Push Mount

Can be used where only one side of the panel is accessible.



| Part Number | Used With Cable Ties** | Dimensions Inches (mm) | Panel Dimensions |               | Material | Color   | Where Used | Mounting Method                | Packaging*     |                |                |                |
|-------------|------------------------|------------------------|------------------|---------------|----------|---------|------------|--------------------------------|----------------|----------------|----------------|----------------|
|             |                        |                        | Thickness Max.   | Hole Diameter |          |         |            |                                | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| PM2H25-C    | M, I, S                | See Drawing            | .125 (3.2)       | .250 (6.4)    | Nylon    | Natural | Indoors    | Inserted into pre-drilled hole | 100            | 500            | 1000           | 5000           |

\*Order Number of Pieces Required in Multiples of Packaging Quantities. \*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate and S = Standard.

## Push Button Mount

Designed for use where both sides of the panel are accessible.




| Part Number | Used With Cable Ties** | Dimensions Inches (mm) | Panel Dimensions |               | Material | Color   | Where Used | Mounting Method                | Packaging*     |                |                |                |
|-------------|------------------------|------------------------|------------------|---------------|----------|---------|------------|--------------------------------|----------------|----------------|----------------|----------------|
|             |                        |                        | Thickness Max.   | Hole Diameter |          |         |            |                                | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| PBMS-H25-C  | M, I, S                | See Drawing            | .125 (3.2)       | .250 (6.4)    | Nylon    | Natural | Indoors    | Inserted into pre-drilled hole | 100            | 500            | 1000           | 5000           |

\*Order Number of Pieces Required in Multiples of Packaging Quantities. \*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate and S = Standard.

## Tie Anchor Mounts

Low profile, versatile mount for applications where space is limited.



| Part Number | Used With Cable Ties** | Dimensions Inches (mm) |            |            |            | Material | Color   | Where Used | Mounting Method | Packaging*     |                |                |                |
|-------------|------------------------|------------------------|------------|------------|------------|----------|---------|------------|-----------------|----------------|----------------|----------------|----------------|
|             |                        | A                      | B          | C          | D          |          |         |            |                 | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| TA1S8-C     | M, I, S                | .75 (19.1)             | .375 (9.5) | .195 (5.0) | .170 (4.3) | Nylon    | Natural | Indoors    | #8 (M4) Screw   | 100            | 500            | 1000           | 5000           |

\*Order Number of Pieces Required in Multiples of Packaging Quantities. \*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate and S = Standard.

## Low Profile Mounts

Designed to secure wire bundles where space is limited.



| Part Number | Used With Cable Ties** | Dimensions Inches (mm) |            |           |                         | Material | Color   | Where Used | Mounting Method         | Packaging*     |                |                |                |
|-------------|------------------------|------------------------|------------|-----------|-------------------------|----------|---------|------------|-------------------------|----------------|----------------|----------------|----------------|
|             |                        | A                      | B          | C         | D                       |          |         |            |                         | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| LPMM-S2-C   | M                      | .40 (10.2)             | .32 (8.1)  | .10 (2.5) | .096 <sup>1</sup> (2.4) | Nylon    | Natural | Indoors    | #2 (M2) Flat-head Screw | 100            | 1000           | 1000           | 10,000         |
| LPMM-S5-C   | M                      | .40 (10.2)             | .32 (8.1)  | .10 (2.5) | .137 <sup>2</sup> (3.5) |          |         | Indoors    | #5 (M3) Flat-head Screw | 100            | 1000           | 1000           | 10,000         |
| LPMS-S8-C   | M, I, S                | .75 (19.1)             | .50 (12.7) | .12 (3.0) | .180 <sup>2</sup> (4.6) |          |         | Indoors    | #8 (M4) Flat-head Screw | 100            | 1000           | 1000           | 5000           |

\*Order Number of Pieces Required in Multiples of Packaging Quantities. \*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate and S = Standard.

## Knock-In Low Profile Mounts

Secures wires to any pre-drilled panel.




| Part Number  | Used With Cable Ties** | A          | Dimensions Inches (mm) | Hole Size  | Material | Color  | Where Used | Mounting Method     | Packaging*     |                |                |                |
|--------------|------------------------|------------|------------------------|------------|----------|--------|------------|---------------------|----------------|----------------|----------------|----------------|
|              |                        |            |                        |            |          |        |            |                     | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| KIMS-H366-C2 | M, I, S                | .155 (3.9) | See Drawing            | .144 (3.7) | Nylon    | Red    | Indoors    | Integral Push Rivet | 100            | 500            | 1000           | 5000           |
| KIMS-H430-C6 | M, I, S                | .180 (4.6) | See Drawing            | .169 (4.3) | Nylon    | Blue   | Indoors    | Integral Push Rivet | 100            | 1000           | 1000           | 5000           |
| KIMS-H500-C4 | M, I, S                | .202 (5.1) | See Drawing            | .196 (5.0) | Nylon    | Yellow | Indoors    | Integral Push Rivet | 100            | 500            | 1000           | 5000           |

\*Order Number of Pieces Required in Multiples of Packaging Quantities. \*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate and S = Standard.

## Masonry Push Mounts

Used to secure wire, cable or tubing to masonry surfaces.



| Part Number | Used With Cable Ties** | Dimensions Inches (mm) |           |           | Hole Dimensions |               | Material                | Color | Where Used          | Mounting Method                | Packaging*     |                |                |                |
|-------------|------------------------|------------------------|-----------|-----------|-----------------|---------------|-------------------------|-------|---------------------|--------------------------------|----------------|----------------|----------------|----------------|
|             |                        | A                      | B         | C         | Drill Depth     | Hole Diameter |                         |       |                     |                                | Std. Pkg. Qty. | Std. Ctn. Qty. | Bulk Pkg. Qty. | Bulk Ctn. Qty. |
| MPMS25-C0   | M, I, S                | .97 (24.6)             | .25 (6.4) | .22 (5.6) | 1.25 (31.8)     | .250 (6.4)    | Weather-Resistant Nylon | Black | Outdoors or Indoors | Inserted into Pre-Drilled Hole | 100            | 500            | 1000           | 5000           |
| MPMH38-L0   | M, I, S, LH, H, HLM    | 1.25 (31.8)            | .30 (7.5) | .38 (9.6) | 1.50 (38.1)     | .375 (10)     |                         |       |                     |                                | 50             | 500            | 500            | 5000           |

\*Order Number of Pieces Required in Multiples of Packaging Quantities. \*\* Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, LH = Light Heavy, H = Heavy and HLM denotes Tak-Ty™ Hook & Loop Cable Ties.

SA102N90-WA