



NOTES:

1. TERMINAL TO BE USED IN HOUSING 70066-**** AND 70450-****.
2. REFER TO PRODUCT SPECIFICATION PS-70058.
3. REFER TO MOLEX OPERATIONS AND SERVICE MANUAL FOR CRIMP DETAILS.
4. TERMINAL TO BE USED WITH (0.64)/.025 SQUARE PINS.
5. TERMINAL TO BE USED WITH 22-24 AWG STRANDED WIRE WITH (1.63)/.064 MAXIMUM DIAMETER INSULATION.
6. TERMINALS SUPPLIED IN REEL FORM.
7. CRIMP SIZE INDICATOR C=22-24 AWG

PLATING:

.000030 MINIMUM GOLD PLATE IN SELECT AREA,
.000075 MINIMUM TIN PLATE IN SELECT AREA,
OVER NICKEL PLATE OVERALL.

(.22±.06)
.0085±.0025

CORRECT MATERIAL NO. EC NO: UCP2014-0996 DRAWN BY: RWHIPPLE 2013/09/03 CHK'D BY: DMORGAN 2013/09/03 APPR: SMILLER 2013/09/24	DESCRIPTION	QUALITY SYMBOLS <div><div>F_A=0</div><div>F_E=0</div><div>F_P=0</div></div>	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 10:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION <div><div></div><div></div></div>											
				mm	INCH	DRAWN BY RWHIPPLE	DATE 2013/06/11	TITLE TERMINAL - BOX/CRIMP FOR 22-24 AWG ON A REEL												
			4 PLACES	± ---	± ---	CHECKED BY JAS	DATE 1988/03/02													
			3 PLACES	± ---	± .005	APPROVED BY SMILLER 2013/07/09					DOCUMENT NO. SD-70058-0026					SHEET NO. 1 OF 1				
			2 PLACES	± 0.13	± .01															
1 PLACE	± 0.25	± ---																		
0 PLACE	± ---	± ---	ANGULAR ±1/2°		MATERIAL NO. 16-02-0088															
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													