



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDM-232-022 REV: 1.0

2.3" 8*8 LED Lamp Dot Matrix Displays

MODEL NO : ELLM-2302WB/HRC-5/H0-A ECN : Page: 1/5

■ Features :

- Large Emitting Dot 0.2"Diameter.
- Low Power/High Brightness.

■ Applications:

- Instrument panels
- Digital readout display

■ Description :

- The LM-2302 series are a large emitting area(5.0mm diameter)LAMP sources configured in a 64 dots 8*8 matrix array.
- These device is made with white clear dots and black surface.

PART NO	CHIP		C.C. or C.A.
	Material	Emitted Color	
ELLM-2302WB/HRC-5/H0-A	GaAlAs	Super Red	C.A.

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936


FAX : 886-2-2267-6244,22676189,22676306

<http://www.everlight.com>



2.3" 8*8 LED Lamp Dot Matrix Displays

■ Package Dimension:



■ NOTES:

1.All dimensions are millimeters ,tolerance is 0.25mm unless otherwise noted.

2.Above specification may be changed without notice.

Supplier will reserve authority on material change for above specification .



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDM-232-022 REV: 1.0

2.3" 8*8 LED Lamp Dot Matrix Displays

MODEL NO : ELLM-2302WB/HRC-5/H0-A ECN : Page: 3/5

■ Absolute maximum ratings at Ta = 25℃ :

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	40	mA
Operating Temperature	Topr	-40 to +85	℃
Storage Temperature	Tstg	-40to+100	℃
Soldering Temperature	Tsol	260 ± 5	℃
Power Dissipation	Pd	110	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	180	mA

■ Electronic optical characteristics :

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous Intensity	Iv	400	600	----	mcd	If=20mA
Peak Wavelength	λ_p	----	660	----	nm	If=20mA
Dominant Wavelength	λ_d	----	643	----	nm	If=20mA
Spectrum Radiation Bandwidth	$\triangle \lambda$	----	20	----	nm	If=20mA
Forward Voltage	Vf	1.5	1.7	2.4	V	If=20mA
Reverse Current	Ir	----	----	10	V	Vr=5V



REV: 1.0

MODEL NO : ELLM-2302WB/HRC-5/H0-A^{ECN}: Page: 4/5

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min ┆ 5 min L : -55°C 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min ┆ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	If = 20 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS	0/1



2.3" 8*8 LED Lamp Dot Matrix Displays

MODEL NO: ELLM-2302WB/HRC-5/H0-A ECN: Page: 5/5

Typical Electro-Optical Characteristic Curves:

SR

