

# T Series

## Subminiature Toggle Switches

### Features/Benefits

- **Compact size—small footprint**
- **Single and double pole models**
- **PC and panel mount options available**
- **RoHS compliant models available**

### Typical Applications

- **Hand-held telecommunications**
- **Instrumentation**
- **Medical equipment**



Models Available

### Specifications

CONTACT RATING: B contact material: 0.4 VA max. @ 20 V AC or DC max. Q contact material (TX01 models): 3 AMPS @ 120 V AC or 28 V DC. All other models: 2 AMPS @ 120 V AC or 28 V DC. See page F-37 for additional ratings.

ELECTRICAL LIFE: TX01 models: 60,000 make-and-break cycles at full load. All other models: 30,000 cycles.

CONTACT RESISTANCE: Below 20 m  $\Omega$  typ. initial @ 2-4 V DC, 100 mA, for both silver and gold plated contacts.

INSULATION RESISTANCE:  $10^9 \Omega$  min.

DIELECTRIC STRENGTH: 1000 Vrms min. @ sea level.

OPERATING TEMPERATURE: -30°C to 85°C.

SOLDERABILITY: Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).

**NOTE:** Any models supplied with P, R, Q, B or G contact material are RoHS compliant and compatible.

**NOTE:** Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

### Materials

CASE: Glass filled nylon 6/6, flame retardant, heat stabilized or diallyl phthalate (DAP), (UL 94V-0) or glass filled nylon 4/6, flame retardant, heat stabilized.

ACTUATOR: Brass, chrome plated.

BUSHING: Brass, nickel plated.

HOUSING: Stainless steel.

SWITCH SUPPORT: Brass, matte-tin plated.

END CONTACTS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Coin silver, silver plated. See above for additional contact materials.

CENTER CONTACTS & TERMINALS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Copper alloy, silver plated. See page F-42 for additional contact materials.

TERMINAL SEAL: Epoxy.

HARDWARE: Nut & Locking Ring: Brass, nickel plated.

Lockwasher: Steel, nickel plated. Additional hardware available separately, see Section N.

### Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages F-33 thru F-37. For additional options not shown in catalog, consult Customer Service Center. All models have epoxy terminal seal and are compatible with all "bottom-wash" PCB cleaning methods.



#### Switch Function

- T101** SPDT On-None-On
- T102** SPDT Off-None-On
- T103** SPDT On-Off-On
- T105** SPDT Mom.-Off-Mom.
- T107** SPDT On-Off-Mom.
- T108** SPDT On-None-Mom.
- T201** DPDT On-None-On
- T203** DPDT On-Off-On
- T205** DPDT Mom.-Off-Mom.
- T207** DPDT On-Off-Mom.
- T208** DPDT On-None-Mom.
- T211** DPDT On-On-On

#### Actuator

- P3** Flatted, anti-rotation, .490" high
- S** .370" high
- K** Locking lever, round tip
- L1** .640" high
- M1** .220" high
- S1** .410" high
- M** .210" high
- L** .290" high

#### Bushing

- H** .220" high, threaded, flat
- H9** .220" high, unthreaded, flat
- CF** Splashproof, .310" high, threaded, flat
- D9** .260" high, unthreaded, keyway
- T** .310" high, threaded, flat
- T9** .310" high, unthreaded, flat
- TD** .260" high, threaded, keyway
- TK** .310" high, threaded, keyway
- Y** .220" high, threaded, keyway
- Y9** .220" high, unthreaded, keyway

#### Terminations

- A** Right angle, PC thru-hole
- AV** Vertical right angle, PC thru-hole
- C** PC Thru-hole
- V3** Vertical mount V-bracket
- Z** Solder lug
- W** Wire wrap

#### Contact Material

- B** Gold
- P** Gold, matte tin
- Q** Silver
- G** Gold over silver
- R** Gold over silver, matte-tin

#### Seal

- E** Epoxy



F

Toggle



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change

T Series  
Subminiature Toggle Switches


SWITCH FUNCTION

| NO. POLES | MODEL NO. | SWITCH FUNCTION                                                                   |                                                                                   |                                                                                   | CONNECTED TERMINALS                                                               |                                                                                   |                                                                                    | SCHEMATIC                                                                                |
|-----------|-----------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|
|           |           | POS. 1                                                                            | POS. 2                                                                            | POS. 3                                                                            | POS. 1                                                                            | POS. 2                                                                            | POS. 3                                                                             |                                                                                          |
|           |           |  |  |  |  |  |  |                                                                                          |
|           |           | C&K marking on opposite side                                                      |                                                                                   |                                                                                   | C&K marking on opposite side                                                      |                                                                                   |                                                                                    |                                                                                          |
| SP        | T101      | ON                                                                                | NONE                                                                              | ON                                                                                | 2-3                                                                               | N/A                                                                               | 2-1                                                                                |       |
|           | T103      | ON                                                                                | OFF                                                                               | ON                                                                                | 2-3                                                                               | OPEN                                                                              | 2-1                                                                                |                                                                                          |
|           | T105      | MOM.                                                                              | OFF                                                                               | MOM.                                                                              |                                                                                   |                                                                                   |                                                                                    |                                                                                          |
|           | T107      | ON                                                                                | OFF                                                                               | MOM.                                                                              | 2-3                                                                               | NA                                                                                | 2-1                                                                                |                                                                                          |
|           | T108      | ON                                                                                | NONE                                                                              | MOM.                                                                              |                                                                                   |                                                                                   |                                                                                    |                                                                                          |
|           | T102      | OFF                                                                               | NONE                                                                              | ON                                                                                | OPEN                                                                              | N/A                                                                               | 3-1                                                                                | SPST  |

SPDT



Part number shown: T101SHZQE

| NO. POLES | MODEL NO. | SWITCH FUNCTION                                                                     |                                                                                     |                                                                                     | CONNECTED TERMINALS                                                                 |                                                                                     |                                                                                       | SCHEMATIC                                                                             |
|-----------|-----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
|           |           | POS. 1                                                                              | POS. 2                                                                              | POS. 3                                                                              | POS. 1                                                                              | POS. 2                                                                              | POS. 3                                                                                |                                                                                       |
|           |           |  |  |  |  |  |  |                                                                                       |
|           |           | C&K marking on opposite side                                                        |                                                                                     |                                                                                     | C&K marking on opposite side                                                        |                                                                                     |                                                                                       |                                                                                       |
| DP        | T201      | ON                                                                                  | NONE                                                                                | ON                                                                                  | 2-3,5-6                                                                             | N/A                                                                                 | 2-1,5-4                                                                               |  |
|           | T203      | ON                                                                                  | OFF                                                                                 | ON                                                                                  | 2-3,5-6                                                                             | OPEN                                                                                | 2-1,5-4                                                                               |                                                                                       |
|           | T205      | MOM.                                                                                | OFF                                                                                 | MOM.                                                                                |                                                                                     |                                                                                     |                                                                                       |                                                                                       |
|           | T208      | ON                                                                                  | NONE                                                                                | MOM.                                                                                | 2-3,5-6                                                                             | N/A                                                                                 | 2-1,5-4                                                                               |                                                                                       |
|           | T211*     | ON                                                                                  | ON                                                                                  | ON.                                                                                 | 2-3,5-6                                                                             | 2-3,5-4                                                                             | 2-1,5-4                                                                               |                                                                                       |


DPDT



Part number shown: T201SHZQE


MOM. = Momentary  
\* Wiring for 3-way switch refer to page N-10

All models with all options when ordered with G, L, R or Q contact material.



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change

www.ck-components.com




Toggle

# T Series Subminiature Toggle Switches

## ACTUATOR




**M** .210" HIGH




Standard with A, AV or V3 terminations.

**S** .370" HIGH




Standard with Z, C or W terminations.


**M1** .220" HIGH  
(with "T" bushing)



**S1** .410" HIGH  
(with "T" bushing)



**L** .290" HIGH



**L1** .640" HIGH




**P3** ANTI-ROTATION, FLATTED,  
.450" HIGH



Available with T & T9 bushings only.  
Dress nut part number 709901201  
supplied standard with threaded bushing.

1 Actuator shown with standard H bushing.  
Subtract .040 (1,02) for TD and D9 bushings,  
subtract .090 (2,29) for T, T9, TK, K9 &  
CF bushings.  
2 Actuators shown with T, T9, TK & CF bushings,  
add .050 (1,27) for TD and D9 bushings,  
add .090 (2,29) for H, H9, Y & Y9 bushings.  
All actuators have chrome finish (except K).

**K** LOCKING LEVER



Not available with CF bushing option.

Bushing option code not required. Not available with TX05 & TX07 models.

### Locking Positions



-01 & -02 Models  
2 Position lock



-03 & -11 Models  
3 Position lock



-08 Models  
1 Position lock


K actuators have natural aluminum finish.

Keyway on right side. To prevent accidental actuation, toggles  
must be lifted before being actuated. When released, toggles  
again lock in place. Overtightening mounting nut may cause  
actuator to bind.


## BUSHING



**H** .220" HIGH THREADED, FLAT




**H9** .220" HIGH UNTHREADED, FLAT




H standard with C, W & Z terminations.

H9 standard with A, AV & V3 terminations.


**Y** .220" HIGH THREADED, KEYWAY




**Y9** .220" HIGH UNTHREADED, KEYWAY



**T** .310" HIGH THREADED, FLAT



**T9** .310" HIGH UNTHREADED, FLAT



Third Angle  
Projection

Dimensions are shown: Inches (mm)

Specifications and dimensions subject to change



**F**


Toggle



# T Series Subminiature Toggle Switches


## BUSHING

**TK** .310" HIGH THREADED, KEYWAY




**TD** .260" HIGH THREADED, KEYWAY

**D9** .260" HIGH UNTHREADED, KEYWAY






**CF** SPLASHPROOF, .310" HIGH THREADED, FLAT




IP67 Degree of protection.  
Internal o-ring actuator seal and  
external bushing seal washer standard.

Not available with K locking lever option.




## TERMINATIONS

**Z** SOLDER LUG




**C** PC THRU-HOLE



Not available with P or R contact materials.

T102 - omit center hole.


**W** WIRE WRAP



Third Angle  
Projection

Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change

www.ck-components.com




Toggle

# T Series Subminiature Toggle Switches


## TERMINATIONS

### A RIGHT ANGLE, PC THRU-HOLE



Actuator Shown In Pos. 1

Not available with T102 model.




#### PC MOUNTING




**T101MH9ABE**  
Horizontal Actuation  
**SPDT**



### A RIGHT ANGLE, PC THRU-HOLE



Actuator Shown In Pos. 1




#### PC MOUNTING



**T201MH9ABE**  
Horizontal Actuation  
**DPDT**


### AV VERTICAL RIGHT ANGLE, PC THRU-HOLE





Actuator Shown In Pos. 1

T102 Models: Omit terminal 2

**NOTE:** Terminal bend radii and lead-in manufacturing option.




#### PC MOUNTING




**T101MH9AVBE**  
Vertical Actuation  
**SPDT**


### AV VERTICAL RIGHT ANGLE, PC THRU-HOLE



Actuator Shown In Pos. 1




#### PC MOUNTING




**T201MH9AVBE**  
Vertical Actuation  
**DPDT**

**NOTE:** Terminal bend radii and lead-in manufacturing option.


### V3 VERTICAL MOUNT, V-BRACKET




Actuator Shown In Pos. 1



**T102 Models:**  
Omit terminal 2



#### PC MOUNTING



**T101MH9V3BE**  
**SPDT**

Third Angle Projection

Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change

www.ck-components.com

# T Series Subminiature Toggle Switches


## TERMINATIONS





**V3** VERTICAL MOUNT, V-BRACKET



T201MH9V3BE  
DPDT



Actuator Shown In Pos. 1



## CONTACT MATERIAL



| OPTION CODE | CONTACT MATERIAL                   | TERMINAL PLATING       | RATINGS                           |                                                                                                                                                                           |
|-------------|------------------------------------|------------------------|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>B</b>    | GOLD <sup>1</sup>                  | GOLD <sup>1</sup>      | LOW LEVEL/<br>DRY CIRCUIT         | 0.4 VA MAX. @ 20 V AC OR DC MAX.                                                                                                                                          |
| <b>P</b>    |                                    | MATTE-TIN <sup>6</sup> |                                   |                                                                                                                                                                           |
| <b>Q</b>    | SILVER <sup>4,5</sup>              | SILVER <sup>5</sup>    | POWER                             | TX01 MODELS: 3 AMPS @ 120 V AC OR 28 V DC.<br>ALL OTHER MODELS: 2 AMPS @ 120 V AC OR 28 V DC.                                                                             |
| <b>G</b>    | GOLD OVER<br>SILVER <sup>2,3</sup> | GOLD <sup>3</sup>      | LOW LEVEL/DRY<br>CIRCUIT OR POWER | TX01 MODELS: 0.4 VA MAX @ 20 V AC OR DC MAX. OR<br>3 AMPS @ 120 V AC OR 28 V DC.<br>ALL OTHER MODELS: 0.4 VA MAX @ 20 V AC OR DC MAX.<br>OR 2 AMPS @ 120 V AC OR 28 V DC. |
| <b>R</b>    |                                    | MATTE-TIN <sup>6</sup> |                                   |                                                                                                                                                                           |

\* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

<sup>1</sup> CONTACTS & TERMINALS: Copper alloy, with gold plate over nickel plate.

<sup>2</sup> END CONTACTS: Coin silver, with gold plate over nickel plate.

<sup>3</sup> CENTER CONTACTS & ALL TERMINALS: Copper alloy, with gold plate over nickel plate.

<sup>4</sup> END CONTACTS: Coin silver, silver plated.

<sup>5</sup> CENTER CONTACT & ALL TERMINALS: Copper alloy, silver plated.


<sup>6</sup> TERMINALS: Copper alloy, with matte-tin over nickel plate.

All models  with all options when ordered with R, G, or Q contact material.  
B contact material standard with A, AV, V3 & W terminations.  
Q contact material standard with C & Z terminations.

## SEAL




**E** EPOXY SEAL



## AVAILABLE HARDWARE

**759D02000** SEALING BOOT



\* Note: For use with S1 actuator style when combined with T, TK, and CF bushings.



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change

[www.ck-components.com](http://www.ck-components.com)



**F**

**Toggle**