

MECF-20-01-L-DV

MECF-05-01-L-DV-WT

MECF SERIES

(1.27 mm) .050"

MINI EDGE CARD SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MECF-DV

Insulator Material:

-01=Black Liquid
Crystal Polymer
-02=Natural Liquid
Crystal Polymer

Contact Material:

BeCu

Plating:

Sn or Au over
50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +125 °C

Current Rating:

3.5 A per pin
(2 adjacent pins powered)

Voltage Rating:

280 VAC

RoHS Compliant:

Yes

Mates with:

(1.60 mm) .062" card,
(2.36 mm) .093" card

HIGH-SPEED CHANNEL PERFORMANCE

MECF-DV

Rating based on Samtec reference channel.
For full SI performance data visit Samtec.com
or contact SIG@samtec.com

25
Gbps

Polarized

Up to
98 I/OsChoice of
two card
thicknessesRugged
weld tab
optionAlignment
pins

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (05-30)
(0.15 mm) .006" max (40-50)*
*(.004" stencil solution
may be available; contact
IPG@samtec.com)

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Non-polarized
- Other platings

MECF

POSITIONS PER ROW

-05, -08, -20,
-30, -40, -50

CARD THICKNESS

-01
= (1.60 mm) .062"
thick card
-02
= (2.36 mm) .093"
thick card

PLATING OPTION

-L
= 10 μ " (0.25 μ m)
Gold on contact,
Matte Tin on tail

DV

OPTION


-WT
= Weld Tabs
(Standard on
-02 card thickness,
optional on -01
card thickness)

-K
= (5.00 mm) .197" DIA
(-01 card thickness)
(5.70 mm) .224" DIA
(-02 card thickness)
Polyimide film
pick & place pad
(-TR only)

-TR
= Tape & Reel
packaging

POSITIONS PER ROW	A	B	C	D
-05	(10.46) .412	(8.64) .340	(14.53) .572	(12.45) .490
-08	(14.27) .562	(12.45) .490	(18.34) .722	(16.26) .640
-20	(29.51) 1.162	(27.69) 1.090	(33.58) 1.322	(31.50) 1.240
-30	(42.21) 1.662	(40.39) 1.590	(46.28) 1.822	(44.20) 1.740
-40	(54.91) 2.162	(53.09) 2.090	(58.98) 2.322	(56.90) 2.240
-50	(67.61) 2.662	(65.79) 2.590	(71.68) 2.822	(69.60) 2.740

POSITIONS PER ROW	POLARIZED POSITIONS (No Contact)
-05	3, 4
-08	5, 6
-20	15, 16
-30	21, 22
-40	31, 32
-50	41, 42



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.

Notes:
While optimized for
50 Ω applications, this
connector with alternative
signal/ground patterns may
also perform well in certain
75 Ω applications.

Some sizes, styles and
options are non-standard,
non-returnable.