






PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL

PC BOARD VERSIONS		
PRODUCT NR:	PCB THICKNESS	DIM A
85866-X02	1.6	2.90
85866-X12	2.4	3.53
85866-X02LF	1.6	2.90
85866-X12LF	2.4	3.53



- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 INDICATED HOLES ARE UNPLATED.
 - 4 For PLATING SPEC, REFER TO DRAWING 10097866.
 - 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
 - 6 SET BACK FOR TAIL BLOCK
 - 7 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.
 - 8 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 - 9 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - 10 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

PC BOARD THICKNESS $\approx$ 0.2
(SEE TABLE)

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
SEE NOTES						www.fciconnect.com	
ltr	ecm no	dr	date	projection	title	5 ROW R.A. S.T.B. SIGNAL RECEPT. 96mm MOD. P.P.	
H	0608-0088	Cent	03/03/09	linear			
C	V00578	LLA	000316	angles		product family METRAL (tm)	
D	V00850	GNV	000512	dr	R. VISSCHERS	941005	code
E	0604-0106	CLU	041230	engr	E. FEIJEN	941005	size dwg no
F	0607-0169	Cent	05/15/07	chr	E. FEIJEN	941005	scale
G	0608-0171	TER	8/26/08	app	E. FEIJEN	941005	5:1
sheet	revision						
index	sheet	1					