





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			J	REVISED PER ECO-14-000255	16JUL2014	NK	MM

1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
2. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
3. RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
4.  FOR KINKED TAILS.
5. 0.000127 [.000005] GOLD IN CONTACT AREA, 0.00254–0.00504 [.000100–.000200] MATTE TIN–LEAD ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
6. HOUSING: LCP, COLOR–BLACK.
POSTS: COPPER ALLOY.
7. 0.000127 [.000005] GOLD IN CONTACT AREA, 0.00254–0.00504 [.000100–.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



△ 8 OBSOLETE	△ 5	101.19 [3.984]	99.08 [3.900]	39	40	4-146291-0
	△ 5	98.65 [3.884]	96.52 [3.800]	38	39	3-146291-9
	△ 5	96.11 [3.784]	93.98 [3.700]	37	38	3-146291-8
	△ 5	93.57 [3.684]	91.44 [3.600]	36	37	3-146291-7
	△ 5	91.03 [3.584]	88.90 [3.500]	35	36	3-146291-6
	△ 5	88.49 [3.484]	86.36 [3.400]	34	35	3-146291-5
	△ 5	85.95 [3.384]	83.82 [3.300]	33	34	3-146291-4
	△ 5	83.41 [3.284]	81.28 [3.200]	32	33	3-146291-3
	△ 5	80.87 [3.184]	78.74 [3.100]	31	32	3-146291-2
	△ 5	78.33 [3.084]	76.20 [3.000]	30	31	3-146291-1
	△ 5	75.79 [2.984]	73.66 [2.900]	29	30	3-146291-0
	△ 5	73.25 [2.884]	71.12 [2.800]	28	29	2-146291-9
	△ 5	70.71 [2.784]	68.58 [2.700]	27	28	2-146291-8
	△ 5	68.17 [2.684]	66.04 [2.600]	26	27	2-146291-7
	△ 5	65.63 [2.584]	63.5 [2.500]	25	26	2-146291-6
	△ 5	63.09 [2.484]	60.96 [2.400]	24	25	2-146291-5
	△ 5	60.55 [2.384]	58.42 [2.300]	23	24	2-146291-4
	△ 5	58.01 [2.284]	55.88 [2.200]	22	23	2-146291-3
	△ 5	55.47 [2.184]	53.34 [2.100]	21	22	2-146291-2
	△ 5	52.93 [2.084]	50.80 [2.000]	20	21	2-146291-1
	△ 5	50.39 [1.984]	48.26 [1.900]	19	20	2-146291-0
	△ 5	47.85 [1.884]	45.72 [1.800]	18	19	1-146291-9
	△ 5	45.31 [1.784]	43.18 [1.700]	17	18	1-146291-8
	△ 5	42.77 [1.684]	40.64 [1.600]	16	17	1-146291-7
	△ 5	40.23 [1.584]	38.10 [1.500]	15	16	1-146291-6
	△ 5	37.69 [1.484]	35.56 [1.400]	14	15	1-146291-5
	△ 5	35.15 [1.384]	33.02 [1.300]	13	14	1-146291-4
	△ 5	32.61 [1.284]	30.48 [1.200]	12	13	1-146291-3
	△ 5	30.07 [1.184]	27.94 [1.100]	11	12	1-146291-2
	△ 5	27.53 [1.084]	25.40 [1.000]	10	11	1-146291-1
	△ 5	24.99 [.984]	22.86 [.900]	9	10	1-146291-0
	△ 5	22.45 [.884]	20.32 [.800]	8	9	146291-9
△ 5	19.91 [.784]	17.78 [.700]	7	8	146291-8	
△ 5	17.37 [.684]	15.24 [.600]	6	7	146291-7	
△ 5	14.83 [.584]	12.70 [.500]	5	6	146291-6	
△ 5	12.29 [.484]	10.16 [.400]	4	5	146291-5	
△ 5	9.75 [.384]	7.62 [.300]	3	4	146291-4	
SUPERSEDED	△ 5	7.21 [.284]	5.08 [.200]	2	3	146291-3
46267-1		4.67 [.184]	2.54 [.100]	1	2	146291-2
OBSOLETE		2.13 [.084]	-	0	1	146291-1
	PLATING	C	B	A	NO OF POSITIONS	PART NUMBER

SUPERSEDED BY 146267-1
OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.				DIN T. HOFFMAN 12/6/95				TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWG G. DUBNICZKI 2/1/96		NAME HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW HIGH TEMPERATURE, VERTICAL WITH RETENTION FEATURE, W/.025 SQ. POSTS, .100 C/L			
				APP'D G. DUBNICZKI 2/1/96					
		0 R/LC ± — 1 R/LC ± — 3 R/LC ± 0.51[.02] 3 R/LC ± 0.127[.005] 4 R/LC ± 0.0127[.0005]		PRODUCT SPEC —		SIZE A1			
				APPLICATION SPEC —					
 MATERIAL		FINISH SEE TABLE		WEIGHT —		CAGE CODE 00779		DRAWING NO C=146291	
				RESTRICTED TO —					
				CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2	
								REV. 0	

