





1	SPS, UL 94V-0 RATED, BLACK.
2	BRASS.
3	.076 μ m MINIMUM GOLD OVER 0.76 μ m MINIMUM PALLADIUM NICKEL ON MATING AREA, 3.80 μ m MINIMUM TIN-LEAD ON SOLDER TAIL, ALL OVER 1.27 μ m MINIMUM NICKEL.
4	DATUMS AND DIMENSIONS ESTABLISHED BY CUSTOMER.
5	RECOMMENDED MINIMUM TRACE WIDTH FOR END POSITIONS WHEN CARRYING 3 AMPS: 1.8 WIDE $\times$ 55 μ m THICK, BOTH SIDES.

				878531-1							
				PART NUMBER							
THIS DRAWING IS A CONTROLLED DOCUMENT FOR OUR PROPRIETARY. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				QWY		R.S.KLINE		07-05-95			
DIMENSIONS: mm 				TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		R.S.KLINE		07-11-95	
				APPROXIMATELY		R.D.W.		R.S.KLINE		07-11-95	
				PRODUCT SPEC		NAME		AMP AMP Incorporated Harrisburg, PA 17105-3608			
				APPLICATION SPEC		HEADER ASSY, 6 POSN, SEQUENCED, MDI					
MATERIAL				FINISH		SIZE		CASE CODE		DRAWING NO	
				SEE CALLOUTS		SEE CALLOUTS		A1 00779		C=878531	
CUSTOMER DRAWING				SCALE		8:1		SHEET		OF 1 REV 0	