



©1966 AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS				
ZONE	LYR	DESCRIPTION	DATE	APPROVED
	A	REVISED	Y-755	9-12-66 M.S. D.H.
	A1	REVISED	2622	8-6-70 M.S. D.H.
	B	REVISED	3131	8-13-71 M.S. R.F.
	C	REVISED FINISH	7225 mS	2-26-81 R.O.
	D	REV PER 0600-6466-97	II	10-98



- ① .00003 GOLD OVER .00005 NICKEL IN CONTACT AREA, TIN-LEAD OVER NICKEL IN TAIL AREA.
- ② .00005 GOLD OVER .00005 NICKEL IN CONTACT AREA, TIN-LEAD OVER NICKEL IN TAIL AREA.

①	202947-3	.140	.595	BRASS	△
085	202947-2	.140	.595	BRASS	△
PART NO.		"D"	"C"	MATERIAL	FINISH

UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON DECIMALS ±.005 ANGLES ±		CONTRACT NO. 3-25-66		AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL SEE TABLE		DATE 4/4/66		NAME CONTACT PIN	
HEAT TREAT		DATE 4/4/66		CODE IDENT NO. 00779	
FINISH SEE TABLE		DATE 12-4-66		NUMBER 202947	
LOG DEF. FO		SCALE 10-1		BY CALC ACTUAL SHEET	

CUSTOMER DRAWING