



Magnetic properties	Conditions	Min	Typ	Max	Unit
Pull-In	at 20°C	12,2		20,4	VDC
Test equipment				KMS-16	

Special Product Data	Conditions	Min	Typ	Max	Unit
Contact - No.			87		
Contact - form			A - NO		
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			200	V
Carry current	DC or Peak AC			0,5	A
Switching current	DC or Peak AC			0,4	A
Sensor-resistance	measured with 40% overdrive Sensor deactivated			150	mOhm
Housing material			PBT glass fibre reinforced		
Case color			blue		
Sealing compound			Epoxy resin		

Environmental data	Conditions	Min	Typ	Max	Unit
Shock	1/2 sine wave duration 11ms			30	g
Vibration	from 10 - 2000 Hz			20	g
Ambient temperature		-20		85	°C
Storage temperature		-35		85	°C
Cleaning			fully sealed		