









| ▲ SWITCH FUNCTION |        |        |
|-------------------|--------|--------|
| POS. 1            | POS. 2 | POS. 3 |
|                   |        |        |
| ON                | NONE   | ON     |
| 2-1               | OPEN   | 2-3    |



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: GOLD
5. RATING: 0.4 (VA) MAX. @20V MAX.
6. ELECTRIC LIFE: 30,000 CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.



|     |        |                           |         |    |
|-----|--------|---------------------------|---------|----|
| D   | 23137  | update print              | 12/8/17 | MW |
| C   | 15013  | CORRECTED ACTUATOR LENGTH | 7/7/05  | JB |
| B   | 14976  | CHANGED ACTUATOR LENGTH   | 6/3/05  | JB |
| A   | 14932  | RELEASED FOR PRODUCTION   | 5/20/05 | JB |
| REV | PCR NO | DESCRIPTION               | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE 500SSP1S3M6REA

SCALE  
2:1DATE  
5/20/2005DR  
JBDWG  
T505002REV  
D