



SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor
- Samsung P/N : [CL10B473KO8NFNC](#)
- Description : CAP, 47nF, 16V, ±10%, X7R, 0603

A. Samsung Part Number

CL 10 B 473 K O 8 N F N C

Series	Samsung Multi-layer Ceramic Capacitor		
Size	0603 (inch code)	L: 1.6 ± 0.1 mm	W: 0.8 ± 0.1 mm
Dielectric	X7R	Inner electrode	Ni
Capacitance	47 nF	Termination	Cu
Capacitance tolerance	±10 %	Plating	Sn 100% (Pb Free)
Rated Voltage	16 V	Product	Product for POWER application
Thickness	0.8 ± 0.1 mm	Special	Reserved for future use
		Packaging	Cardboard Type, 7" reel

B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
Capacitance	Within specified tolerance	1kHz±10% 1.0±0.2Vrms
Tan δ (DF)	0.035 max.	
Insulation Resistance	10,000Mohm or 100Mohm·μF Whichever is Smaller	Rated Voltage 60~120 sec.
Appearance	No abnormal exterior appearance	Microscope (×10)
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
Temperature Characterisitcs	X7R (From -55 to 125, Capacitance change shoud be within ±15%)	
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g·F, for 10±1 sec.
Bending Strength	Capacitance change : within ±12.5%	Bending to the limit (2mm) with 1.0mm/sec.
Solderability	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245±5, 3±0.3sec. (preheating : 80~120 for 10~30sec.)
Resistance to Soldering heat	Capacitance change : within ±7.5% Tan δ, IR : initial spec.	Solder pot : 270±5, 10±1sec.

	Performance	Test condition
Vibration Test	Capacitance change : within $\pm 5\%$ Tan δ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours \times 3 direction (x, y, z)
Moisture Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.05 max IR : 500Mohm or $25\text{Mohm} \cdot \mu\text{F}$ Whichever is Smaller	With rated voltage $40\pm 2^\circ\text{C}$, 90~95%RH, 500+12/-0hrs
High Temperature Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.05 max IR : 1000Mohm or $50\text{Mohm} \cdot \mu\text{F}$ Whichever is Smaller	With 200% of the rated voltage Max. operating temperature $1000+48/-0\text{hrs}$
Temperature Cycling	Capacitance change : within $\pm 7.5\%$ Tan δ , IR : initial spec.	1 cycle condition Min. operating temperature 25 Max. operating temperature 25 5 cycle test

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : $260+0/-5^\circ\text{C}$, 10sec. Max)

* For the more detail Specification, Please refer to the Samsung MLCC catalogue.