

Customer Information Sheet

DRAWING No.: M20-611XXXX

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

**SPECIFICATION:****MATERIAL:****MOULDING =**

05 FINISH = GLASS FILLED POLYESTER UL94V-0 BLACK

45 FINISH = HIGH TEMP NYLON 6T UL94V-0, BLACK

CONTACTS = PHOSPHOR BRONZE**FINISH:****CONTACTS = 0.08 μ GOLD OVER NICKEL****ELECTRICAL:****CURRENT RATING = 3A MAX****CONTACT RESISTANCE = 30 MILLIOHMS MAX****INSULATION RESISTANCE = 5,000 MEGOHMS MIN****VOLTAGE PROOF = 1,000V AC FOR 1 MINUTE****MECHANICAL:****INSERTION FORCE (PER CONTACT) = 2.0N/MAX****WITHDRAWAL FORCE (PER CONTACT) = 0.3N MIN****ENVIRONMENTAL:****TEMPERATURE RANGE = -55°C TO +105°C****PACKING:****TUBE**

No. OF WAYS PER ROW	DIM 'A'	DIM 'B'
20	51.46	48.26
32	81.94	78.74

NOTES:1. ALL TOLERANCES ARE ± 0.20 UNLESS OTHERWISE STATED.**ORDER CODE:****M20-611XXXX**

No. OF WAYS PER ROW

20, 32

FINISH:

05 = GOLD

45 = GOLD (RoHS COMPLIANT)

CP	7	03.12.09	10582
NAME	ISS.	DATE	C/NOTE
APPROVED: C.PENROSE			
CHECKED: R.ADDE			
DRAWN: W.J.BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ± 1 mm
X.X = ± 0.25 mm
X.XX = ± 0.10 mm
X.XXX = ± 0.01 mm

ANGLES = $\pm 5^\circ$

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²**TITLE:**PCI04 CONNECTOR
(NON-STACKTHROUGH)

DRAWING NUMBER:

M20-611XXXX

SHT

2 OF 2