

Surface Mount

Dual Matched MMIC Amplifiers

NEW!

MERA-7433

50Ω High Dynamic Range DC to 1 GHz

Features

- Two matched amplifiers in one package
- InGaP HBT IF and RF amplifier
- frequency range, DC to 1 GHz, usable to 4 GHz
- high gain, 25 dB typ. at 100 MHz
- up to +19 dBm typ. output power at 100 MHz
- high IP3, +36 dBm at 100 MHz
- low noise figure, 2.7 dB typ.
- low thermal resistance
- transient protected
- patent pending
- useable as balanced and push pull amplifier

Applications

- cellular
- catv
- VHF & UHF communication receivers & transmitters



CASE STYLE: DL805
PRICE: \$ 4.70 ea. QTY (25)

Electrical Specifications @25°C

Freq.* (GHz)	Gain, dB Typical A1, A2						Maximum Power (dBm)					Dynamic Range				VSWR (:1) Typ.		Maximum Rating**		DC Operating Power Pin 5, Pin 8				Thermal Resistance		matching ¹					
																										Amplitude Unbalance between 2 amps (dB)				Phase Unbalance between 2 amps (deg.)	
																										DC-1 GHz Typ. Max.		1-4 GHz Typ. Max.		DC-1 GHz Typ.	
f _L -f _U	0.1	1	2	3	4	Min.@ 1GHz	Output (1 dB Comp.) Typ. 0.1 GHz 1.0 GHz 2.0 GHz	Min.@ 0.1GHz	Input (no dmg.)	NF (dB) Typ.	0.1 GHz	0.5 GHz	1.0 GHz	In	Out	I mA	P mW	Current (mA)	Volt Typ	Min	Max	θjc, typ. °C/W									
DC-1	25	22.4	19	16.2	13.4	20	19	18.3	14.8	18	10	2.7	36	35	32	1.25	1.8	130	700	80	4.8	4.3	5.3	120	0.15	0.3	0.3	—	0.5	1.0	

* Guaranteed specification DC-1GHz. Low frequency cutoff determined by external coupling capacitors.


** Permanent damage may occur if any of these limits are exceeded.

These ratings are not intended for continuous normal operation. Reliability predictions and normal operating conditions are applicable at current specified.

Pin Connections

PORT	
RF IN 1	1
RF OUT 1	8
RF IN 2	4
RF OUT 2	5
DC 1	8
DC 2	5
GROUND	2,3,6,7 and paddle

MTTF vs. Junction Temp.




Maximum Ratings²

Operating Case Temperature -45°C to 85°C


Storage Temperature -55°C to 100°C

2. See application note AN-60-032 for adequate heat sinking of paddle.


typical biasing configuration



Outline Drawing



Demo Board MCL P/N: TB-294 Suggested PCB Layout (PL-165)



Outline Dimensions (inch)

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
.128	.128	.035	.008	.080	.047	.013	—	.014	.026	.158	.158	.084	.013	.030	.048	.020	.025	grams
3.25	3.25	0.90	0.20	2.03	1.19	0.33	—	0.36	0.66	4.01	4.01	2.13	0.33	0.76	1.22	0.51	0.64	.02

Mini-Circuits®







Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010






Mini-Circuits ISO 9001 & ISO 14001 Certified





INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

REV. OR
M94145
ED-11699/7
WZ/TD/CP/AM
041104







Freq. MHz	S11 (Input Return Loss)			S21 (Power Gain)			S12 (Isolation Out-in)			S22 (Output Return Loss)			K
	dB	Mag	Angle(deg)	dB	Mag	Angle	dB	Mag	Angle	dB	Mag	Angle	
20.00	-30.65	0.03	179.29	24.85	17.48	175.69	-27.79	0.04	-6.39	-19.19	0.11	177.75	1.05
30.00	-30.66	0.03	177.60	24.85	17.48	174.46	-27.51	0.04	-2.37	-19.01	0.11	177.20	1.04
50.00	-32.45	0.02	-161.44	24.83	17.44	171.30	-27.82	0.04	-5.22	-18.88	0.11	-178.75	1.05
100.00	-29.56	0.03	-151.50	24.76	17.30	163.47	-27.80	0.04	-7.16	-18.29	0.12	-174.46	1.05
200.00	-26.33	0.05	-154.32	24.54	16.87	148.12	-27.67	0.04	-15.11	-16.78	0.14	-174.26	1.05
300.00	-23.79	0.06	-158.15	24.32	16.44	132.94	-27.59	0.04	-23.26	-15.42	0.17	-178.51	1.05
400.00	-22.26	0.08	-168.49	24.08	16.00	118.16	-27.57	0.04	-29.47	-14.32	0.19	173.95	1.05
500.00	-21.39	0.09	-175.93	23.84	15.56	103.62	-27.56	0.04	-37.11	-13.28	0.22	164.41	1.05
600.00	-20.49	0.09	173.33	23.56	15.07	89.29	-27.31	0.04	-45.16	-12.40	0.24	154.36	1.04
700.00	-19.65	0.10	164.46	23.28	14.59	75.03	-27.23	0.04	-53.21	-11.60	0.26	144.53	1.03
800.00	-19.09	0.11	155.72	22.98	14.09	61.16	-27.12	0.04	-60.84	-10.99	0.28	134.01	1.03
900.00	-18.46	0.12	146.31	22.65	13.57	47.37	-27.06	0.04	-68.96	-10.47	0.30	123.23	1.03
1000.00	-18.03	0.13	135.98	22.34	13.09	33.83	-26.88	0.05	-76.45	-9.99	0.32	112.52	1.03
1100.00	-17.45	0.13	126.04	22.01	12.60	20.31	-26.76	0.05	-85.37	-9.59	0.33	101.33	1.03
1200.00	-17.02	0.14	115.92	21.69	12.15	7.13	-26.62	0.05	-93.13	-9.25	0.34	90.22	1.03
1400.00	-16.43	0.15	96.35	21.03	11.26	-18.81	-26.34	0.05	-110.21	-8.69	0.37	68.01	1.03
1600.00	-15.90	0.16	75.14	20.36	10.42	-44.16	-25.98	0.05	-126.57	-8.23	0.39	45.75	1.03
1800.00	-15.40	0.17	55.21	19.74	9.71	-69.29	-25.67	0.05	-144.16	-7.85	0.41	23.63	1.03
2000.00	-15.10	0.18	32.91	19.10	9.02	-93.79	-25.30	0.05	-161.62	-7.58	0.42	1.42	1.04
2200.00	-14.76	0.18	10.19	18.48	8.39	-118.18	-24.95	0.06	-179.21	-7.38	0.43	-20.95	1.05
2400.00	-14.53	0.19	-13.49	17.86	7.82	-142.32	-24.63	0.06	162.18	-7.19	0.44	-43.18	1.06
2600.00	-14.24	0.19	-37.58	17.29	7.32	-166.14	-24.31	0.06	143.76	-6.97	0.45	-65.80	1.07
2800.00	-13.80	0.20	-62.42	16.70	6.84	169.92	-24.05	0.06	124.96	-6.76	0.46	-88.26	1.09
3000.00	-13.38	0.21	-88.07	16.14	6.41	146.11	-23.76	0.06	106.00	-6.59	0.47	-110.89	1.11
3200.00	-12.96	0.22	-114.09	15.55	5.99	122.70	-23.55	0.07	86.92	-6.44	0.48	-133.80	1.13
3400.00	-12.44	0.24	-140.05	14.97	5.60	99.38	-23.27	0.07	67.26	-6.30	0.48	-156.85	1.16
3600.00	-11.81	0.26	-165.14	14.42	5.26	76.07	-23.08	0.07	48.16	-6.08	0.50	-179.84	1.18
3800.00	-10.88	0.29	169.74	13.87	4.94	52.67	-22.93	0.07	27.88	-5.83	0.51	157.00	1.20
4000.00	-10.07	0.31	145.06	13.31	4.63	29.38	-22.83	0.07	8.09	-5.58	0.53	134.24	1.22
4500.00	-8.28	0.39	86.65	11.77	3.88	-28.13	-22.67	0.07	-41.31	-4.91	0.57	77.08	1.28
5000.00	-6.72	0.46	31.04	10.10	3.20	-84.70	-22.71	0.07	-90.46	-4.33	0.61	22.74	1.36
5500.00	-5.56	0.53	-21.51	8.45	2.65	-139.53	-22.90	0.07	-138.68	-3.80	0.65	-29.26	1.44
6000.00	-4.76	0.58	-71.40	6.81	2.19	166.96	-23.05	0.07	174.30	-3.54	0.67	-79.39	1.54
6500.00	-4.19	0.62	-119.47	5.17	1.81	114.74	-23.32	0.07	126.45	-3.33	0.68	-128.40	1.67
7000.00	-3.76	0.65	-166.39	3.60	1.51	63.79	-23.31	0.07	82.26	-3.21	0.69	-175.94	1.79
7500.00	-3.54	0.67	148.39	2.25	1.30	14.43	-23.39	0.07	37.02	-3.07	0.70	137.82	1.92
8000.00	-3.35	0.68	103.42	1.12	1.14	-34.61	-23.31	0.07	-8.50	-2.99	0.71	92.53	2.01
9000.00	-3.27	0.69	11.87	-0.47	0.95	-133.18	-22.84	0.07	-101.64	-2.87	0.72	1.30	2.09
10000.00	-3.35	0.68	-87.43	-1.86	0.81	125.16	-22.49	0.08	159.53	-2.74	0.73	-92.89	2.23
11000.00	-3.33	0.68	167.73	-3.12	0.70	19.23	-22.80	0.07	56.32	-2.85	0.72	171.76	2.62